



mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
ltr	ecn no	dr	date	.XX±.01/.X±.3		title	
AC	140002	LSS	07/22/94	.XXX±.005/.XX±.13		HEADER, QUICKIE	
AD	N05-0129	ZC	5/20/05	.XXXX±.0020/.XXX±.051		SEA, HORSE, RIGHT ANGLE	
AE	N05-0151	WG	7/31/07	0'±2'		product family QUICKIE	
AF	N08-0175	R.B	2008/08/22	J. SHREINER 1/16/90		size dwg no	
		engr		M. SMYK 1/16/90		A 65823	
		chr		M. SMYK 1/16/90		scale	
		appd		M. SMYK 1/16/90		5:1	
AE	sheet	revision	AF	AF	AF	AF	AF
21	index	sheet	1	2	3	4	5
			6	7	8	9	10
			11	12	13	14	15
			16	17	18	19	20
			21	22	23	24	25






RECOMMENDED HOLE PATTERN  
SCALE 10:1



VIEW F-F




SECTION G-G  
ROTATED 90°CW

Tous droits strictement réservés. Reproduction ou communication à des tiers. Interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.


All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCJ www.fciconnect.com	
ltr	ecn no	dr	date	linear	projection	product family	title
AF				.XX±.01/.X±.3		QUICKIE	HEADER, QUICKIE
				.XXX±.005/.XX±.13		size	SEA, HORSE, RIGHT ANGLE
				.XXXX±.0020/.XXX±.051	0°±2°	dwg no	code
						A	—
				dr	J. SHREINER	scale	sheet
				enfr	M. SMYK	5:1	2 of 21
				chr	M. SMYK		
				appd	M. SMYK		
sheet	revision						
21							
index	sheet						
2							


STB LATCH  
LATCH NOTE  
6617Z-001  
65824-001




HEADER WITH LATCHES




2X5  
STYLE A




2X5  
STYLE B



2X7  
STYLE C



2X8 THRU 2X30  
(2X10 SHOWN)  
STYLE D



ALL SIZES  
STYLE E

NOTES:

1. RECOMMENDED MOUNTING SCREW SIZE: #2-56 FILLISTER HD MACH SCREW, 3/8" LG FOR 1/16" & 3/32" BOARD, 7/16" LG FOR 1/8" BOARD.
2. MOLDING MAT'L: 30% GLASS FILLED POLYESTER, FLAME RETARDANT PER UL-94V-0, COLOR: BLUE.
3. PIN MAT'L: 3/4 HARD PHOS BRONZE ALLOY UNS C-51000.
4. 1\* MAX DRAFT PERMISSIBLE ON ALL SURFACES UNLESS OTHERWISE SPECIFIED.
5. PLATING ON LEAD-IN PORTION OF PIN IS MANUFACTURING OPTION.
6. BASIC DIM SHALL BE LOCATED SYMMETRICAL TO DATUM -Y-.
7. LOW PROFILE LATCHES TO BE USED WITH FEMALE CONNECTOR WITHOUT STRAIN RELIEF.  
STANDARD LATCHES TO BE USED WITH FEMALE CONNECTOR WITH STRAIN RELIEF.
8. .040±.003/1.02±.08 DIA HOLE TYP FOR SQ PINS, .035±.003/.89±.08. DIA HOLE TYP FOR RND PINS.
9. A. RETENTION FEATURE AVAILABLE ON CONNECTORS WITH .105/2.67, 120/3.05 OR 150/3.81 TAIL LENGTH. RETENTION P/N INCLUDES THE LETTER 'R' AFTER THE EXISTING P/N.  
EXAMPLE: 65823-XXX FOR EXISTING P/N  
RETENTION P/N  
65823-XXXR FOR RETENTION P/N  
RETENTION FEATURE LOCATION IS MANUFACTURERS OPTION.  
B. ROUND PINS HAVE 15 LBS/6.8 KGS MAX INSERTION AND .25 LB/.1 KG MIN RETENTION FORCE WHEN USED IN .035±.003/.89±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.  
C. SQUARE PINS HAVE A 15 LBS/6.8 KG MAX INSERTION AND .5 LB/.2 KG MIN RETENTION FORCE WHEN USED IN .040±.003/1.02±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.  
65496-\*\*\*L F IS JUST A LEAD FREE PRODUCT.  
10. THE HOUSING OF XXXX-YYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.  
11. PLATING OPTION: MAYBE EITHER GOLD OR GXT PLATING AT MANUFACTURER'S OPTION.
- 12.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCJ		www.fcjconnect.com	
ltr	ecn no	dr	date	linear	projection	title		HEADER, QUICKIE	
AF				.XX±.01/.X±.3		SEA, HORSE, RIGHT ANGLE		code	
				.XXX±.005/.XX±.13		product family		QUICKIE	
				.XXXX±.0020/.XXX±.051		size		dwg no	
				0'±2'		INCH/MM		A	
				dr J. SHREINER 1/16/90		scale		5:1	
				enfr M. SMYK 1/16/90		sheet		3 of 21	
				chr M. SMYK 1/16/90		revision			
				appd M. SMYK 1/16/90		sheet			
21	index								



SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-001(LF)	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76 Au DIVER 50u" / .1.27u Ni	A
-002(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-003(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-004(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-005(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-006(LF)	2x5	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u" / .3.81u Sn	A
-007(LF)	2x7	RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u" / .76 Au DIVER 50u" / .1.27u Ni	C
-008(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-009(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-010(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-011(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-012(LF)	2x7	SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u" / .3.81u Sn	C
-013(LF)	2x8	RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u" / .76 Au DIVER 50u" / .1.27u Ni	D
-014(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-015(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-016(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-017(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-018(LF)	2x8	SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u" / .3.81u Sn	
-019(LF)	2x10	RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u" / .76 Au DIVER 50u" / .1.27u Ni	
-020(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-021(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-022(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-023(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-024(LF)	2x10	SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u" / .3.81u Sn	
-025(LF)	2x13	RND	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1	30u" / .76 Au DIVER 50u" / .1.27u Ni	
-026(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-027(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-028(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-029(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-030(LF)	2x13	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.675/17.15	1.66/42.1	150u" / .3.81u Sn	
-031(LF)	2x17	RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u" / .76 Au DIVER 50u" / .1.27u Ni	
-032(LF)		SQ				.105/2.67		150u" / .3.81u Sn	
-033(LF)		RND				.150/3.81		30u" / .76 Au DIVER 50u" / .1.27u Ni	
-034(LF)		SQ				.150/3.81		150u" / .3.81u Sn	
-035(LF)		SQ				.675/17.15		30u" / .76 Au DIVER 50u" / .1.27u Ni	
65823-036(LF)	2x17	SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u" / .3.81u Sn	D

A

A

B

B



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Property of FCI. Copyright FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.



mat'l. code		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com	
ltr	ecn no	dr	date	COPY		title	
AF				projection		HEADER, QUICKIE	
						SEA, HORSE, RIGHT ANGLE	
				angles		product family QUICKIE	
				dr		code	
				J. SHREINER		1/16/90	
				engr		1/16/90	
				M. SMYK		size	
				chr		1/16/90	
				M. SMYK		scale	
				M. SMYK		5:1	
				appd		A	
sheet	revision					65823	
21	index					A	

PART NUMBER	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE	
											ecn no
65823-037<LF>	2x20	ND	RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u"/.76u Au DVER 50u"/1.27u Ni	D	
-038<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-039<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-040<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-041<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
-042<LF>	2x20		SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u"/.3.81u Sn		
-043<LF>	2x25		RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u Au DVER 50u"/1.27u Ni		
-044<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-045<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-046<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-047<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
-048<LF>	2x25	ND	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u"/.3.81u Sn	D	
-049<LF>	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au DVER 50u"/1.27u Ni	A	
-050<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-051<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-052<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-053<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
-054<LF>	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/.3.81u Sn	A	
-055<LF>	2x7		RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u"/.76u Au DVER 50u"/1.27u Ni	C	
-056<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-057<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-058<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-059<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
-060<LF>	2x7		SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u"/.3.81u Sn	C	
-061<LF>	2x8		RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u"/.76u Au DVER 50u"/1.27u Ni	D	
-062<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-063<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-064<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-065<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
-066<LF>	2x8		SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u"/.3.81u Sn		
-067<LF>	2x10		RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76u Au DVER 50u"/1.27u Ni		
-068<LF>			SQ				.105/2.67		150u"/.3.81u Sn		
-069<LF>			RND				.150/3.81		30u"/.76u Au DVER 50u"/1.27u Ni		
-070<LF>			SQ				.150/3.81		150u"/.3.81u Sn		
-071<LF>			SQ				.675/17.15		30u"/.76u Au DVER 50u"/1.27u Ni		
65823-072<LF>	2x10	STD	SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u"/.3.81u Sn	D	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



strictly reserved. Reproduction or issue to third parties in any form is not permitted without written authority from the proprietor. FCI. Copyright FCI.



CUSTOMER COPY

tolerances unless otherwise specified  
 .XX±.01/.XX±.3  
 .XXX±.005/.XX±.13  
 .XXXX±.0020/.XXX±.051  
 0°±2'

mat'l. code  
 ltr ecn no dr date  
 AF  
 angles  
 dr J. SHREINER 1/16/90  
 engl M. SMYK 1/16/90

www.fciconnect.com  
 title HEADER, QUICKIE  
 SEA, HORSE, RIGHT ANGLE  
 product family QUICKIE  
 size dwg no  
 code

projection  
 INCH/MM  
 1/16/90  
 1/16/90  
 STA: Plus Released  
 65823-072-3  
 5 of 21

1/16/90  
 1/16/90  
 1/16/90  
 1/16/90

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-073 <LF> 2x13	STD	RND	2.060/52.32	1.200/30.48	1.950/38.61	.105/2.67	1.66/42.1	30u" / .76u Au OVER 50u" / 1.27u Ni	D
-074 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-075 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-076 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-077 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
-078 <LF> 2x13		SQ	2.060/52.32	1.200/30.48	1.950/38.61	.675/17.15	1.66/42.1	150u" / 3.81u" 1/27u Ni	
-079 <LF> 2x17		RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u" / .76u Au OVER 50u" / 1.27u Ni	
-080 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-081 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-082 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-083 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
-084 <LF> 2x17		SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u" / 3.81u" 1/27u Ni	
-085 <LF> 2x20		RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u" / .76u Au OVER 50u" / 1.27u Ni	
-086 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-087 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-088 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-089 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
-090 <LF> 2x20		SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u" / 3.81u" 1/27u Ni	
-091 <LF> 2x25		RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u Au OVER 50u" / 1.27u Ni	
-092 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-093 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-094 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-095 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
-096 <LF> 2x25	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u" / 3.81u" 1/27u Ni	
-097 <LF> 2x30	ND	RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u Au OVER 50u" / 1.27u Ni	
-098 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-099 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-100 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-101 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
-102 <LF>	ND	SQ				.675/17.15		150u" / 3.81u" 1/27u Ni	
-103 <LF>	STD	RND				.105/2.67		30u" / .76u Au OVER 50u" / 1.27u Ni	
-104 <LF>		SQ				.105/2.67		150u" / 3.81u" 1/27u Ni	
-105 <LF>		RND				.150/3.81		30u" / .76u Au OVER 50u" / 1.27u Ni	
-106 <LF>		SQ				.150/3.81		150u" / 3.81u" 1/27u Ni	
-107 <LF>		SQ				.675/17.15		30u" / .76u Au OVER 50u" / 1.27u Ni	
65823-108 <LF> 2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	150u" / 3.81u" 1/27u Ni	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY	
ltr	ecn no	dr	date	projection	www.fciconnect.com
AF				linear	title
				angular	SEA, HORSE, RIGHT ANGLE
				dr	product family QUICKIE
				engr	size dwg no
				chr	A
				appd	65823
sheet	revision	sheet	code		
21	index		sheet		6 of 21

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY	
ltr	ecn no	dr	date	projection	www.fciconnect.com
AF				linear	title
				angular	SEA, HORSE, RIGHT ANGLE
				dr	product family QUICKIE
				engr	size dwg no
				chr	A
				appd	65823
sheet	revision	sheet	code		
21	index		sheet		6 of 21

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-109(LF) 2x5	ND	SQ	1.260/32.00	.400/10.16	.780/18.29	.105/2.67	.86/21.8	30µ"/.76µ Au DVER 50µ"/1.27µ Ni	A
-110(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.980/23.37	↑	1.06/26.9	↑	C
-111(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-112(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-113(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-114(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-115(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-116(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-117(LF) 2x30	ND	↑	3.760/95.50	2.900/73.66	3.220/81.79	↑	3.36/85.3	↑	D
-118(LF) 2x5	STD	↑	1.260/32.00	.400/10.16	.780/18.29	↑	.86/21.8	↑	A
-119(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.980/23.37	↑	1.06/26.9	↑	C
-120(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-121(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-122(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-123(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-124(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-125(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-126(LF) 2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30µ"/.76µ Au DVER 50µ"/1.27µ Ni	D
-127(LF) 2x5	ND	RND	1.260/32.00	.400/10.16	.780/18.29	.150/3.81	.86/21.8	30µ"/.76µ GXT/GOLD FLASH	A
-128(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.980/23.37	↑	1.06/26.9	↑	C
-129(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-130(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-131(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-132(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-133(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-134(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-135(LF) 2x30	ND	↑	3.760/95.50	2.900/73.66	3.220/81.79	↑	3.36/85.3	↑	D
-136(LF) 2x5	STD	↑	1.260/32.00	.400/10.16	.780/18.29	↑	.86/21.8	↑	A
-137(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.980/23.37	↑	1.06/26.9	↑	C
-138(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-139(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-140(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-141(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-142(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-143(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
65823-144(LF) 2x30	STD	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30µ"/.76µ GXT/GOLD FLASH	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER		FCJ	
ltr	ecn no	dr	date	COPY		www.fcjconnect.com	
AF				projection		title	
				.XX±.01/.X±.3		HEADER, QUICKIE	
				.XXX±.005/.XX±.13		SEA, HORSE, RIGHT ANGLE	
				.XXXX±.0020/.XXX±.051		product family QUICKIE	
				0'±2'		size dwg no	
				dr J. SHREINER		code	
				enfr M. SMYK		65823	
				chr M. SMYK		sheet	
				appd M. SMYK		7 of 21	
sheet	revision			scale			
21	index			5:1			

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-145 <LF> 2x5	LP	RND	1. 260/32.00	. 400/10.16	. 720/18.29	. 105/2.67	. 86/21.8	30u" / .76u Au DVER 50u" / .1.27u Ni 150u" / .3.81u Sn	A
-146 <LF>		SQ				. 105/2.67			
-147 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-148 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-149 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
-150 <LF> 2x5		SQ	1. 260/32.00	. 400/10.16	. 720/18.29	. 675/17.15	. 86/21.8	150u" / .3.81u Sn	A
-151 <LF> 2x7		RND	1. 460/37.08	. 600/15.24	. 920/23.37	. 105/2.67	1. 06/26.9	30u" / .76u Au DVER 50u" / .1.27u Ni	C
-152 <LF>		SQ				. 105/2.67		150u" / .3.81u Sn	
-153 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-154 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-155 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
-156 <LF> 2x7		SQ	1. 460/37.08	. 600/15.24	. 920/23.37	. 675/17.15	1. 06/26.9	150u" / .3.81u Sn	C
-157 <LF> 2x8		RND	1. 560/39.62	. 700/17.78	1. 020/25.91	. 105/2.67	1. 16/29.4	30u" / .76u Au DVER 50u" / .1.27u Ni	D
-158 <LF>		SQ				. 105/2.67		150u" / .3.81u Sn	
-159 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-160 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-161 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
-162 <LF> 2x8		SQ	1. 560/39.62	. 700/17.78	1. 020/25.91	. 675/17.15	1. 16/29.4	150u" / .3.81u Sn	
-163 <LF> 2x10		RND	1. 760/44.70	. 900/22.86	1. 220/30.99	. 105/2.67	1. 36/34.5	30u" / .76u Au DVER 50u" / .1.27u Ni	
-164 <LF>		SQ				. 105/2.67		150u" / .3.81u Sn	
-165 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-166 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-167 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
-168 <LF> 2x10		SQ	1. 760/44.70	. 900/22.86	1. 220/30.99	. 675/17.15	1. 36/34.5	150u" / .3.81u Sn	
-169 <LF> 2x13		RND	2. 060/52.32	1. 200/30.48	1. 520/38.61	. 105/2.67	1. 66/42.1	30u" / .76u Au DVER 50u" / .1.27u Ni	
-170 <LF>		SQ				. 105/2.67		150u" / .3.81u Sn	
-171 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-172 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-173 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
-174 <LF> 2x13		SQ	2. 060/52.32	1. 200/30.48	1. 520/38.61	. 675/17.15	1. 66/42.1	150u" / .3.81u Sn	
-175 <LF> 2x17		RND	2. 460/62.48	1. 600/40.64	1. 920/48.77	. 105/2.67	2. 06/52.3	30u" / .76u Au DVER 50u" / .1.27u Ni	
-176 <LF>		SQ				. 105/2.67		150u" / .3.81u Sn	
-177 <LF>		RND				. 150/3.81		30u" / .76u Au DVER 50u" / .1.27u Ni	
-178 <LF>		SQ				. 150/3.81		150u" / .3.81u Sn	
-179 <LF>		SQ				. 675/17.15		30u" / .76u Au DVER 50u" / .1.27u Ni	
65823-180 <LF> 2x17	LP	SQ	2. 460/62.48	1. 600/40.64	1. 920/48.77	. 675/17.15	2. 06/52.3	150u" / .3.81u Sn	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FGI	
ltr	ecn no	dr	date	projection	title	product family	code
AF				linear	HEADER, QUICKIE	QUICKIE	
				angles	SEA, HORSE, RIGHT ANGLE	size dwg no	
				dr			
				engr			
				chr			
				appd			
sheet	revision			INCH/MM	scale		
21	index			5:1		65823	8 of 21



www.fcconnect.com  
 title HEADER, QUICKIE  
 product family QUICKIE  
 size dwg no  
 code  
 sheet 8 of 21

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-181(LF) 2x20	LP	RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u" / .76u DVER 50u" / 1.27u NI	D
-182(LF)	↑	SQ	↑	↑	↑	.105/2.67	↑	150u" / 3.81u Sn	↑
-183(LF)	↑	RND	↑	↑	↑	.150/3.81	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-184(LF)	↑	SQ	↑	↑	↑	.150/3.81	↑	150u" / 3.81u Sn	↑
-185(LF)	↑	SQ	↑	↑	↑	.675/17.15	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-186(LF) 2x20	SQ	SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u" / 3.81u Sn	↑
-187(LF) 2x25	RND	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u DVER 50u" / 1.27u NI	↑
-188(LF)	↑	SQ	↑	↑	↑	.105/2.67	↑	150u" / 3.81u Sn	↑
-189(LF)	↑	RND	↑	↑	↑	.150/3.81	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-190(LF)	↑	SQ	↑	↑	↑	.150/3.81	↑	150u" / 3.81u Sn	↑
-191(LF)	↑	SQ	↑	↑	↑	.675/17.15	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-192(LF) 2x25	SQ	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u" / 3.81u Sn	↑
-193(LF) 2x30	RND	RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u DVER 50u" / 1.27u NI	↑
-194(LF)	↑	SQ	↑	↑	↑	.105/2.67	↑	150u" / 3.81u Sn	↑
-195(LF)	↑	RND	↑	↑	↑	.150/3.81	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-196(LF)	↑	SQ	↑	↑	↑	.150/3.81	↑	150u" / 3.81u Sn	↑
-197(LF)	↑	SQ	↑	↑	↑	.675/17.15	↑	30u" / .76u DVER 50u" / 1.27u NI	↑
-198(LF) 2x30	↑	↑	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	150u" / 3.81u Sn	D
-199(LF) 2x5	↑	↑	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76u DVER 50u" / 1.27u NI	A
-200(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-201(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-202(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-203(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-204(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-205(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-206(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-207(LF) 2x30	SQ	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u DVER 50u" / 1.27u NI	D
-208(LF) 2x5	RND	RND	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	30u" / .76u GXT/GOLD FLASH	A
-209(LF) 2x7	↑	↑	1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-210(LF) 2x8	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-211(LF) 2x10	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-212(LF) 2x13	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-213(LF) 2x17	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-214(LF) 2x20	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-215(LF) 2x25	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
65823-216(LF) 2x30	LP	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u" / .76u GXT/GOLD FLASH	D

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FQJ	
ltr	ecn no	dr	date	linear	angles	dr	engr	chr	appd	projection	title
AF				.XX±.01/.X±.3	0°±2'	J. SHREINER	M. SMYK	M. SMYK	M. SMYK	INCH/MM	HEADER, QUICKIE
				.XXX±.005/.XX±.13						SEA, HORSE, RIGHT ANGLE	product family QUICKIE
				.XXX±.0020/.XX±.051						code	code
										size/dwg no	size/dwg no
										scale	scale
										5:1	5:1
											A
											65823
											sheet
											9 of 21
21	index	sheet	revision								



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
55823-217(LF)	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30ur / .76u GXT/GOLD FLASH	A
-218(LF)	↑	↑	1.460/37.08	.600/15.24	.950/23.37	↑	1.06/26.9	↑	C
-219(LF)	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-220(LF)	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-221(LF)	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-222(LF)	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-223(LF)	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-224(LF)	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-225(LF)	↑	↑	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	↑	D
-226(LF)	↑	↑	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	↑	A
-227(LF)	↑	↑	1.460/37.08	.600/15.24	.950/23.37	↑	1.06/26.9	↑	C
-228(LF)	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-229(LF)	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-230(LF)	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-231(LF)	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-232(LF)	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-233(LF)	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-234(LF)	↑	↑	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	↑	D
-235(LF)	↑	↑	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	↑	A
-236(LF)	↑	↑	1.460/37.08	.600/15.24	.950/23.37	↑	1.06/26.9	↑	C
-237(LF)	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-238(LF)	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-239(LF)	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-240(LF)	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-241(LF)	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-242(LF)	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-243(LF)	↑	↑	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	↑	D
-244(LF)	↑	↑	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	↑	A
-245(LF)	↑	↑	1.460/37.08	.600/15.24	.950/23.37	↑	1.06/26.9	↑	C
-246(LF)	↑	↑	1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-247(LF)	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-248(LF)	↑	↑	2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-249(LF)	↑	↑	2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-250(LF)	↑	↑	2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-251(LF)	↑	↑	3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
55823-252(LF)	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30ur / .76u GXT/GOLD FLASH	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCJ	
ltr	ecn no	dr	date	linear	projection	product family	code
AF				.XX±.01/.X±.3	⊕	QUICKIE	—
				.XXX±.005/.XX±.13		SEA, HORSE, RIGHT ANGLE	sheet 10 of 21
				.XXX±.0020/.XX±.051		QUICKIE	—
				0'±2'		size	65823
				J. SHREINER	1/16/90	scale	5:1
				M. SMYK	1/16/90		
				M. SMYK	1/16/90		
				M. SMYK	1/16/90		
sheet	revision	sheet					
21							
index							

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-253(LF) 2x5	RND		1.260/32.00	.400/10.16	.780/18.29	.105/2.67	.86/21.8	30u" / .76u GXT/GOLD FLASH	A
-254(LF) 2x7			1.460/37.08	.600/15.24	.950/23.37		1.06/26.9		C
-255(LF) 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-256(LF) 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-257(LF) 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-258(LF) 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-259(LF) 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-260(LF) 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-261(LF) 2x30	RND		3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-262(LF) 2x5	SQ		1.260/32.00	.400/10.16	.780/18.29	.675/17.15	.86/21.8		A
-263(LF) 2x7			1.460/37.08	.600/15.24	.950/23.37		1.06/26.9		C
-264(LF) 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-265(LF) 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-266(LF) 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-267(LF) 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-268(LF) 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-269(LF) 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-270(LF) 2x30	LP		3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	30u" / .76u GXT/GOLD FLASH	D
-271(LF) 2x5	NO		1.260/32.00	.400/10.16	.780/18.29	.105/2.67	.86/21.8	15u" / .38u Au OVER 50u" / .1.27u Ni	A
-272(LF) 2x7			1.460/37.08	.600/15.24	.950/23.37		1.06/26.9		C
-273(LF) 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-274(LF) 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-275(LF) 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-276(LF) 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-277(LF) 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-278(LF) 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-279(LF) 2x30			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-280(LF) 2x5			1.260/32.00	.400/10.16	.780/18.29	.150/3.81	.86/21.8		A
-281(LF) 2x7			1.460/37.08	.600/15.24	.950/23.37		1.06/26.9		C
-282(LF) 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-283(LF) 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-284(LF) 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-285(LF) 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-286(LF) 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-287(LF) 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-288(LF) 2x30	NO		3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	15u" / .38u Au OVER 50u" / .1.27u Ni	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER	FCI	
ltr	ecn no	dr	date	COPY	www.fciconnect.com	
AF				projection		
						title
				linear		HEADER, QUICKIE
				angles		SEA, HORSE, RIGHT ANGLE
				dr		product family
				engr		QUICKIE
				chr		size
				appd		dwg no
						A
						65823
						code
						sheet
						11 of 21
21	sheet	revision				
index	sheet					

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
-290<LF> 2x5	NO	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u". 38u Au OVER 50u" /1. 27u Ni	A
-290<LF> 2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-291<LF> 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-292<LF> 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-293<LF> 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-294<LF> 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-295<LF> 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-296<LF> 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-297<LF> 2x30	NO	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-298<LF> 2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A
-299<LF> 2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-300<LF> 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-301<LF> 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-302<LF> 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-303<LF> 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-304<LF> 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-305<LF> 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-306<LF> 2x30			3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3		D
-307<LF> 2x5			1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8		A
-308<LF> 2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-309<LF> 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-310<LF> 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-311<LF> 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-312<LF> 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-313<LF> 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-314<LF> 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-315<LF> 2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-316<LF> 2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A
-317<LF> 2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-318<LF> 2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-319<LF> 2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-320<LF> 2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-311<LF> 2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-312<LF> 2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-313<LF> 2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-313<LF> 2x30		STD	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	15u". 38u Au OVER 50u" /1. 27u Ni	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	projection	product family	code
AF				.XX±.01/.X±.3	projection	QUICKIE	—
				.XXX±.005/.XX±.13	⊕	SEA, HORSE, RIGHT ANGLE	sheet 12 of 21
				.XXXX±.0020/.XXX±.051		product family QUICKIE	
				0'±2'		size dwg no	
				dr J. SHREINER	INCH/MM	A	65823
				enfr M. SMYK	scale		
				chr M. SMYK	5:1		
				appd M. SMYK			
sheet	revision						
21	index						

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-325 <LF> 2x5	LP	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u" / .38u Au DVER 50u" / 1.27u Ni	A
↑	↑	↑	1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-326 <LF> 2x7			1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-327 <LF> 2x8			1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-328 <LF> 2x10			2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-329 <LF> 2x13			2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-330 <LF> 2x17			2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-331 <LF> 2x20			3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-332 <LF> 2x25			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	↑	D
-333 <LF> 2x30			1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	↑	A
↑	↑	↑	1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-334 <LF> 2x5			1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-335 <LF> 2x7			1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-336 <LF> 2x8			2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-337 <LF> 2x10			2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-338 <LF> 2x13			2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-339 <LF> 2x17			3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-340 <LF> 2x20			3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	↑	D
-341 <LF> 2x25			1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	↑	A
↑	↑	↑	1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-342 <LF> 2x30			1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
-343 <LF> 2x5			1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-344 <LF> 2x7			2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-345 <LF> 2x8			2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-346 <LF> 2x10			2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-347 <LF> 2x13			3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-348 <LF> 2x17			3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3	15u" / .38u Au DVER 50u" / 1.27u Ni	↑
-349 <LF> 2x20			3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u Au DVER 50u" / 1.27u Ni	D
-350 <LF> 2x25			1.460/37.08	.600/15.24	.920/23.37	↑	1.06/26.9	↑	C
-351 <LF> 2x30			1.560/39.62	.700/17.78	1.020/25.91	↑	1.16/29.4	↑	D
↑	↑	↑	1.760/44.70	.900/22.86	1.220/30.99	↑	1.36/34.5	↑	↑
-352 <LF> 2x5			2.060/52.32	1.200/30.48	1.520/38.61	↑	1.66/42.1	↑	↑
-353 <LF> 2x7			2.460/62.48	1.600/40.64	1.920/48.77	↑	2.06/52.3	↑	↑
-354 <LF> 2x8			2.760/70.10	1.900/48.26	2.220/56.39	↑	2.36/59.9	↑	↑
-355 <LF> 2x10			3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-356 <LF> 2x13			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u Au DVER 50u" / 1.27u Ni	↑
-357 <LF> 2x17			3.260/82.80	2.400/60.96	2.720/69.09	↑	2.86/72.6	↑	↑
-358 <LF> 2x20			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u Au DVER 50u" / 1.27u Ni	D
-359 <LF> 2x25			↑	↑	↑	↑	↑	↑	↑
↑	↑	↑	↑	↑	↑	↑	↑	↑	↑
65823-360 <LF> 2x30			3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u Au DVER 50u" / 1.27u Ni	D

\*CUSTOMER SPECIAL

		CUSTOMER COPY		tolerances unless otherwise specified		mat'l. code		www.fciconnect.com	
title		projection		linear		dr		date	
SEA, HORSE, RIGHT ANGLE		⊕		.XX±.01/.X±.3		J. SHREINER			
product family		INCH/MM		.XXX±.005/.XX±.13		M. SMYK		1/16/90	
QUICKIE		scale		.XXXX±.0020/.XXX±.051		chr		1/16/90	
size		5:1		0'±2'		M. SMYK		1/16/90	
dwg no		A		↑		appd		↑	
code		65823		↑		sheet		↑	
sheet		13 of 21		↑		revision		↑	
13 of 21		↑		↑		sheet		↑	
↑		↑		↑		index		↑	

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-361<LF> 2x5	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76u Au DVER 50u" / 1.27u NI	A
-362<LF>	ND	RND						30u" / .76u Au DVER 50u" / 1.27u NI	B
-363<LF>	ND	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-364<LF>	ND	RND						30u" / .76u GXT/GOLD FLASH	
-365<LF>	ND	SQ						150u" / 3.81u Sn	
-366<LF>	STD	RND						30u" / .76u Au DVER 50u" / 1.27u NI	
-367<LF>	STD	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-368<LF>	STD	RND						30u" / .76u GXT/GOLD FLASH	
-369<LF>	STD	SQ						150u" / 3.81u Sn	
-370<LF>	LP	RND						30u" / .76u Au DVER 50u" / 1.27u NI	
-371<LF>	LP	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-372<LF>	LP	RND						30u" / .76u GXT/GOLD FLASH	
-373<LF>	LP	SQ				.105/2.67		150u" / 3.81u Sn	
-374<LF>	ND	RND				.150/3.81		30u" / .76u Au DVER 50u" / 1.27u NI	
-375<LF>	ND	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-376<LF>	ND	RND						30u" / .76u GXT/GOLD FLASH	
-377<LF>	ND	SQ						150u" / 3.81u Sn	
-378<LF>	STD	RND						30u" / .76u Au DVER 50u" / 1.27u NI	
-379<LF>	STD	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-380<LF>	STD	RND						30u" / .76u GXT/GOLD FLASH	
-381<LF>	STD	SQ						150u" / 3.81u Sn	
-382<LF>	LP	RND						30u" / .76u Au DVER 50u" / 1.27u NI	
-383<LF>	LP	RND						15' / .38u Au DVER 50u" / 1.27u NI	
-384<LF>	LP	RND						30u" / .76u GXT/GOLD FLASH	
-385<LF>	LP	SQ				.150/3.81		150u" / 3.81u Sn	
-386<LF>	ND	SQ				.675/17.15		30u" / .76u Au DVER 50u" / 1.27u NI	
-387<LF>	ND							15' / .38u Au DVER 50u" / 1.27u NI	
-388<LF>	ND							30u" / .76u GXT/GOLD FLASH	
-389<LF>	ND							150u" / 3.81u Sn	
-390<LF>	STD							30u" / .76u Au DVER 50u" / 1.27u NI	
-391<LF>	STD							15' / .38u Au DVER 50u" / 1.27u NI	
-392<LF>	STD							30u" / .76u GXT/GOLD FLASH	
-393<LF>	STD							150u" / 3.81u Sn	
-394<LF>	LP							30u" / .76u Au DVER 50u" / 1.27u NI	
-395<LF>	LP							15' / .38u Au DVER 50u" / 1.27u NI	
65823-396<LF> 2x5	LP	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	30u" / .76u GXT/GOLD FLASH	B

\*CUSTOMER SPECIAL

<b>FCI</b>		<b>CUSTOMER COPY</b>		tolerances unless otherwise specified	
www.fciconnect.com		projection		.XX±.01 / .X±.3	
title <b>HEADER, QUICKIE</b>		INCH/MM		.XXX±.005 / .XX±.13	
SEA, HORSE, RIGHT ANGLE		scale		.XXX±.0020 / .XXX±.051	
product family <b>QUICKIE</b>		5:1		0°±2'	
size dwg no <b>65823</b>		code		J. SHREINER 1/16/90	
A		sheet		M. SMYK 1/16/90	
		1 of 21		chr M. SMYK 1/16/90	
				appd M. SMYK 1/16/90	
sheet		revision			
index		sheet			



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-397(LF)	2x5	LP	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/.3.81u Sn	B
-398(LF)	2x10	66258-001	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.75u Au DVER 50u"/1.27u Ni	D
-399(LF)	2x5	NO	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u"/.38u Au DVER 50u"/1.27u Ni	A
-400(LF)		STD				.105/2.67			
-401(LF)		LP				.105/2.67			
-402(LF)		NO				.150/3.81			
-403(LF)		STD				.150/3.81			
-404(LF)		LP				.150/3.81			A
-405(LF)		NO				.105/2.67			B
-406(LF)		STD				.105/2.67			
-407(LF)		LP				.105/2.67			
-408(LF)		NO				.150/3.81			
-409(LF)		STD				.150/3.81			
-410(LF)	2x5	LP	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		B
-411(LF)	2x7	NO	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9		C
-412(LF)		STD				.105/2.67			
-413(LF)		LP				.105/2.67			
-414(LF)		NO				.150/3.81			
-415(LF)		STD				.150/3.81			
-416(LF)	2x7	LP	1.460/37.08	.600/15.24	.920/23.37	.150/3.81	1.06/26.9		C
-417(LF)	2x8	NO	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4		D
-418(LF)		STD				.105/2.67			
-419(LF)		LP				.105/2.67			
-420(LF)		NO				.150/3.81			
-421(LF)		STD				.150/3.81			
-422(LF)	2x8	LP	1.560/39.62	.700/17.78	1.020/25.91	.150/3.81	1.16/29.4		
-423(LF)	2x10	NO	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5		
-424(LF)		STD				.105/2.67			
-425(LF)		LP				.105/2.67			
-426(LF)		NO				.150/3.81			
-427(LF)		STD				.150/3.81			
-428(LF)	2x10	LP	1.760/44.70	.900/22.86	1.220/30.99	.150/3.81	1.36/34.5		
-429(LF)	2x13	NO	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1		
-430(LF)		STD				.105/2.67			
-431(LF)		LP				.105/2.67			
65823-432(LF)	2x13	NO	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u"/.38u Au DVER 50u"/1.27u Ni	D

		www.fciconnect.com	
CUSTOMER	FCI	CUSTOMER	FCI
COPY	COPY	projection	projection
tolerances unless otherwise specified	.XX±.01/.X±.3 .XXX±.005/.XX±.13 .XXXX±.0020/.XXX±.051	angles	0°±2'
mat'l. code	AF	dr	J. SHREINER 1/16/90
itr	AF	engr	M. SMYK 1/16/90
date		chr	M. SMYK 1/16/90
scale		appd	M. SMYK 1/16/90
revision		sheet	21
sheet		index	2

product family	QUICKIE	code	
size	dwg no	sheet	15 of 21
INCH/MM	5:1		
65823	A		
HEADER, QUICKIE	SEA, HORSE, RIGHT ANGLE		

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-433(LF)	STD	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u" / .38u Au DVER 50u" / 1.27u Ni	D
-434(LF)	LP		2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1		
-435(LF)	ND		2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3		
-436(LF)	STD					.105/2.67			
-437(LF)	LP					.105/2.67			
-438(LF)	ND					.150/3.81			
-439(LF)	STD					.150/3.81			
-440(LF)	LP		2.460/62.48	1.600/40.64	1.920/48.77	.150/3.81	2.06/52.3		
-441(LF)	ND		2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9		
-442(LF)	STD					.105/2.67			
-443(LF)	LP					.105/2.67			
-444(LF)	ND					.150/3.81			
-445(LF)	STD					.150/3.81			
-446(LF)	LP		2.760/70.10	1.900/48.26	2.220/56.39	.150/3.81	2.36/59.9		
-447(LF)	ND		3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6		
-448(LF)	STD					.105/2.67			
-449(LF)	LP					.105/2.67			
-450(LF)	ND					.150/3.81			
-451(LF)	STD					.150/3.81			
-452(LF)	LP		3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6		
-453(LF)	ND		3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		
-454(LF)	STD					.105/2.67			
-455(LF)	LP					.105/2.67			
-456(LF)	ND					.150/3.81			
-457(LF)	STD					.150/3.81			
-458(LF)	LP	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3		
-459(LF)	ND	RND	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6		
-460(LF)	STD								
-461(LF)	LP							15u" / .38u Au DVER 50u" / 1.27u Ni	
-462(LF)	ND							30u" / .76u Au DVER 50u" / 1.27u Ni	
-463(LF)	STD							30u" / .76u Au DVER 50u" / 1.27u Ni	
-464(LF)	LP							30u" / .76u Au DVER 50u" / 1.27u Ni	
-465(LF)	ND							30u" / .76u GXT/GOLD FLASH	
-466(LF)	STD							30u" / .76u GXT/GOLD FLASH	
-467(LF)	LP	RND						30u" / .76u GXT/GOLD FLASH	
65823-468(LF)	ND	SQ	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6	150u" / 3.81u Sn	D

		<b>CUSTOMER COPY</b>		tolerances unless otherwise specified		www.fciconnect.com	
mat'l. code	AF	itr	ecn no	dr	date	linear	.XX±.01/.X±.3
						angles	.XXX±.005/.XX±.13
						dr	.XXXX±.0020/.XXX±.051
						engr	0"±2"
						chr	J. SHREINER 1/16/90
						appd	M. SMYK 1/16/90
						sheet	M. SMYK 1/16/90
						index	M. SMYK 1/16/90
						revision	
						sheet	
						scale	5:1
						product family	QUICKIE
						size/dwg no	A
						code	65823
						sheet	16 of 21

**FCI**  
**HEADER, QUICKIE**  
**SEA, HORSE, RIGHT ANGLE**

projection

INCH/MM

scale 5:1

product family QUICKIE


size/dwg no A

code 65823

sheet 16 of 21


SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-469(LF)	STD	SQ	1. 960/49.80	1. 100/27.94	1. 420/36.07	. 105/2. 67	1. 56/39. 62	150u"/3. 81u TIN	D
-470(LF)	LP	SQ				. 105/2. 67		150u"/3. 81u TIN	
-471(LF)	ND	RND				. 150/3. 81		15u"/. 38u Au DVER 50u"/1. 27u NI	
-472(LF)	STD							15u"/. 38u Au DVER 50u"/1. 27u NI	
-473(LF)	LP							15u"/. 38u Au DVER 50u"/1. 27u NI	
-474(LF)	ND							30u"/. 76u Au DVER 50u"/1. 27u NI	
-475(LF)	STD							30u"/. 76u Au DVER 50u"/1. 27u NI	
-476(LF)	LP							30u"/. 76u Au DVER 50u"/1. 27u NI	
-477(LF)	ND							30u"/. 76u GXT/GOLD FLASH	
-478(LF)	STD							30u"/. 76u GXT/GOLD FLASH	
-479(LF)	LP	RND						30u"/. 76u GXT/GOLD FLASH	
-480(LF)	ND	SQ						150u"/3. 81u TIN	
-481(LF)	STD							150u"/3. 81u TIN	
-482(LF)	LP				. 150/3. 81			150u"/3. 81u TIN	
-483(LF)	ND				. 105/2. 67			15u"/. 38u Au DVER 50u"/1. 27u NI	
-484(LF)	STD							15u"/. 38u Au DVER 50u"/1. 27u NI	
-485(LF)	LP							15u"/. 38u Au DVER 50u"/1. 27u NI	
-486(LF)	ND							30u"/. 76u Au DVER 50u"/1. 27u NI	
-487(LF)	STD							30u"/. 76u Au DVER 50u"/1. 27u NI	
-488(LF)	LP							30u"/. 76u Au DVER 50u"/1. 27u NI	
-489(LF)	ND							15u"/. 38u Au DVER 50u"/1. 27u NI	
-490(LF)	STD							15u"/. 38u Au DVER 50u"/1. 27u NI	
-491(LF)	LP				. 105/2. 67			15u"/. 38u Au DVER 50u"/1. 27u NI	
-492(LF)	ND				. 675/17. 15			15u"/. 38u Au DVER 50u"/1. 27u NI	
-493(LF)	STD							15u"/. 38u Au DVER 50u"/1. 27u NI	
-494(LF)	LP							15u"/. 38u Au DVER 50u"/1. 27u NI	
-495(LF)	ND							30u"/. 76u Au DVER 50u"/1. 27u NI	
-496(LF)	STD							30u"/. 76u Au DVER 50u"/1. 27u NI	
-497(LF)	LP							30u"/. 76u Au DVER 50u"/1. 27u NI	
-498(LF)	ND							30u"/. 76u GXT/GOLD FLASH	
-499(LF)	STD							30u"/. 76u GXT/GOLD FLASH	
-500(LF)	LP							30u"/. 76u GXT/GOLD FLASH	
-501(LF)	ND							150u"/3. 81u TIN	
-502(LF)	STD							150u"/3. 81u TIN	
-503(LF)	LP	SQ	1. 960/49.80	1. 100/27.94	1. 420/36.07	. 675/17. 15	1. 56/39. 62	150u"/3. 81u TIN	
65823-504(LF)	ND	RND	2. 260/57.40	1. 400/35.56	1. 720/43.69	. 105/2. 67	1. 86/47. 24	15u"/. 38u Au DVER 50u"/1. 27u NI	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY	
ltr	ecn no	dr	date	projection	www.fciconnect.com
AF				0°±2'	title
				J. SHREINER	SEA, HORSE, RIGHT ANGLE
				M. SMYK	product family
				M. SMYK	size
				M. SMYK	dwg no
sheet	revision			scale	code
21	index			5:1	A
					65823
					17 of 21



**FCI**  
 HEADER, QUICKIE  
 SEA, HORSE, RIGHT ANGLE  
 product family QUICKIE  
 size dwg no A 65823  
 code -  
 sheet 17 of 21

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-505(LF)	STD	RND	2.260/57.40	1.400/35.56	1.720/43.69	.105/2.67	1.86/47.2	15u"/.38u Au DVER 50u"/1.27u Ni	D
-506(LF)	LP							15u"/.38u Au DVER 50u"/1.27u Ni	
-507(LF)	ND							30u"/.76u Au DVER 50u"/1.27u Ni	
-508(LF)	STD							30u"/.76u Au DVER 50u"/1.27u Ni	
-509(LF)	LP							30u"/.76u Au DVER 50u"/1.27u Ni	
-510(LF)	ND							30u"/.76u Au DVER 50u"/1.27u Ni	
-511(LF)	STD							30u"/.76u GXT GOLD FLASH	
-512(LF)	LP	RND						30u"/.76u GXT GOLD FLASH	
-513(LF)	ND	SQ						150u"/3.81u TIN	
-514(LF)	STD	SQ						150u"/3.81u TIN	
-515(LF)	LP	SQ			.105/2.67			150u"/3.81u TIN	
-516(LF)	ND	RND			.150/3.81			15u"/.38u Au DVER 50u"/1.27u Ni	
-517(LF)	STD							15u"/.38u Au DVER 50u"/1.27u Ni	
-518(LF)	LP							15u"/.38u Au DVER 50u"/1.27u Ni	
-519(LF)	ND							30u"/.76u Au DVER 50u"/1.27u Ni	
-520(LF)	STD							30u"/.76u Au DVER 50u"/1.27u Ni	
-521(LF)	LP							30u"/.76u Au DVER 50u"/1.27u Ni	
-522(LF)	ND							30u"/.76u GXT GOLD FLASH	
-523(LF)	STD							30u"/.76u GXT GOLD FLASH	
-524(LF)	LP	RND						30u"/.76u GXT GOLD FLASH	
-525(LF)	ND	SQ						150u"/3.81u TIN	
-526(LF)	STD							150u"/3.81u TIN	
-527(LF)	LP				.150/3.81			150u"/3.81u TIN	
-528(LF)	ND				.105/2.67			15u"/.38u Au DVER 50u"/1.27u Ni	
-529(LF)	STD							15u"/.38u Au DVER 50u"/1.27u Ni	
-530(LF)	LP							15u"/.38u Au DVER 50u"/1.27u Ni	
-531(LF)	ND							30u"/.76u Au DVER 50u"/1.27u Ni	
-532(LF)	STD							30u"/.76u Au DVER 50u"/1.27u Ni	
-533(LF)	LP				.105/2.67			30u"/.76u Au DVER 50u"/1.27u Ni	
-534(LF)	ND				.150/3.81			15u"/.38u Au DVER 50u"/1.27u Ni	
-535(LF)	STD				.150/3.81			15u"/.38u Au DVER 50u"/1.27u Ni	
-536(LF)	LP				.150/3.81			15u"/.38u Au DVER 50u"/1.27u Ni	
-537(LF)	ND				.675/17.15			15u"/.38u Au DVER 50u"/1.27u Ni	
-538(LF)	STD							15u"/.38u Au DVER 50u"/1.27u Ni	
-539(LF)	LP							15u"/.38u Au DVER 50u"/1.27u Ni	
65823-540(LF)	ND	SQ	2.260/57.40	1.400/35.56	1.720/43.69	.675/17.15	1.86/47.2	30u"/.76u Au DVER 50u"/1.27u Ni	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	projection	title	code
AF				.XX±.01/.X±.3	⊕	HEADER, QUICKIE	—
				.XXX±.005/.XX±.13		SEA, HORSE, RIGHT ANGLE	sheet
				.XXXX±.0020/.XXX±.051		product family QUICKIE	18 of 21
				0'±2'		size dwg no	
				J. SHREINER	1/16/90	A	65823
				M. SMYK	1/16/90		
				chr	1/16/90		
				appd	1/16/90		
sheet	revision						
21	index						

SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-541(LF)	STD	SQ	2. 260/57. 40	1. 400/35. 56	1. 720/48L69	. 675/17. 15	1. 86/47. 2	30u" / .76u Au DVER 50u" / .1. 27u Ni	D
-542(LF)	LP							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-543(LF)	ND							30u" / .76u GXT/GOLD FLASH	
-544(LF)	STD							30u" / .76u GXT/GOLD FLASH	
-545(LF)	LP							30u" / .76u GXT/GOLD FLASH	
-546(LF)	ND							150u" / .3. 81u TIN	
-547(LF)	STD							150u" / .3. 81u TIN	
-548(LF)	LP	SQ	2. 260/57. 40	1. 400/35. 56	1. 720/43. 69	. 675/17. 15	1. 86/47. 2	15u" / .38u Au DVER 50u" / .1. 27u Ni	
-549(LF)	ND	RND	2. 960/75. 20	2. 100/53. 34	2. 420/61. 47	. 105/2. 67	2. 56/65. 0	15u" / .38u Au DVER 50u" / .1. 27u Ni	
-550(LF)	STD							15u" / .38u Au DVER 50u" / .1. 27u Ni	
-551(LF)	LP							15u" / .38u Au DVER 50u" / .1. 27u Ni	
-552(LF)	ND							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-553(LF)	STD							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-554(LF)	LP							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-555(LF)	ND							30u" / .76u GXT/GOLD FLASH	
-556(LF)	STD							30u" / .76u GXT/GOLD FLASH	
-557(LF)	LP	RND						30u" / .76u GXT/GOLD FLASH	
-558(LF)	ND	SQ						150u" / .3. 81u TIN	
-559(LF)	STD	SQ						150u" / .3. 81u TIN	
-560(LF)	LP	SQ				. 105/2. 67		150u" / .3. 81u TIN	
-561(LF)	ND	RND				. 150/3. 81		15u" / .38u Au DVER 50u" / .1. 27u Ni	
-562(LF)	STD							15u" / .38u Au DVER 50u" / .1. 27u Ni	
-563(LF)	LP							15u" / .38u Au DVER 50u" / .1. 27u Ni	
-564(LF)	ND							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-565(LF)	STD							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-566(LF)	LP							30u" / .76u Au DVER 50u" / .1. 27u Ni	
-567(LF)	ND							30u" / .76u GXT/GOLD FLASH	
-568(LF)	STD							30u" / .76u GXT/GOLD FLASH	
-569(LF)	LP	RND						30u" / .76u GXT/GOLD FLASH	
-570(LF)	ND	SQ						150u" / .3. 81u TIN	
-571(LF)	STD							150u" / .3. 81u TIN	
-572(LF)	LP					. 150/3. 81		150u" / .3. 81u TIN	
-573(LF)	ND					. 105/2. 67		15u" / .38u Au DVER 50u" / .1. 27u Ni	
-574(LF)	STD							15u" / .38u Au DVER 50u" / .1. 27u Ni	
-575(LF)	LP							15u" / .38u Au DVER 50u" / .1. 27u Ni	
65823-576(LF)	ND	SQ	2. 960/75. 20	2. 100/53. 34	2. 420/61. 47	. 105/2. 67	2. 56/65. 0	30u" / .76u Au DVER 50u" / .1. 27u Ni	D

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCG	
ltr	ecn no	dr	date	projection	title	product family	code
AF				linear	HEADER, QUICKIE	SEA, HORSE, RIGHT ANGLE	—
				angles	QUICKIE	size/dwg no	—
				dr	J. SHREINER	1/16/90	—
				engr	M. SMYK	1/16/90	—
				chr	M. SMYK	1/16/90	—
				appd	M. SMYK	1/16/90	—
sheet	revision			INCH/MM	scale	5:1	A
21	index						65823
							19 of 21



www.fcconnect.com  
 title HEADER, QUICKIE  
 product family QUICKIE  
 size/dwg no  
 code  
 sheet 19 of 21



SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-577(LF)	STD	SQ	2.960/75.18	2.100/53.34	2.420/61.47	.105/2.67	2.56/65.0	30u" / .76u Au DVER 50u" / .1.27u Ni	D
-578(LF)	LP					.105/2.67		30u" / .76u Au DVER 50u" / .1.27u Ni	
-579(LF)	ND					.150/3.81		15u" / .38u Au DVER 50u" / .1.27u Ni	
-580(LF)	STD					.150/3.81		15u" / .38u Au DVER 50u" / .1.27u Ni	
-581(LF)	LP					.150/3.81		15u" / .38u Au DVER 50u" / .1.27u Ni	
-582(LF)	ND					.675/17.15		15u" / .38u Au DVER 50u" / .1.27u Ni	
-583(LF)	STD							15u" / .38u Au DVER 50u" / .1.27u Ni	
-584(LF)	LP							15u" / .38u Au DVER 50u" / .1.27u Ni	
-585(LF)	ND							30u" / .76u Au DVER 50u" / .1.27u Ni	
-586(LF)	STD							30u" / .76u Au DVER 50u" / .1.27u Ni	
-587(LF)	LP							30u" / .76u Au DVER 50u" / .1.27u Ni	
-588(LF)	ND							30u" / .76u GXT/GOLD FLASH	
-589(LF)	STD							30u" / .76u GXT/GOLD FLASH	
-590(LF)	LP							30u" / .76u GXT/GOLD FLASH	
-591(LF)	ND							150u" / .3.81u TIN	
-592(LF)	STD							150u" / .3.81u TIN	
-593(LF)	LP	SQ	2.960/75.18	2.100/53.34	2.420/61.47	.675/17.15	2.56/65.0	150u" / .3.81u TIN	
-594(LF)	66258	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u Au DVER 50u" / .1.27u Ni	
-595(LF)	66258	RND	3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6	30u" / .76u Au DVER 50u" / .1.27u Ni	
-596(LF)	STD	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u" / .1.27u Au DVER 50u" / .1.27u Ni	
-597(LF)	ND	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u GXT/GOLD FLASH	
-598(LF)	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u GXT/GOLD FLASH	
-599(LF)	LP	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u GXT/GOLD FLASH	
-600(LF)	ND	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u" / .1.27u Au DVER 50u" / .1.27u Ni	
-601(LF)	LP	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	50u" / .1.27u Au DVER 50u" / .1.27u Ni	
-606(LF)	STD	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u Au DVER 50u" / .1.27u Ni	
-607(LF)	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6	30u" / .76u Au DVER 50u" / .1.27u Ni	D
65823-608(LF)	STD	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u" / .76u GXT/GOLD FLASH	E

\* CUSTOMER SPECIAL

<b>FCI</b>		<b>CUSTOMER COPY</b>		<b>CUSTOMER COPY</b>	
www.fciconnect.com		projection		title	
HEADER, QUICKIE		SEA, HORSE, RIGHT ANGLE		product family QUICKIE	
code		INCH/MM		size/dwg no	
-		5:1		A	
sheet		scale		65823	
20 of 21		revision		sheet	
21		sheet		20 of 21	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

