



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

*how to purchase*

- [sales contacts](#)
- [stock check](#)

*search*

- [Product Line Search](#)

Please select a Product Line to search.

*Part # / Text Search*


Part No.:

Text Search:

- quick links*
- [Dialight Corporate Video](#)
  - [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. \*\*View PDF File\*\*](#)
  - [Application Notes](#)
  - [FAQs](#)
  - [Dialight Ltd \(UK\)](#)
  - [Dialight Garufo](#)
  - [Dialight BLP](#)
  - [LumiDrives](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# <b>5505405004F</b>	5 mm Lens Single Color
Description	5 mm Quad CBI
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Single Housing
Configuration	5 mm Lens
Lamp Type	Single Color
Viewing	Right Angle
Viewing Angle	50
Test Current (mA)	20mA
Forward Current (mA)	25mA
LED Centerline	<b>2.98</b>
Polarity	<b>Cathode Right</b>

Absolute Maximum Ratings (Ta = 25 °)	
Derating	<b>from 50Å° @ .5 mA/Å° C</b>
Solder Temp	<b>260Å° for 5 sec</b>
Operating Temp	<b>-25 to +85° C</b>
Storage Temp	<b>-30 to +100° C</b>



### Operating Characteristics

LED Position	1-4
Color	Amber
Lamp Type	Single Color
LED Type	Super Bright
Intensity Min (mcd)	17
Intensity Typ (mcd)	34.0
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	75
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

**Distributor Stock Check**

Check stock with our distributors now.