



Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes

FAQs

Dialight Ltd (UK)

Dialight Garufo

Dialight BLP

LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5530102004F

3 mm Lens

Description

Package Options

Product Type

Sub Product Type

Configuration

Viewing

Viewing Angle

Test Current (mA)

3 mm Bi-Level CBI

29 Pieces Per Tube

Through Hole Indicators

with Bi-Level Housing

3 mm Lens

Right Angle

45

10mA

Absolute Maximum Ratings

(Ta = 25 ° )

Solder Temp

Operating Temp

Storage Temp

260Å° for 5 sec

-25 to + 85° C

-30 to + 100° C

RoHS /pB Free

view PDF

Operating Characteristics

| LED Position               | Found in position(s): 1 | Found in position(s): 2 |
|----------------------------|-------------------------|-------------------------|
| Color                      | Blank                   | Green                   |
| Lamp Type                  | Single Color            | Single Color            |
| LED Type                   |                         | High Efficiency         |
| Intensity Min (mcd)        |                         | 5.6                     |
| Intensity Typ (mcd)        |                         | 16.0                    |
| Intensity Max (mcd)        |                         |                         |
| Fwd Voltage Min            |                         |                         |
| Fwd Voltage Typ            |                         |                         |
| Fwd Voltage Max            |                         |                         |
| Dom Wavelength Min (nm)    |                         |                         |
| Dom Wavelength Typ (nm)    |                         |                         |
| Dom Wavelength Max (nm)    |                         |                         |
| Power Dissipation Max (mW) |                         | 75                      |
| Backlighting               |                         |                         |
| Pitch Between Vertical     |                         |                         |
| Pitch Between Horizontal   |                         |                         |
| Lum Intensity Min          |                         |                         |
| Lum Intensity Typ          |                         |                         |
| Lum Intensity Max          |                         |                         |

Distributor Stock Check

Check stock with our distributors now.

5530102004F

check stock