




- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5530231010F	3 mm Lens
Description	3 mm Bi-Level CBI
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	2mA

Absolute Maximum Ratings (T _a = 25 °)	
Solder Temp	260Å° for 5 sec



Distributor Stock Check

Check stock with our distributors now.

5530231010F

[check stock](#)

- [how to purchase](#)
- [sales contacts](#)
- [stock check](#)

search

[Product Line Search](#)

Please select a Product Line to search.

[find](#)

Part # / Text Search

Part No.:

Text Search:

[search](#)

- [quick links](#)
- Dialight Corporate Video**
- [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. **View PDF File**](#)
- Application Notes**
- [FAQs](#)
- Dialight Ltd (UK)**
- Dialight Garufo**
- Dialight BLP**
- LumiDrives**

Operating Characteristics

	Found in position(s): 1	Found in position(s): 2
LED Position		
Color	Red	Yellow
Lamp Type	Single Color	Single Color
LED Type	Low Current	Low Current
Intensity Min (mcd)	1.0	2.3
Intensity Typ (mcd)	1.6	5.0
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	20	75
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		