



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# <b>56807411113F</b>	3 mm Lens
Description	3 mm Quad X 3 Backlighting R/G-R/G-R/G-R/G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260Å° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C

**Distributor Stock Check**

Check stock with our distributors now.

56807411113F

[check stock](#)

- how to purchase
- [sales contacts](#)
  - [stock check](#)



search

Product Line Search

Please select a Product Line to search.

[find](#)

### Operating Characteristics

LED Position	Found in position(s): 1-4
Color	Red / Green
Lamp Type	Bi-Color / Bi-Color
LED Type	
Intensity Min (mcd)	2.5 / 3.7
Intensity Typ (mcd)	4.7 / 10.0
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	621 / 569
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	100 / 100
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Part # / Text Search

Part No.:

Text Search:

[search](#)

- quick links

**Dialight Corporate Video**

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

**Application Notes**

[FAQs](#)

- [Dialight Ltd \(UK\)](#)
- [Dialight Garufo](#)
- [Dialight BLP](#)
- [LumiDrives](#)