



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

- how to purchase
 -  sales contacts
 -  stock check

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

 Text Search:

search

☐ quick links

- Dialight Corporate Video
 - Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)
- Application Notes
 - FAQs
- Dialight Ltd (UK)
 - Dialight Garufo
 - Dialight BLP
 - LumiDrives

Circuit Board Indicators - Through Hole Indicators	
P/N# 5682234323F	3 mm Lens
Description	3 mm Quad-Level CBI Y/G-Y-G-Y
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	80
Test Current (mA)	10mA
Absolute Maximum Ratings (T _a = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics				
LED Position	Found in position(s): 1	Found in position(s): 2,4	Found in position(s): 3	
Color	Yellow / Green	Yellow	Green	
Lamp Type	Bi-Color / Bi-Color	Bi-Color	Bi-Color	
LED Type				
Intensity Min (mcd)	2.5 / 2.5	10.0	32.0	
Intensity Typ (mcd)	4.3 / 6.3		50.0	
Intensity Max (mcd)		50		
Fwd Voltage Min				
Fwd Voltage Typ				
Fwd Voltage Max				
Dom Wavelength Min (nm)	587 / 569	587	569	
Dom Wavelength Typ (nm)				
Dom Wavelength Max (nm)				
Power Dissipation Max (mW)	60 / 100	60	100	
Backlighting				
Pitch Between Vertical				
Pitch Between Horizontal				
Lum Intensity Min				
Lum Intensity Typ				
Lum Intensity Max				

Distributor Stock Check

Check stock with our distributors now.

5682234323F

check stock