


1000 AMP INDUSTRIAL AC+DC TRUE RMS CLAMP METER

Cat #: CMI-1000 UPC #: 783310021872
SPECIFICATIONS **SUPPORT DOCUMENTS**

REVIEWS / Q&A



1000 AMP INDUSTRIAL AC+DC TRUE RMS CLAMP METER

Cat #: CMI-1000 UPC #: 783310021872

SHARE

[0 Reviews](#)

[1 question](#) and [1 answer](#) for this product

[Write a review](#) [Ask a question](#)

- Measures AC+DC current and DC microamps
- AC and AC+DC voltage measurements with digital low pass filter for accurate readings on variable frequency drives
- Also measures DC voltage, resistance, capacitance, temperature and frequency
- Tests continuity and diodes
- Phase Sequence & Motor Rotation tests
- Peak-RMS measures motor in rush current
- Flashlight inside clamp jaw for easier work in dark locations
- Backlight & relative mode for added versatility
- AmpTip™ increases accuracy on small wires and low current
- Two voltage detection modes - non-contact or using a single test lead
- Data hold
- Recording of Maximum, Minimum, and Average readings
- Crest (peak hold) feature captures current or voltage peaks as short as 5 milliseconds
- Lifetime warranty

BUY NOW >

REGISTER YOUR PRODUCT >

Specifications

Amperage Measurement
60, 600, 1000 Amps AC+DC

Display
LCD, 6000 Count

Frequency Rating
Voltage: 50/60 Hz. Current: 40 to 400 Hz

Includes
(2) 1.5V AA batteries, test leads and clips, carrying case
Jaw Opening
2.0" (51 mm)

SPECIFICATIONS

Measurement Category
CAT III 1000V, CAT IV 600V

SUPPORT DOCUMENTS

REVIEWS / Q&A

Replacement Part
02714 test leads and clips, TC-30 carrying case

Resistance Measurement
600, 6k, 60k Ohms

Standard
CAT IV, C/US UL Listed, CE

True Power
AC+DC True RMS

Voltage Measurement
600, 1000 Volts AC+DC

*Greenlee® may make improvements and/or changes in the specifications of products at any time, in its sole discretion, without notice or obligation and further reserves the right to change or discontinue models.

Support Documents

Operator's Manual

[📄](https://cdn.greenlee.com/resources/media?key=3b46b52c-b3d1-4801-a6f6-23302a05711d&languageCode=en&type=document) CM-1360, CM-1560 CMH-1000, CMI-1000 Instruction Manual (Cont. Portuguese) (https://cdn.greenlee.com/resources/media?key=3b46b52c-b3d1-4801-a6f6-23302a05711d&languageCode=en&type=document)(4.83 MB)

[📄](https://cdn.greenlee.com/resources/media?key=1c249b1b-979f-49c4-bbac-fd2acb069584&languageCode=en&type=document) CM-1360, CM-1560, CMH-1000, CMI-1000 Instruction Manual (https://cdn.greenlee.com/resources/media?key=1c249b1b-979f-49c4-bbac-fd2acb069584&languageCode=en&type=document)(18.56 MB)

REVIEWS

Q&A

★★★★★



Search topics and reviews



0
Reviews

1
Question

1
Answer

Reviews

★★★★★

Be the first to review this product