



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5690201111F	3 mm Lens Single Color
Description	3 mm Dual Bi-Level CBI R-R-R-R
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	3 mm Lens
Lamp Type	Single Color
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	2mA

Absolute Maximum Ratings (T _a = 25 °)	
Reverse Voltage	5 V
Solder Temp	260Å° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C

Distributor Stock Check

Check stock with our distributors now.

[check stock](#)

how to purchase

- [sales contacts](#)
- [stock check](#)

search

Product Line Search

Please select a Product Line to search.

[find](#)

Part # / Text Search


Part No.:

Text Search:

[search](#)

quick links

- Dialight Corporate Video**
- [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. **View PDF File**](#)
- Application Notes**
- [FAQs](#)
- Dialight Ltd (UK)**
- Dialight Garufo**
- Dialight BLP**
- LumiDrives**



Operating Characteristics

LED Position	1-4
Color	Red
Lamp Type	Single Color
LED Type	Low Current
Intensity Min (mcd)	1
Intensity Typ (mcd)	1.6
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	20
Backlighting	
Pitch Between Vertical	4.57
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	