



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

how to purchase

- [sales contacts](#)
- [stock check](#)

search

[Product Line Search](#)

Please select a Product Line to search.

Part # / Text Search

Part No.:


Text Search:

quick links

- Dialight Corporate Video**
- [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. \*\*View PDF File\*\*](#)
- Application Notes**
- [FAQs](#)
- Dialight Ltd (UK)**
- [Dialight Garufo](#)
- [Dialight BLP](#)
- [LumiDrives](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# <b>5692212200F</b>	3 mm Lens Single Color
Description	3 mm Bi-Level CBI G-G
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	3 mm Lens
Lamp Type	Single Color
Viewing	Right Angle
Viewing Angle	45
Test Current (mA)	10mA
Forward Current (mA)	30mA
LED Centerline	<b>2.29</b>
Polarity	<b>Cathode Pin 1 &amp; 3</b>

Absolute Maximum Ratings (Ta = 25 °)	
Reverse Current	<b>100 @ Vr = 5V</b>
Derating	<b>from 50Å° @ .4 mA/Å°C</b>
Reverse Voltage	<b>5 V</b>
Solder Temp	<b>260Å° for 5 sec</b>
Operating Temp	<b>-55 to +100° C</b>
Storage Temp	<b>-55 to +100° C</b>



Operating Characteristics

LED Position	1,2
Color	Green
Lamp Type	Single Color
LED Type	High Efficiency
Intensity Min (mcd)	32
Intensity Typ (mcd)	50.0
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	100
Backlighting	
Pitch Between Vertical	4.57
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

**Distributor Stock Check**

Check stock with our distributors now.