

Mar.1.2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
<b>APPLICABLE STANDARD</b>									
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)			STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C			
	VOLTAGE	250 V AC			APPLICABLE CONNECTOR	DF1B-*S-2.5R			
	CURRENT	3 A							
<b>SPECIFICATIONS</b>									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
<b>CONSTRUCTION</b>									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			X	X
MARKING		CONFIRMED VISUALLY.						X	X
<b>ELECTRIC CHARACTERISTICS</b>									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			30 mΩ MAX.			X	—
INSULATION RESISTANCE		500 V DC.			1000 MΩ MIN.			X	—
VOLTAGE PROOF		650 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			X	—
<b>MECHANICAL CHARACTERISTICS</b>									
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	—
SHOCK		490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 30 mΩ MAX. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	—
<b>ENVIRONMENTAL CHARACTERISTICS</b>									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→+85→ 5 TO 35 °C TIME 30→ 5 MAX→ 30→ 5 MAX min UNDER 5 CYCLES.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	—
RESISTANCE TO SOLDERING HEAT		1) AUTOMATIC SOLDERING (FLOW) SOLDER TEMPERATURE, 260 °C FOR IMMERSION, DURATION, 5 sec. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE : 300 °C, SOLDERING TIME : 3 sec. NO STRENGTH ON CONTACT.			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR INSERTION DURATION, 5 s.			SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.			X	—
REMARKS					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.					F.Matsuki	H. Umehara	T. Miyazaki	J. Ona	
Unless otherwise specified, refer to JIS C 5402.					'04.03.25	'04.03.25	'04.03.25	04.03.25	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test									
<b>HRS</b> HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET			PART NO.	
								DF1BZ- * P-2.5DS	
CODE NO.(OLD)			DRAWING NO.		PART NO.			1/1	
CL			ELC4-305814-01		CL541				