


RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPST
CONTACT CONFIGURATION

- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
 3. TERM. NOS. FOR REF. ONLY
 4. ACTUATION FORCE: 130±40gf
 5. TRAVEL TO MAKE: 0.3mm +0.4/-0.0
 6. RATING: 30mA, @12V DC
 7. CONTACT RESISTANCE: 50 milli-ohms typical
 8. DIELECTRIC STRENGTH: 300V RMS min at sea level.
 9. ELECTRICAL LIFE CYCLE: 1,000,000 make & break cycles at full load.
 10. DESIGNATE MAJOR DIMENSIONS

C	15472	REMOVED WASHABLE FROM DESC.	10/28/05	C
B	10088	REVISED & REDRAWN	1/27/99	
REV.	ECN No.	DESCRIPTION	DATE	CHKD

TITLE		SCALE		DATE	DR	DWG	REV
GS 10.00 F130 QP		5:1		1/13/99	MM	L600001	C



THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMERRED