


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	NOTE1 -55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	NOTE2 -25 °C TO +60 °C		
	VOLTAGE	125 V AC	OPERATING HUMIDITY RANGE	95 % MAX		
	CURRENT	500 mA	APPLICABLE CABLE	—		
<b>SPECIFICATIONS</b>						
ITEM	TEST METHOD		REQUIREMENTS	QT	AT	
<b>CONSTRUCTION</b>						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.			X	X	
<b>ELECTRIC CHARACTERISTICS</b>						
CONTACT RESISTANCE	100 mA MAX (DC OR 1000 Hz AC).		200 mΩ MAX.	X	X	
		 <p>(AN EXAMPLE OF CONNECTOR CONFIGURATION IS SHOWN.)</p>				
INSULATION RESISTANCE	100 V DC.		100 MΩ MIN.	X	X	
VOLTAGE PROOF	500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	X	
<b>MECHANICAL CHARACTERISTICS</b>						
MECHANICAL OPERATION	200 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE : 220 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—	
VIBRATION	FREQUENCY 10 TO 55 Hz SINGLE AMPLITUDE 0.75 mm, AT 2 HOURS FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 5 μs. ② CONTACT RESISTANCE : 220 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—	
SHOCK	490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			X	—	
<b>ENVIRONMENTAL CHARACTERISTICS</b>						
DAMP HEAT (STEADY STATE)	EXPOSED AT +40 °C, 90 TO 95 % , 500 h		① CONTACT RESISTANCE : 220 mΩ MAX. ② INSULATION RESISTANCE : 1 MΩ MIN. (AT HIGH HUMIDITY) 10 MΩ MIN. (AT DRY) ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55±3 → 5 TO 35 → 85±2 → 5 TO 35 °C TIME 30 TO 35 → 5 MAX → 30 TO 35 → 5 MAX min UNDER 5 CYCLES.		① CONTACT RESISTANCE : 220 mΩ MAX. ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—	
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE : 220 mΩ MAX. ② NO HEAVY CORROSION.	X	—	
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 260 ± 5 °C FOR IMMERSION, DURATION 10 ± 1 S.		NO DEFORMATION OF CASE AND EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245 ± 2 °C FOR IMMERSION, DURATION 3 ± 1 S.		MIN. 95 % OF SOLDER IMMersed AREA SHALL BE COVERED NEW SOLDER COATING.	X	—	
NOTE1 THE OPERATION TEMPERATURE INCLUDES THE RYSE BY CURRENT CARRYING.						
NOTE2 STORAGE TEMPERATURE RANGE SHOWS STORAGE CONDITION FOR UNUSED PRODUCTS INCLUDING PACKING MATERIALS. FOLLOW THE OPERATING TEMPERATURE RANGE FOR STORAGE CONDITION AFTER MOUNTING.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
REMARK				APPROVED MN. KENJO	20211126	
				CHECKED KG. OKITA	20211125	
				DESIGNED MO. SHIMOYAMA	20211125	
				DRAWN NK. OOSHIMA	20211124	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-022410-60-00		
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	TM2RE-2424 (60)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0222-0751-7-60	△ 1/1	