



▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
OFF	NONE	ON
OPEN	N/A	1-1A, 2-2A



RECOMMENDED PANEL MOUNTING






PANEL THICKNESS	X
0.75-1.25	19.1-19.2
1.25-2.00	19.3-19.4
2.00-3.00	19.4-19.6



CIRCUIT: DPST

- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

- ▲3. RATING:
- 6A @250VAC; 9A @125VAC (UL, CSA, VDE)
 - 4(1)A @250VAC (ENEC)
4. LAMP VOLTAGE: 125VAC (NEON BULB)
 5. MATERIAL: CONTACT SURFACE: COIN SILVER, SILVER PLATE
TERMINAL: COPPER ALLOY W/SILVER PLATE.
 6. CONTACT RESISTANCE: 20mΩ TYP. INITIAL
 7. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
 8. DIELECTRIC STRENGTH: >1,500V RMS min. @SEA LEVEL
 9. MECHANICAL LIFE: 30,000 CYCLES.
 10. ELECTRICAL LIFE: 10,000 CYCLES
 11. ▲ DENOTES CRITICAL PARAMETER.
 12. 2002/95/EC (ROHS) COMPLIANT
 13. DEGREE OF PROTECTION: IP20



▲ NEON BULB

PARAMETERS	SYMBOL	MAX.	UNITS
LAMP VOLTAGE(AC)	V	125	V
STARTUP VOLTAGE	V _s	95	V
CURRENT	I	0.8	mA
SERIES RESISTANCE (125V)	R	120	OMHS



TITLE R1973BBLKRILKF1

A	20149	RELEASE FOR PRODUCTION	9/16/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

SCALE	DATE	DR	DWG	REV
1.5:1	9/16/2011	BGL	M400126	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED