



Index

Product	Page
HBL® Extra Heavy Duty Hospital Grade Duplex Receptacles	
Features and Benefits	L-2
Duplex and Style Line® Decorator	L-3
SNAPConnect® Receptacles	L-4
Hubbell-PRO Receptacles	L-7
USB Charger Receptacle, Single and 4-PLEX® Receptacles	L-9
Hospital Grade Plugs, Connector Bodies and Receptacles	
15 and 20A, 125V	L-10
15 and 20A, 250V	L-11
Hospital Grade GFCI Receptacles	
Extra Heavy Duty Tamper-Resistant GFCI Receptacles	L-12
Heavy Duty Tamper-Resistant GFCI Receptacles	L-13
GFCI Receptacles with Auto Grounding	L-14
Heavy Duty SNAPConnect® GFCI LED Receptacles	L-15
Hospital Grade Surge Protection Devices	L-16
Hubbellock® Plugs, Connectors and Receptacles	L-17
Hubbellock® Mobile X-Ray Devices	L-18
Technical Information	L-19

HBL® Extra Heavy Duty Industrial Series



Industrial and Commercial Series GFCIs



Surge Protection Devices



Hubbellock® Receptacles, Plugs and Connectors






One-piece nickel-plated brass integral ground strap for greater corrosion resistance

Patented ground contact provides redundant grounding

Unique bypass contact design results in greater contact force and reduced heat buildup

Square head, 10-thread bronze center rivet won't rotate, reduces stripping and resists corrosion

I.D. marking surface provides quick, sure circuit identification



HBL8200GY

Barbed assembly arms reduce possibility of face/base separation

Back wired ground terminal allows faster, easier installation

RTP base offers greater heat resistance, plus contact stability

External bundling terminals contain wire strands and are designed for quick inspection

Deep body design increases impact and chemical resistance

Hubbell "Hospital Grade" Devices

To qualify for the "Hospital Grade" designation and use of the associated green dot symbol, UL requires that the manufacturer design its devices to perform to specific levels. These levels form an established baseline below which no manufacturer can fall and still carry a green dot.

Hubbell sets their standards high. Each product is built to withstand the severe conditions of abuse that are unique to the hospital environment. Hubbell receptacles have exclusive design features that set them apart from the competition.

- Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature.
- Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas.
- High tech reinforced thermoplastic polyester (RTP) back is tough and heat resistant.

Because of these features and others, the benefit is performance, reliability, and value for any health care facility.



One piece, nickel plated brass mounting strap with integral ground contacts, along with secondary ground contact, provides superior grounding for low resistance flow of fault currents as well as corrosion resistance. Barbed locking arms keep the face locked in place to diminish potential for face/base separation. Back wired ground screw reduces installation time.



Exclusive bypass contacts are made of nickel-plated brass alloy. This design increases blade retention forces, insuring a reliable uninterrupted flow of power.



Reinforced thermoplastic back provides superior thermal, electrical and mechanical properties. By providing contact stability, this high performance material will reduce heat buildup giving you long lasting performance.



External wiring clamps allow for visual inspection of the terminals. A unique strand containment feature on the terminal "bundles" the wire, ensuring 100% clamping of wire strands and reducing heat from the termination.



IP20
 SUITABILITY



15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP




20A 125V
 NEMA 5-20R
 UL CSA
 1 HP


HBL® Extra Heavy Duty Hospital Grade ● Receptacles

Duplex


Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back and side wired.	Black	HBL8200BK	-
	Blue	-	HBL8300BL
	Brown	HBL8200	HBL8300
	Gray	HBL8200GY	HBL8300GY
	Ivory	HBL8200I	HBL8300I
	Light Almond	HBL8200LA	HBL8300LA
	Red	HBL8200RED	HBL8300RED
	White	HBL8200W	HBL8300W
Flush, LED illuminated face, back and side wired.	Gray	HBL8200ILGY	HBL8300ILGY
	Ivory	HBL8200ILI	HBL8300ILI
	Red	HBL8200ILR	HBL8300ILR
	White	HBL8200ILW	HBL8300ILW
Tamper-Resistant receptacle with wire leads. Complies with requirements of NEC® article 517-18(c).	Brown	HBL8200SGA	HBL8300SGA
	Gray	HBL8200SGGYA	HBL8300SGGYA
	Ivory	HBL8200SGIA	HBL8300SGIA
	Light Almond	HBL8200SGLA	HBL8300SGLA
	Red	HBL8200SGRA	HBL8300SGRA
	White	HBL8200SGWA	HBL8300SGWA
Isolated ground ^A .	Orange	IG8200	IG8300
	Red	IG8200R	IG8300R




HBL8200GY




HBL8300SGA



HBL8300RMRI



HBL8200ILW



HBL2172

MRI Receptacle, Duplex

Description	Color	Catalog Number	
MRI receptacle, flush, thermoplastic polyester face, back and side wired.	Ivory	HBL8200IMRI	HBL8300IMRI
	Light Almond	HBL8200LAMRI	HBL8300LAMRI
	Red	HBL8200RMRI	HBL8300RMRI
	White	HBL8200WMRI	HBL8300WMRI

Slender/Compact, Duplex

Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back, and side wired. Fed. Spec. verified.	Brown	HBL8200H	HBL8300H
	Gray	HBL8200HG	HBL8300HG
	Green	-	HBL8300HGN
	Ivory	HBL8200HI	HBL8300HI
	Light Almond	HBL8200HLA	HBL8300HLA
	Red	HBL8200HRED	HBL8300HRED
	White	HBL8200HW	HBL8300HW

Style Line® Decorator*

Description	Color	Catalog Number	
Flush, nylon face, back and side wired.	Brown	HBL2172	HBL2182
	Gray	HBL2172GY	HBL2182GY
	Ivory	HBL2172I	HBL2182I
	Office White	-	HBL2182OW
	Red	HBL2172R	HBL2182R
	White	HBL2172WA	HBL2182WA
Isolated ground ^A .	Ivory	-	IG2182I
	Orange	-	IG2182
	White	-	IG2182WA

Note: ^ASee section M for additional information on isolated ground devices.

*Not Fed. Spec. Listed.

See pages A-48 and A-49 for accessories.

See page L-19 for technical information.

See page Tech-10 for Tamper-Resistant description.

See section N for wallplates.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).

Dimensions in Inches (mm)



IP20
 SUITABILITY




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

**Extra Heavy Duty
 Hospital Grade ● SNAPConnect®**

Duplex

Description	Color	Catalog Number	
Hospital grade, finder groove, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA*.	Black	SNAP8200BKA*	SNAP8300BKA*
	Brown	SNAP8200A*	SNAP8300A*
	Gray	SNAP8200GYA*	SNAP8300GYA*
	Ivory	SNAP8200IA*	SNAP8300IA*
	Light Almond	SNAP8200LAA*	SNAP8300LAA*
	Red	SNAP8200RA*	SNAP8300RA*
	White	SNAP8200WA*	SNAP8300WA*
 Hospital grade, Tamper-Resistant, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP8200BKTR	SNAP8300BKTR
	Brown	SNAP8200TR	SNAP8300TR
	Gray	SNAP8200GYTR	SNAP8300GYTR
	Ivory	SNAP8200ITR	SNAP8300ITR
	Light Almond	SNAP8200LATR	SNAP8300LATR
	Red	SNAP8200RTR	SNAP8300RTR
	White	SNAP8200WTR	SNAP8300WTR
Isolated ground ^A , Hospital grade, Tamper-Resistant.	Orange	SNAP8200IGTR	SNAP8300IGTR
	Red	SNAP8200RIGTR	SNAP8300RIGTR
 Hospital grade, with Power Indicating LED, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP8200BKL	SNAP8300BKL
	Brown	SNAP8200L	SNAP8300L
	Gray	SNAP8200GYL	SNAP8300GYL
	Ivory	SNAP8200IL	SNAP8300IL
	Light Almond	SNAP8200LAL	SNAP8300LAL
	Red	SNAP8200RL	SNAP8300RL
	White	SNAP8200WL	SNAP8300WL
Isolated ground ^A , Hospital grade, with Power Indicating LED.	Orange	SNAP8200IGL	SNAP8300IGL
	Red	SNAP8200RIGL	SNAP8300RIGL
  Hospital grade, Tamper-Resistant, with Power Indicating LED, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP8200BKLTR	SNAP8300BKLTR
	Brown	SNAP8200LTR	SNAP8300LTR
	Gray	SNAP8200GYLTR	SNAP8300GYLTR
	Ivory	SNAP8200ILTR	SNAP8300ILTR
	Light Almond	SNAP8200LALTR	SNAP8300LALTR
	Red	SNAP8200RLTR	SNAP8300RLTR
	White	SNAP8200WLTR	SNAP8300WLTR
Isolated ground ^A , Hospital grade, TR with Power Indicating LED.	Orange	SNAP8200IGLTR	SNAP8300IGLTR
	Red	SNAP8200RIGLTR	SNAP8300RIGLTR


Note: ^ASee section M additional information on isolated ground devices.
 See page A-15 for additional information on SNAPConnect® features.
 See pages A-48 and A-49 for accessories.
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.
 See page L-20 for technical information.
 See section N for wallplates.
 Consult factory for available Split-Circuit capable SNAPConnect® devices.

SNAPConnect® Right Angle Pigtailed Connector


Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material	Solid	SNAP1RA	SNAP1RNA
	Stranded	SNAP2RA	SNAP2RNA

Note: For Assembled in USA products, must order connector with NA suffix.
 See page L-20 for technical information.


Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.




SNAP8300WA




SNAP8300LATR



SNAP8300L



SNAP8300RLTR



SNAP1RA

Dimensions in Inches (mm)

Straight Blade Devices

15 and 20 Ampere, 125 Volts

2 Pole, 3 Wire Grounding



IP20
SUITABILITY



15A 125V
NEMA 5-15R
UL CSA
0.5 HP




20A 125V
NEMA 5-20R
UL CSA
1 HP

Extra Heavy Duty Hospital Grade ● SNAPConnect®


Style Line® Decorator

Description	Color	Catalog Number	
Hospital grade, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA*.	Black	SNAP2172BKA*	SNAP2182BKA*
	Brown	SNAP2172A*	SNAP2182A*
	Gray	SNAP2172GYA*	SNAP2182GYA*
	Ivory	SNAP2172IA*	SNAP2182IA*
	Light Almond	SNAP2172LAA*	SNAP2182LAA*
	Red	SNAP2172RA*	SNAP2182RA*
	White	SNAP2172WA*	SNAP2182WA*
Hospital grade, Tamper-Resistant, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP2172BKTR	SNAP2182BKTR
	Brown	SNAP2172TR	SNAP2182TR
	Gray	SNAP2172GYTR	SNAP2182GYTR
	Ivory	SNAP2172ITR	SNAP2182ITR
	Light Almond	SNAP2172LATR	SNAP2182LATR
	Red	SNAP2172RTR	SNAP2182RTR
	White	SNAP2172WTR	SNAP2182WTR
Isolated ground ^A , Hospital grade, Tamper-Resistant.	Orange	SNAP2172IGTR	SNAP2182IGTR
	Red	SNAP2172RIGTR	SNAP2182RIGTR
Hospital grade, with Power Indicating LED, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP2172BKL	SNAP2182BKL
	Brown	SNAP2172L	SNAP2182L
	Gray	SNAP2172GYL	SNAP2182GYL
	Ivory	SNAP2172IL	SNAP2182IL
	Light Almond	SNAP2172LAL	SNAP2182LAL
	Red	SNAP2172RL	SNAP2182RL
	White	SNAP2172WL	SNAP2182WL
Isolated ground ^A , Hospital grade, with Power Indicating LED.	Orange	SNAP2172IGL	SNAP2182IGL
	Red	SNAP2172RIGL	SNAP2182RIGL
Hospital grade, Tamper-Resistant, with Power Indicating LED, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	SNAP2172BKLTR	SNAP2182BKLTR
	Brown	SNAP2172LTR	SNAP2182LTR
	Gray	SNAP2172GYLTR	SNAP2182GYLTR
	Ivory	SNAP2172ILTR	SNAP2182ILTR
	Light Almond	SNAP2172LALTR	SNAP2182LALTR
	Red	SNAP2172RLTR	SNAP2182RLTR
	White	SNAP2172WLTR	SNAP2182WLTR
Isolated ground ^A , Hospital grade, TR with Power Indicating LED.	Orange	SNAP2172IGLTR	SNAP2182IGLTR
	Red	SNAP2172RIGLTR	SNAP2182RIGLTR


Note: ^ASee section M additional information on isolated ground devices.
See page A-15 for additional information on SNAPConnect® features.
See pages A-48 and A-49 for accessories.
See page Tech-10 for Tamper-Resistant and LED Power Indicators description.
See page L-20 for technical information.
See section N for wallplates.
Consult factory for available Split-Circuit capable SNAPConnect® devices.




SNAP2182A




SNAP2182ITR



SNAP2182RL



SNAP2182GYLTR



SNAP1RA

SNAPConnect® Right Angle Pigtailed Connector

Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material	Solid	SNAP1RA	SNAP1RNA
	Stranded	SNAP2RA	SNAP2RNA

Note: For Assembled in USA products, must order connector with NA suffix.
See page L-20 for technical information.

Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.

Dimensions in Inches (mm)



Fed.Spec.




Meets UL
 Standard 943
 Class A GFCI



15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP




20A 125V
 NEMA 5-20R
 UL CSA
 1 HP



GFR8300SNAPRNA

SNAPConnect® GFCI LED Hospital Grade ●, Assembled in USA

Description	Rating	Color	15A 125V AC	20A 125V AC
Hospital Grade SNAPConnect GFCI LED, self-grounding staple, requires connector below, sold separately.	15 and 20A 125V AC	Black Brown Gray Ivory Light Almond Red White	GFR8200SNAPBKNA GFR8200SNAPNA GFR8200SNAPGYNA GFR8200SNAPINA GFR8200SNAPLANA GFR8200SNAPRNA GFR8200SNAPWNA	GFR8300SNAPBKNA GFR8300SNAPNA GFR8300SNAPGYNA GFR8300SNAPINA GFR8300SNAPLANA GFR8300SNAPRNA GFR8300SNAPWNA




GFTR8300SNAPWNA

SNAPConnect® GFCI LED Hospital Grade ●, Tamper and Weather Resistant, Assembled in USA



Description	Rating	Color	15A 125V AC	20A 125V AC
Hospital Grade SNAPConnect GFCI TR/WR, self-grounding staple, requires connector below, sold separately.	15 and 20A 125V AC	Black Brown Gray Ivory Light Almond Red White	GFTR8200SNAPBKNA GFTR8200SNAPNA GFTR8200SNAPGYNA GFTR8200SNAPINA GFTR8200SNAPLANA GFTR8200SNAPRNA GFTR8200SNAPWNA	GFTR8300SNAPBKNA GFTR8300SNAPNA GFTR8300SNAPGYNA GFTR8300SNAPINA GFTR8300SNAPLANA GFTR8300SNAPRNA GFTR8300SNAPWNA



SNAP8300USBW

SNAPConnect® USB Charger Hospital Grade ●, Duplex Receptacles




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP



Description	Color	15A 125V AC	20A 125V AC
Hospital Grade SNAPConnect USB Charger, Tamper-Resistant Style Line® decorator duplex receptacle, two USB type 2.0 ports 3 Amp, 5 Volt DC, 15 or 20 Amp, 125 Volt AC.	Black Brown Gray Ivory Light Almond Red White	SNAP8200USBBK SNAP8200USB SNAP8200USBGY SNAP8200USBI SNAP8200USBLA SNAP8200USBR SNAP8200USBW	SNAP8300USBBK SNAP8300USB SNAP8300USBGY SNAP8300USBI SNAP8300USBLA SNAP8300USBR SNAP8300USBW



SNAP8262S

SNAPConnect® Surge Protection Hospital Grade ●, Tamper-Resistant Receptacle with Power Indicating LED




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP



Description	Color	15A 125V AC	20A 125V AC
Hospital Grade SNAPConnect Surge suppression, Tamper-Resistant, smooth face, duplex receptacle.	Blue Gray Ivory Light Almond Red White	SNAP8262S SNAP8262GYS SNAP8262IS SNAP8262LAS SNAP8262RS SNAP8262WS	SNAP8362S SNAP8362GYS SNAP8362IS SNAP8362LAS SNAP8362RS SNAP8362WS



SNAP1RA

SNAPConnect® Right Angle Pigtailed Terminal

Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads, 600V, #12 AWG THHN/THWN-2, Polycarbonate housing material.	Solid Stranded	SNAP1RA SNAP2RA	SNAP1RNA SNAP2RNA


Note: See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.
 See page M-19 for SNAPConnect® technical information.

Dimensions in Inches (mm)

Hospital Products
15 and 20 Ampere, 125 Volts
 2 Pole, 3 Wire Grounding




Hubbell-PRO Features



8200REDLTR


Hubbell-PRO Heavy Duty Hospital Grade Receptacles




Duplex

Description	Color	Catalog Number	
Hospital grade, smooth nylon face, back and side wired. Assembled in USA.	Black	8200BK	8300BK
	Brown	8200	8300
	Gray	8200GY	8300GY
	Ivory	8200IV	8300IV
	Light Almond	8200LA	8300LA
	Red	8200RED	8300RED
	White	8200WHI	8300WHI
Hospital grade, Tamper-Resistant, smooth nylon face, back and side wired. Assembled in USA.	Black	8200BKTR	8300BKTR
	Brown	8200TR	8300TR
	Gray	8200GYTR	8300GYTR
	Ivory	8200IVTR	8300IVTR
	Light Almond	8200LATR	8300LATR
	Red	8200REDTR	8300REDTR
	White	8200WTR	8300WTR
Hospital grade, with Power Indicating LED, smooth nylon face, back and side wired. Assembled in USA.	Black	8200BKL	8300BKL
	Brown	8200L	8300L
	Gray	8200GYL	8300GYL
	Ivory	8200IVL	8300IVL
	Light Almond	8200LAL	8300LALM
	Red	8200REDL	8300REDL
	White	8200WL	8300WL
Hospital grade, Tamper-Resistant, with Power Indicating LED, smooth nylon face, back and side wired. Assembled in USA.	Black	8200BKLTR	8300BKLTR
	Brown	8200LTR	8300LTR
	Gray	8200GYLTR	8300GYLTR
	Ivory	8200IVLTR	8300IVLTR
	Light Almond	8200LALTR	8300LALTR
	Red	8200REDLTR	8300REDLTR
	White	8200WLTR	8300WLTR


Note: See pages A-48 and A-49 for accessories.
 See page L-21 for technical information.
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.
 See section N for wallplates.



8200LA




8200TR




8200REDLTR

Dimensions in Inches (mm)


The products listed on this page are Assembled in USA, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.




2182IVLTR



2172LATR



2172L



2182IVLTR

Dimensions in Inches (mm)

Hubbell-PRO Heavy Duty Hospital Grade ● Receptacles



Style Line® Decorator

Description	Color	Catalog Number	
Hospital grade, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	2172BK	2182BK
	Brown	2172	2182
	Gray	2172GY	2182GY
	Ivory	2172IV	2182IV
	Light Almond	2172LA	2182LA
	Red	2172RED	2182RED
	White	2172W	2182W
Hospital grade, Tamper-Resistant, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	2172BKTR	2182BKTR
	Brown	2172TR	2182TR
	Gray	2172GYTR	2182GYTR
	Ivory	2172IVTR	2182IVTR
	Light Almond	2172LATR	2182LATR
	Red	2172REDTR	2182REDTR
	White	2172WTR	2182WTR
Hospital grade, with Power Indicating LED, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	2172BKL	2182BKL
	Brown	2172L	2182L
	Gray	2172GYL	2182GYL
	Ivory	2172IVL	2182IVL
	Light Almond	2172LAL	2182LAL
	Red	2172REDL	2182REDL
	White	2172WL	2182WL
Hospital grade, Tamper-Resistant, with Power Indicating LED, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	2172BKLTR	2182BKLTR
	Brown	2172LTR	2182LTR
	Gray	2172GYLTR	2182GYLTR
	Ivory	2172IVLTR	2182IVLTR
	Light Almond	2172LALTR	2182LALTR
	Red	2172REDLTR	2182REDLTR
	White	2172WLTR	2182WLTR

Note: See pages A-48 and A-49 for accessories.
 See page L-21 for technical information.
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.
 See section N for wallplates.

The products listed on this page are Assembled in USA, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.



USB Charger Tamper-Resistant Hospital Grade Receptacles




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

Description	Color	15A 125V AC	20A 125V AC
USB Charger Tamper-Resistant receptacle, Two USB Type 2.0 ports 3 Amp, 5 Volt DC, 15 or 20 Amp, 125 Volt AC decorator duplex.	Black	USB8200BK	USB8300BK
	Brown	USB8200	USB8300
	Gray	USB8200GY	USB8300GY
	Ivory	USB8200I	USB8300I
	Light Almond	USB8200LA	USB8300LA
	Red	USB8200R	USB8300R
	White	USB8200W	USB8300W



USB8300W

Note: See page A-20 for standard USB charger.
 See page Tech-10 for Tamper-Resistant description.

HBL® Extra Heavy Duty Hospital Grade Single Receptacles

IP20
 SUITABILITY




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

Description	Color	Catalog Number	
Flush, nylon face, back and side wired, Fed. Spec. verified.	Almond	-	HBL8310AL
	Brown	HBL8210	HBL8310
	Gray	HBL8210GY	HBL8310GY
	Ivory	HBL8210I	HBL8310I
	Red	HBL8210R	HBL8310R
	White	HBL8210W	HBL8310W
Panel mount on 1.94 in. (49.2) centers.	Brown	HBL8284	-
	Ivory	HBL8284I	HBL8384I
Isolated ground ^A .	Orange	IG8210	IG8310



HBL8210GY

Note: ^ASee section M for additional information on isolated ground devices.

4-PLEX® Hospital Grade Receptacles




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP


Description	Color	Catalog Number	
4 outlet high impact resistant Polycarbonate construction. Mount to 4 in. square box.	Brown	HBL415H	HBL420H
	Gray	-	HBL420HG
	Ivory	HBL415HI	HBL420HI
	Red	HBL415HR	HBL420HR
	White	HBL415HW	HBL420HW



HBL415HI

4-PLEX® Accessories

Description	Color	Catalog Number	
4-PLEX adapter plates for 1- and 2-gang, device boxes.	Brown	HBL4AP	HBL4AP
	Gray	HBL4APGY	HBL4APGY
	Ivory	HBL4API	HBL4API
	Red	HBL4APR	HBL4APR
	White	HBL4APW	HBL4APW



HBL4API

Dimensions in Inches (mm)


IP20
SUITABILITY



15A 125V
NEMA 5-15P
UL CSA



20A 125V
NEMA 5-20P
UL CSA




HBL8215C

Hospital Grade ● Plugs

Insulgrip®

Description	Cord Diameter	Catalog Number	
Black and white nylon.	.230"-.720" (5.8-18.3)	HBL8215C	HBL8315C
Transparent housing.	.230"-.720" (5.8-18.3)	HBL8215CT	HBL8315CT
8 position angle plug, transparent housing.	.250"-.655" (6.4-16.6)	HBL8215CAT*	HBL8315CAT*




HBL8215CAT

Valise®

Description	Cord Diameter	Catalog Number	
White nylon.	.300"-.660" (7.6-16.8)	HBL8115V	HBL8364V
Insulation displacement, white nylon.	.300"-.360" (7.6-9.1)	HBL8013V*	-

Note: *Not Fed. Spec. Listed.
 See page A-49 for accessories.
 See pages L-23 and L-24 for technical information.



HBL8115V

IP20
SUITABILITY



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

Hospital Grade ● Connector Bodies

Insulgrip®

Description	Cord Diameter	Catalog Number	
Black and white nylon.	.230"-.720" (5.8-18.3)	HBL8219C	HBL8319C
Transparent housing.	.230"-.720" (5.8-18.3)	HBL8219CT	HBL8319CT


Valise®

Description	Cord Diameter	Catalog Number	
White nylon.	.300"-.660" (7.6-16.8)	HBL8119V	-


Note: See page A-49 for accessories.
 See pages L-23 and L-24 for technical information.



HBL8219C



HBL8219CT



HBL8119V

Dimensions in Inches (mm)

IP20
SUITABILITY



15A 250V
NEMA 6-15P
UL CSA
1.5 HP




20A 250V
NEMA 6-20P
UL CSA
2 HP

Hospital Grade ● Plugs

Valise®

Description	Cord Diameter	Catalog Number	
Valise plug, white nylon.	.300"-.660" (7.6-16.8)	HBL8666V	HBL8464V

Note: HP ratings listed above are based on 208 to 240V AC only.



HBL8666V

Hospital Grade ● Receptacles

HBL® Extra Heavy Duty, Duplex

Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back and side wired, multiple drive screws.	Brown Ivory	HBL8600 HBL8600I	HBL8400 HBL8400I


Note: See page A-48 for accessories.
 See section N for wallplates.



15A 250V
NEMA 6-15R
UL CSA
1.5 HP



20A 250V
NEMA 6-20R
UL CSA
2 HP



HBL8600I


Hospital Grade ● Connector Bodies

Valise®

Description	Cord Diameter	Catalog Number
White nylon.	.300"-.660" (7.6-16.8)	HBL8469V



20A 250V
NEMA 6-20R
UL CSA
2 HP



HBL8469V

Dimensions in Inches (mm)



GFR8300SGI

10kA Short Circuit Current Rating

- Limits improper access to energized contacts
 - Exclusive patented tamper-resistant protection through switching technology
- Continually tests and monitors for people protection automatically
 - Patented self test diagnostics
- Power indication
 - Steady "ON" **GREEN LED** provides indication of power
- Ground fault indicator
 - Steady "ON" **RED LED** provides visual indication of a ground fault condition; flashing red indicates device has lost capability to provide protection
- No power at face if reverse wired
 - Open circuit condition eliminates false assumption of protection at face
- Durable face with V-0 flammability rating
 - Polyester face cover



Hospital Grade ● AUTOGUARD®
Self Test GFCI Receptacles
Tamper-Resistant and Weather Resistant



15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

Description	Rating	Color	Catalog Number	Catalog Number
  Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	GFR8200SGBK	GFR8300SGBK
		Brown	GFR8200SG	GFR8300SG
		Gray	GFR8200SGGY	GFR8300SGGY
		Ivory	GFR8200SGI	GFR8300SGI
		Red	GFR8200SGR	GFR8300SGR
		White	GFR8200SGW	GFR8300SGW



GFR8300SGW


Hospital Grade ● CircuitGuard®
GFCI Receptacles
Tamper-Resistant and Weather Resistant



15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

Description	Rating	Color	Catalog Number	Catalog Number
  Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	GFR8200BKTR	GFR8300BKTR
		Brown	GFR8200TR	GFR8300TR
		Gray	GFR8200GYTR	GFR8300GYTR
		Ivory	GFR8200ITR	GFR8300ITR
		Red	GFR8200RTR	GFR8300RTR
		White	GFR8200WTR	GFR8300WTR



GFR8300RTR

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with both a matching color nylon wallplate, and a SS26 302/304 super stainless steel wallplate. 20 amp feed-through capability. See page Tech-10 for Tamper and Weather Resistant descriptions.

Hospital Products Heavy Duty GFCI Receptacles Tamper-Resistant and Weather Resistant with Auto Grounding




GFR8300HITR

10kA Short Circuit Current Rating

- Limits improper access to energized contacts
 - Patented shutter design for tamper-resistant protection
- No power at face if reverse wired
 - Open circuit condition eliminates false assumption of protection at face
- Ground fault EOL indicator
 - Flashing **RED** indicates device has lost capability to provide protection
- Accepts fork terminals
 - Open terminal design
- Installation ease
 - Internal back wiring
 - Automatic self-grounding staple
 - Captive mounting screws

Hospital Grade ● Circuit Guard® GFCI Receptacles Tamper-Resistant and Weather Resistant



Description	Rating	Color	Catalog Number
Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFR8200HBKTR
		Brown	GFR8200HTR
		Gray	GFR8200HGYTR
		Ivory	GFR8200HITR
		Light Almond	GFR8200HLATR
		Red	GFR8200HRTR
		White	GFR8200HWTR
			GFR8300HBKTR
			GFR8300HTR
			GFR8300HGYTR
			GFR8300HITR
			GFR8300HLATR
			GFR8300HRTR
			GFR8300HWTR



GFR8200HGYTR

Hospital Grade ● Tamper-Resistant and Weather Resistant Assembled in USA



Description	Rating	Color	Catalog Number
Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple. Assembled in USA.	15 and 20A 125VAC	Black	GFR8200HBKTRU
		Brown	GFR8200HTRU
		Gray	GFR8200HGYTRU
		Ivory	GFR8200HITRU
		Light Almond	GFR8200HLATRU
		Red	GFR8200HRTRU
		White	GFR8200HWTRU
			GFR8300HBKTRU
			GFR8300HTRU
			GFR8300HGYTRU
			GFR8300HITRU
			GFR8300HLATRU
			GFR8300HRTRU
			GFR8300HWTRU



GFR8300HTRU

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feed-through capability. See page Tech-10 for Tamper and Weather Resistant descriptions.

Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.



GFR8200HILA

10kA Short Circuit Current Rating

- Comprehensive diagnostics
 - When test button is actuated, both the electronic components and mechanical trip mechanism are functionally tested
- Ground fault EOL indicator
 - Flashing **RED** indicates device has lost capability to provide protection
- No power at face if reverse wired
 - Open circuit condition eliminates false assumption of protection at face
- Installation ease
 - Internal back wiring
 - Automatic self-grounding staple
 - Captive mounting screws



15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

**Hospital Grade ●
 Circuit Guard® GFCI Receptacles**

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFR8200HBKLA	GFR8300HBKLA
		Brown	GFR8200HLA	GFR8300HLA
	Gray	GFR8200HGYLA	GFR8300HGYLA	
	Ivory	GFR8200HILA	GFR8300HILA	
	Light Almond	GFR8200HLAA	GFR8300HLAA	
	Red	GFR8200HRLA	GFR8300HRLA	
White	GFR8200HWLA	GFR8300HWLA		

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feed-through capability.



GFR8200HWLA

**Hospital Grade ● GFCI LED
 Assembled in USA**

Description	Rating	Color	Catalog Number	
Hospital Grade ●, impact resistant flush nylon face, back and side wired, self-grounding staple. Assembled in USA.	15 and 20A 125V AC	Black	GFR8200HBKLU	GFR8300HBKLU
		Brown	GFR8200HLU	GFR8300HLU
		Gray	GFR8200HGYLU	GFR8300HGYLU
		Ivory	GFR8200HILU	GFR8300HILU
		Light Almond	GFR8200HLALU	GFR8300HLALU
		Red	GFR8200HRLU	GFR8300HRLU
White	GFR8200HWLU	GFR8300HWLU		



GFR8300HRLU

GFCI Receptacle Specifications per GFCI Products Listed (Pages L-12 to L-15)

Trip Level	4 to 6 mA.
Trip Time	.025 second nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15% (102V to 132V).
Amperage	15A/20A, 20A Feed Thru.
Maximum Interrupting Capacity	10,000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978. CSA Certified.
Codes	Meets all NEC® and CEC requirements. NEMA WD-6 ANSI 73.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).


Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.



GFR8300SNAPINA

SNAPConnect® GFCI Features

- Audible SNAP, indicates solid connection
 - Secure, easy grip latch
- Inspection of power contacts
 - Clear terminal housing
 - No exposed metal
- Ground fault EOL indicator
 - Flashing **RED** indicates device has lost capability to provide protection
- Requires minimal box space
 - Compact size
 - Clean finished look
- Installation ease
 - Automatic self-grounding staple



Hospital Grade ● SNAPConnect® GFCI LED
Assembled in USA

Description	Rating	Color	Catalog Number	
SNAPConnect® GFCI, self-grounding staple. Assembled in USA.	15 and 20A 125V AC	Black	GFR8200SNAPBKNA	GFR8300SNAPBKNA
		Brown	GFR8200SNAPNA	GFR8300SNAPNA
		Gray	GFR8200SNAPGYNA	GFR8300SNAPGYNA
		Ivory	GFR8200SNAPINA	GFR8300SNAPINA
		Light Almond	GFR8200SNAPLANA	GFR8300SNAPLANA
		Red	GFR8200SNAPRNA	GFR8300SNAPRNA
		White	GFR8200SNAPWNA	GFR8300SNAPWNA
Requires connector below, sold separately.				



GFR8200SNAPWNA

Hospital Grade ● SNAPConnect® GFCI LED
Tamper and Weather Resistant, Assembled in USA

Description	Rating	Color	Catalog Number	
SNAPConnect® GFCI TR/WR, self-grounding staple. Assembled in USA.	15 and 20A 125V AC	Black	GFTR8200SNAPBKNA	GFTR8300SNAPBKNA
		Brown	GFTR8200SNAPNA	GFTR8300SNAPNA
		Gray	GFTR8200SNAPGYNA	GFTR8300SNAPGYNA
		Ivory	GFTR8200SNAPINA	GFTR8300SNAPINA
		Light Almond	GFTR8200SNAPLANA	GFTR8300SNAPLANA
		Red	GFTR8200SNAPRNA	GFTR8300SNAPRNA
		White	GFTR8200SNAPWNA	GFTR8300SNAPWNA
Requires connector below, sold separately.				



GFR8300SNAPGYNA

SNAPConnect® Right Angle Pigtailed Connector


Description	Wire Type	General Use	Buy American
		Catalog Number	Catalog Number
Clear right angle terminal with 6 inch leads, 600V, #12 AWG THHN/THWN-2, Polycarbonate housing material.	Solid	SNAP1RA	SNAP1RNA
	Stranded	SNAP2RA	SNAP2RNA

Note: For Assembled in USA products, must order connector with NA suffix.
 See page Tech-10 for Tamper and Weather Resistant descriptions.
 See section N for wallplates.




SNAP1RNA


Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.




SNAP8362GYS



HBL8362ISA



HBL420HS



HBL4API



HBL6PSHG

Dimensions in Inches (mm)

Hospital Grade ● Circuit Guard® Receptacles



Description	Color	Catalog Number	
SNAPConnect® Tamper-Resistant, surge suppression receptacle, smooth face, duplex. Requires connector on page L-15, sold separately.	Blue	SNAP8262S	SNAP8362S
	Gray	SNAP8262GYS	SNAP8362GYS
	Ivory	SNAP8262IS	SNAP8362IS
	Light Almond	SNAP8262LAS	SNAP8362LAS
	Red	SNAP8262RS	SNAP8362RS
	White	SNAP8262WS	SNAP8362WS
Surge suppression receptacles with light and alarm, 240 joules/15000A per mode.	Almond	HBL8262ALSA	HBL8362ALSA
	Blue	HBL8262SA	HBL8362SA
	Gray	HBL8262GYSA	HBL8362GYSA
	Ivory	HBL8262ISA	HBL8362ISA
	Red	HBL8262RSA	HBL8362RSA
	White	HBL8262WSA	HBL8362WSA
Isolated ground, surge suppression receptacles with light and alarm, 240 joules/15000A per mode.	Blue	IG8262SA	IG8362SA
	Gray	IG8262GYSA	IG8362GYSA
	Ivory	IG8262ISA	IG8362ISA
	Orange	IG8262OSA	IG8362OSA
	Red	IG8262RSA	IG8362RSA
	White	IG8262WSA	IG8362WSA
4-PLEX® surge suppression receptacles with lights, 80 joules/6500A per mode.	Blue	-	HBL420HS
	Ivory	-	HBL420HIS
	Red	-	HBL420HRS

Note: See page Tech-10 for Tamper-Resistant description.

4-PLEX® Accessories

Description	Color	Catalog Number
4-PLEX Adapter Plates for 1- and 2-gang, and 4 in. (101.6) square device boxes.	Blue	HBL4APBL
	Ivory	HBL4API
	Red	HBL4APR
4-PLEX Portable Box. Portable 4 in. (101.6) square box with cord grip. Accepts up to .66 in. (16.8) diameter cord.	Ivory	HBL4PBI

Note: 4-PLEX Box is not UL Listed.

Metallic Power Strip Surge Protected



Description	Catalog Number
15A 125V power strip with filtering, surge protection, 3 hospital grade duplex receptacles, 6 foot power supply cord and hospital grade plug.	HBL6PSHG

Note: See section M for additional information on surge protection products.

Wallplates (Sold Separately)

Configuration	High-Impact Nylon			Plated Steel		Stainless Steel (S/S) Brass	
	Color	Standard	Mid-Size				
1-Gang	Almond	NP26AL	NPJ26AL	Chrome Brass Plated	SCH26 SBP26	Smooth S/S Smooth S/S Smooth Brass	SS26 SSJ26 [▲] SB26
	Blue	-	NPJ26CBL*				
	Blue	-	NPJ26BL				
	Gray	NP26GY	NPJ26GY				
	Ivory	-	NPJ26C*				
	Ivory	NP26I	NPJ26I				
	Off. White	NP26OW	NPJ26OW				
	Orange	NP26OIG**	-				
	Red	NP26R	NPJ26R				
	White	NP26W	NPJ26W				

Note: *Premarked "COMPUTER ONLY." Lettering is block 1/4" high.
 **Premarked "ISOLATED GROUND." Lettering is block 1/4" high.
 ▲ Jumbo size plate.
 See page A-62 for technical information on 4-PLEX devices.

Hospital Products Hubbellok® Plugs, Connector Bodies and Receptacles

20 Ampere, 125 Volts AC only, 2 Pole, 3 Wire Grounding



For Hospital Use Only



Hubbellok® Plugs and Connector Bodies

Description	Plugs	Connector Bodies
Nylon cover, thermoset interior.	HBL23014HGB	HBL23001HGB
Armored, epoxy filled, rubber cord grip.	HBL23004HG	-


Note: Cord clamp range for plug and connector .300" to .660" (7.6 to 16.8).



20A 125V AC



20A 125V AC



HBL23014HGB

Receptacles

Description	Catalog Number
Black, back wired.	- HBL23000HG



HBL23001HGB


Wallplates

Description	Catalog Number
Stainless steel 302/304, single-gang.	HBL23901HG
Stainless steel 302/304, three-gang for two receptacles.	HBL23909HG

Note: Suffix HG or HGB type for hospital use only.




IP30
SUITABILITY



20A 125V AC

Explosion Proof Plug

Description	Catalog Number
Plug, with, epoxy kit, accepts #12 or #14 type SO cable.	HBL24312




HBL23000HG


Hazardous to Non-hazardous Location Receptacle Conversion Kits

Conversion kits for replacement of explosion proof receptacles listed above, with non-explosion proof receptacles, in the hospital areas formerly classified as hazardous locations and now classified non-hazardous locations due to the change from flammable anesthetizing gases to nonflammable anesthetizing gases.

For Conversion To:	Catalog Number
20A, 125V, duplex receptacle (Hubbell HBL830 Series). Includes adapter ring and stainless steel wall plate for duplex receptacle (receptacle not included).	HBL24300RKD
20A, 125V, Hospital Hubbell receptacle (Hubbell HBL23000HG) or 20A, 125V, straight blade single receptacle (Hubbell HBL8310 series). Includes adapter ring and stainless wall plate for single receptacle (receptacle not included).	HBL24300RKS



HBL24312




Dimensions in Inches (mm)




HBL25515




HBL25615



HBL25605




HBL25603



HBL25509

IP30
 SUITABILITY



50A 250V AC




60A 250V AC


Mobile X-Ray Plugs

Description	Catalog Number	
Plug, with epoxy kit, less cord clamp.	HBL25515	HBL25615
Plug, with cord clamp, less epoxy kit.	HBL25525	HBL25625

*Note: Cord clamp range of plugs with cord clamps .830" to 1.3" (21.1 to 33.0).
 50A plugs fit 50A or 60A receptacles.*



50A 250V AC



60A 250V AC

Mobile X-Ray Receptacles

Description	Catalog Number	
Receptacle with stainless steel plate assembly.	HBL25505	HBL25605
Receptacle with cast aluminum plate assembly.	HBL25503	HBL25603
Replacement receptacle interior.	-	IN16494

Accessory

Description	Catalog Number
Box stamped steel 8" x 8" x 4" (203.2 x 203.2 x 101.6), accommodates 50A and 60A mobile X-ray receptacles. Knockout sizes 1¼", 1½" and 2".	HBL25509

Dimensions in Inches (mm)



HBL8200GY

**HBL® Extra Heavy Duty, Straight Blade
Hospital Grade Duplex Receptacles**

Specifications

Receptacles	Part	Description
Typical Specification – Catalog No. HBL8200	Receptacle	15A
Manufacturer’s Identification – Hubbell HBL8200	Top	PBT*
Description – Hospital Grade, Straight Blade Duplex Receptacle	Base	RTP**
Type – 2 Pole, 3 Wire, Grounding	By-Pass Power Contacts	.037 in. (.9) Brass – Nickel Finish
Rating – 15A, 125V	Clamping Plate	.031 in. (.8) Brass – Nickel Finish
Certification: UL Listed to UL 498 File E2186, Fed. Spec. WC596,	Mounting Strap	.050 in. (1.3) Brass – Nickel Finish
Hospital Grade, NEMA® WD-6 Compliant	Line Terminal Screws	#10-32 Silicone Bronze, Multiple Drive
Certified to CSA, C22.2, No. 42 File 285	Hex Head Grounding Screw	#10-32 (Green) Silicon Bronze, Multiple Drive
	Center Assembly Rivet	Silicon Bronze
	Automatic Self-Grounding Clip	Stainless Steel
	Flat Head Mounting Screws	Stainless Steel

Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green).
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.
Environmental – Material	
Flammability	UL 94V-0 and UL 94-5 VA.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

Note: *Polybutylene Terephthalate.
**Reinforced Thermoplastic Polyester.

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



**SNAPConnect® Straight Blade
Hospital Grade Duplex Receptacles**



Specifications


Receptacle	Part	Description
Typical Specification – Catalog No. SNAP8200	Receptacle	15A
Manufacturer's Identification – Hubbell SNAP8200	Top	Nylon
Description – Straight Blade Duplex Receptacle	Base	Nylon
Type – 2 Pole, 3 Wire, Grounding	Triple Wipe Power Contacts	Brass
Rating – 15A, 125V	Mounting Strap	Galvanized Steel; Brass (HG)
Certification – UL Listed to UL 498	Automatic Self-Grounding Clip	Stainless Steel
Fed. Spec. WC596, Certified to CSA 22.2, No. 42	Flat Head Mounting Screws	Steel-Zinc Plated/Self Tapping

Connector	Contact	Connector Body	Wire
SNAP1RA	Brass	Clear Polycarbonate	6" Solid copper #12 AWG THHN/THWN-2 600V, T90 Nylon FT-1, PVC 90°C (min).
SNAP2RA	Brass	Clear Polycarbonate	6" Stranded copper #12 AWG THHN/THWN-2 600V, T90 Nylon FT-1, PVC 90°C (min).


Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V as rated.
Current Interrupting	Receptacle certified for current interrupting at full rated current with equivalently rated NEMA® plug.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated DC current.
Mechanical	
Terminal Wire Leads Identification	Terminal wire leads identified in accordance with UL 498 (Black, White, Green).
Product Identification	Ratings are a permanent part of the device.
Environmental – Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact).

Dimensions



NEMA® is a registered trademark of the National Electrical Manufacturers Association.



**Hubbell-PRO Heavy Duty, Straight Blade
Hospital Grade Duplex Receptacles**

Specifications

Receptacle	Part	Description
Typical Specification - Catalog No. 8200	Receptacle	15A
Manufacturer's Identification - Hubbell-PRO 8200	Top	Nylon
Description - Straight Blade Hospital Grade Duplex Receptacle	Base	Nylon
Type - 2 Pole, 3 Wire, Grounding	Triple Wipe Power Contacts	.0295 in. Brass
Rating - 15A, 125V (also 20A, 125V)	Clamping Plate	Plated Steel
Certification - UL Listed to UL 498, Fed. Spec. WC596	Mounting Strap	.040 in. Galvanized Steel
Hospital Grade, NEMA® WD-6 Compliant	Terminal Screws	Plated Steel
Certified to CSA	Hex Head Grounding Screw	Plated Steel
	Automatic Self-Grounding Staple	Stainless Steel
	Mounting Screws	Zinc Plated Steel

Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.
Environmental – Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



USB8300R

**USB Charger Tamper-Resistant, Straight Blade
Hospital Grade Duplex Receptacles**

Specifications

USB Charger Receptacle	Part	Description
Typical Specification - Catalog No. USB8300	Charger Receptacle	USB 3 Amp 5V DC, Electrical 15 or 20 Amp 125V AC
Manufacturer's Identification - Hubbell USB8300		
USB Charger	Ports	Type A, 2.0
	LED	Green Indicator
Receptacle	Top	Nylon
Description - Hospital Grade, Straight Blade Duplex Receptacle	Base	Nylon
Type - 2 Pole, 3 Wire, Grounding	Triple Wipe Power Contacts	.030 in. Cooper Alloy
Rating - 15 or 20 Amp, 125V AC, USB 3 Amp, 5V DC	Clamping Plate	Plated Steel
	Mounting Strap	.040 in. Galvanized Steel
Certification - cULus Listed to UL498 and UL1310	Terminal Screws	Plated Steel
Hospital Grade, NEMA® WD-6 Compliant (USB8200 and 8300 series only)	Hex Head Grounding Screw	Plated Steel
Complies with battery charging specification USB BC1.2	Automatic Self-Grounding Staple	Stainless Steel
Complies with Part 15 of the FCC rules	Mounting Screws	Zinc Plated Steel
Compatible with USB 1.1/2.0/3.0 devices, including Apple products		

Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.
Mechanical	
USB Port	Stainless Steel Rated for 10,000 plug insertions and removal
Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.
Circuit Feed-Through	20 Amp 125 Volt
Environmental - Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



HBL8215C



HBL8219C

**Insulgrip® Plugs and Connectors
Hospital Grade**

Specifications

Plug	Part	Description
Typical Specification—Catalog No. HBL8215C	Plug	15A
Manufacturer's Identification—Hubbell HBL8215C Plug	Housing	Nylon— Black
Description—Hospital Grade Straight Blade Plug	Blade Holder	Nylon— Natural
Type—2 Pole, 3 Wire, Grounding	Retainer	Polycarbonate—Clear
Rating— 15A, 125V	Cord Clamp	Nylon—Natural
Certification—UL Listed, CSA Certified	Contact Blades	.060 in. (1.5) Brass
UL Verified to Fed. Spec. WC596	Ground Contact Blade	.040 in. (1.0) Brass
IP Suitability—IP20	Line Terminal Screws	#8-32 Brass, Multiple Drive
	Ground Screw	#8-32 Brass, Multiple Drive (Green)
	Wire Clamps	.080 in. (2.0) Steel—Nickel Finish
Connector	Part	Description
Typical Specification—Catalog No. HBL8219	Connector	15A
Manufacturer's Identification—Hubbell HBL8219C Connector	Housing	Nylon—Black
Description—Hospital Grade Straight Blade Connector Body	Contact Holder	Nylon— Natural
Type—2 Pole, 3 Wire, Grounding	Retainer	Polycarbonate—Clear
Rating—15A, 125V	Cord Clamp	Nylon—Natural
Certification—UL Listed, CSA Certified	Contacts	.040 in. (1.0) Copper Alloy
UL Verified to Fed. Spec. WC596	Line Terminal Screws	#8-32 Brass, Multiple Drive
IP Suitability—IP20	Ground Screw	#8-32 Brass, Multiple Drive (Green)
	Wire Clamps	.080 in. (2.0) Steel—Nickel Finish

Performance

Electrical	
Dielectric Voltage	Withstands 2000V AC minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 100 cycles of overload at 150% of rated voltage DC.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL and CSA (Brass, White, and Green).
Terminal Accommodation	#18-10 AWG.
Product Identification	Ratings are a permanent part of the device.
Torque Range	Cord clamp/terminal screws 9 to 12 in-lbs.
Cord Diameter Range	.230"-.720" (5.8-18.3) Integral cord grip.
Environmental-Material	
Flammability	UL 94HB or better.
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)

Note: Please consult the factory for product dimensions and specifications for other products listed in this catalog.



HBL8115V



HBL8119V

**Valise® Plugs and Connectors
Hospital Grade**

Specifications

Plug	Part	Description
Typical Specification—Catalog No. HBL8115V	Plug	15A
Manufacturer's Identification—Hubbell HBL8115V Plug	Housing	Nylon
Description—Hospital Grade Straight Body Plug	Contact Blades	Brass
Type— 2 Pole, 3 Wire, Grounding	Ground Blade	Brass
Rating—15A, 125V	Terminal Screws	Multiple Drive
Certifications—UL Listed to UL498	Cable Inserts	Polyphenylene Oxide
File E1706, CSA Certified to C22.2	Terminal Clamps	Plated CR Steel
No. 42 File LR280. Fed. Spec. WC596	Body Holding Screws	Multiple Drive
IP Suitability—IP20		
Connector	Part	Description
Typical Specification—Catalog No. HBL8119V	Connector	15A
Manufacturer's Identifications—Hubbell HBL8119V Connector Body	Housing	Nylon
Description—Hospital Grade Straight Connector Body	Contact and Ground Spring	Brass
Type—2 Pole, 3 Wire, Grounding	Terminal Screws	Multiple Drive
Rating—15A, 125V	Cable Inserts	Polyphenylene Oxide
Certifications—UL Listed to UL498	Terminal Clamps	Plated CR Steel
File E1706, CSA Certified to C22.2	Body Holding Screws	Multiple Drive
No. 42 File LR280. Fed. Spec. WC596		
IP Suitability—IP20		

Performance

Electrical	
Dielectric Voltage	Withstands 2000V AC minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current Interrupting at full rated current.
Temperature Rise	Max. 30°C temperature rise at full rated current.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL and CSA (Brass, White, and Green)
Terminal Accommodation	#16 to #12 AWG.
Product Identification	Ratings are a permanent part of the device.
Torque	Terminal screws 12 in.-lbs. Cord clamp screws 7 to 10 in.-lbs.
Cord Diameter Range	.300" to .660" (7.6 to 16.8)
Environmental-Material	
Flammability	UL 94HB
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact).
Standards	
NEMA® Configurations WD6.	
Listed to UL Standard UL498 and UL Verified to Ped. Spec. WC596.	
Certified to CSA Standard C22.2 No. 42.	

NEMA® is a registered trademark of the National Electrical Manufacturers Association.