

2-2350891-1 ✓ ACTIVE

DEUTSCH | DEUTSCH NTSEAL


TE Internal #: 2-2350891-1

20 Position Housing, Housing for Male Terminals, Wire-to-Wire, 3.5 mm [.138 in] Centerline, Sealable, Black, Wire & Cable, Power, DEUTSCH NTSEAL

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Housings



Connector & Housing Type: **Housing for Male Terminals**

Number of Positions: **20**

Sealable: **Yes**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Number of Rows: **5**

Features

Product Type Features

Connector Shape	Rectangular
Mixed & Hybrid Connector	Yes
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	20
Number of Rows	5

Body Features

Primary Product Color	Black
Connector & Keying Code	A

Contact Features



Contact Size	Size 16, Size 20
Contact Type	Pin
Mating Pin Diameter	1 mm, 1.55 mm [.039 in][.061 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	3.5 mm [.138 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
Operating Temperature (Max)	125 °C [257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JAN 2025 (247)</p> <p>SVHC > Threshold:</p> <p>Dodecamethylcyclhexasiloxane (D6) (.5% in Component Part)</p> <p>Decamethylcyclopentasiloxane (D5) (.5% in Component Part)</p> <p>Octamethylcyclotetrasiloxane (D4) (.5% in Component Part)</p> <p>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>













Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-2350890-1 20POS, HYBRID, SOC HSG ASSY, SLD, COD A</p>	 <p>TE Part # 2373921-1 CVTY PLUG, PIN DIA 2.5, CVTY DIA, 2.5, GRY</p>	 <p>TE Part # 2373921-2 CVTY PLUG, PIN DIA 1.6, CVTY DIA, 1.9, YEL</p>	 <p>TE Part # 2350890-1 20POS, HYBRID, SOC HSG ASSY, SLD, COD A</p>
 <p>TE Part # 2350943-3 FIX RING, CONN KIT</p>	 <p>TE Part # 2357921-1 BACKSHELL, CONN KIT</p>	 <p>TE Part # 2350943-2 FIX RING, CONN KIT</p>	 <p>TE Part # 2357302-2 BACKSHELL, CONN KIT</p>
 <p>TE Part # 2350943-1 FIX RING, CONN KIT</p>	 <p>TE Part # 2350943-4 FIX RING, CONN KIT</p>		


Also in the Series | **DEUTSCH NTSEAL**



Automotive Housings(68)



Automotive Seals & Cavity Plugs(8)



Other Automotive Connector Accessories(7)

Customers Also Bought



TE Part #1743282-1
8POS MQS REC COD A



TE Part #2112046-2
COVER,90,FOR 26POS



TE Part #2213766-3
AV19 SPM 3A POWER LED WHITE 24V



TE Part #1-2350890-1
20POS,HYBRID,SOC HSG ASSY,SLD, COD A



TE Part #2357921-1
BACKSHELL,CONN KIT



TE Part #2366494-1
48POS,HYBRID,SOC HSG ASSY,SLD, COD A



TE Part #2-2366509-1
48POS,HYBRID,PIN HSG ASSY,SLD, COD A



TE Part #2366517-1
FIX RING,CONN KIT



TE Part #2378527-1
BACKSHELL,CONN KIT



TE Part #341352
ALTERNATOR CONN.HSG.BLACK

Documents

Product Drawings

[20POS,HYBRID,PIN HSG ASSY,SLD,COD A](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-2350891-1_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_2-2350891-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2350891-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NTSEAL Sealed Wire-to-Wire Connectors](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English