




DEUTSCH

TE Internal #: 5-2600020-2

Automotive Terminals, Pin, Pin Diameter 1.56 mm [.061 in],
Terminal Transmits 0 – 24 A (Low Power), 20 – 24AWG Wire Size,
Family Seal

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals



Terminal & Splice Type: Pin

Mating Pin Diameter: 1.56 mm [.061 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: 20 – 24 AWG

Sealable: No

Features

Product Type Features

Sealable	No
Primary Locking Feature	Clean Body
Automotive Terminal Wire Type	Copper
Insulated	Yes

Body Features

Automotive Terminal Seal Type	Family Seal
-------------------------------	-------------

Contact Features

Terminal & Splice Type	Pin
Mating Pin Diameter	1.56 mm [.061 in]
Automotive Terminal Interface Plating	Nickel (Ni)

Termination Features

Automotive Terminal Termination Method	F-Crimp
--	---------

Dimensions

--	--



Wire Size	20 – 24 AWG
Tab Length	9.2 mm[.362 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2837877-1
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 2-2837877-2
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 2-2837878-1
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 2-2837878-2
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 2-2837879-1
OCEAN-2.0-APPLICATOR-S-053F0800



TE Part # 2-2837879-2
OCEAN-2.0-APPLICATOR-S-053F0800



TE Part # 2837877-1
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 2837877-2
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 2837878-1
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 2837878-2
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 2837879-1
OCEAN-2.0-APPLICATOR-S-053F0800



TE Part # 2837879-2
OCEAN-2.0-APPLICATOR-S-053F0800



TE Part # 7-2837877-1
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 7-2837877-2
OCEAN-2.0-APPLICATOR-S-053F0730



TE Part # 7-2837877-7
OCEAN_2.0_SPARE_PART_KIT-053F0730



TE Part # 7-2837878-1
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 7-2837878-2
OCEAN-2.0-APPLICATOR-S-053F0750



TE Part # 7-2837878-7
OCEAN_2.0_SPARE_PART_KIT-053F0750



TE Part # 7-2837879-1
OCEAN-2.0-APPLICATOR-S-053F0800



TE Part # 7-2837879-2
OCEAN-2.0-APPLICATOR-S-053F0800

Customers Also Bought



TE Part #DT06-2S-P060
DEUTSCH DT Series Housings & Connectors



TE Part #5004-001-2405
DUST CAP, 24SZ, REC, BLK, HDBOX



TE Part #2500034-6
SRC Female Conduit Cover



TE Part #CAR2PC68-001
CAR PLUG DIN9680 2way, IP68



TE Part #DARS24296-000A3
CAR PIN STANDARD CONT. #5, silver plated



TE Part #DARS24924-000A3
CAR PIN CONT. #5, mod-001, silver plated



TE Part #DTSK06-1-08SB
PLUG, INLINE, KEY B



TE Part #HC5956
BATT.LEAD 90 DEG 70MM+VE.



TE Part #HC5957
BATT.LEAD 90 DEG 70MM-VE.



TE Part #SRK-PC-080-35-601
PIN, SOLID, SIZE M8, 35mm2, AG

Documents

Product Drawings

[XRC PIN TERMINAL 20-24AWG Ni Plated](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_5-2600020-2_1.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_5-2600020-2_1.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_5-2600020-2_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

845240032

Automotive Terminals, Pin, Pin Diameter 1.56 mm [.061 in], Terminal Transmits 0 – 24 A (Low Power), 20 – 24AWG Wire Size, Family Seal



Application Specification

English