

Datasheet

Item No. 25.181.7353.0

Printed circuit board terminal 8291 D / 3 / 9 Z OB

PCB Terminal Block, 3-tier, 9-pole, without marking, with insulation plate, pitch 5,08 mm, series: 8291 D/3/9 Z OB



Item No.	25.181.7353.0
EAN	4015573178595
order unit	50 Piece(s)

Approvals



Technical data

General

Modular spacing	5.08 mm
Connection type	Screw connection
Soldering process	Wave soldering
Number of poles	9
Conductor to circuit board	180°
Number of levels	3
Integrated test socket	Yes
Insulation plate	Yes
Retaining pins	No
Marking	No

Technical data

Nominal cross section	2.5 mm ²
Rated current	16 A
Overvoltage Category I	1000 V
Overvoltage Category II	690 V
Overvoltage Category III	250 V
Rated impulse voltage	4 kV

Connection Data

Wire strip length	6.5 mm
Minimum cross section solid	0.14 mm ²
Maximum cross section solid	4 mm ²
Minimum cross section fine stranded	0.14 mm ²
Maximum cross section fine stranded	2.5 mm ²

Technical Data UL/CSA

Cross section UL	22-12 AWG
Voltage UL	300
Current field wiring	20 A
Current factory wiring	30 A
Cross section CSA	22-12 AWG
Voltage CSA	300 V
Current CSA	25 A

Other

Type of insulation material	Thermoplastic
Colour	Grey
Height	41 mm
Length	17.78 mm
Depth	33.9 mm
Material attachment screw	Steel
Material contact base	E-Cu
Material contact surface	Sn