


LOB Series

Features

- Ultra low resistance values to 0.005Ω
- Up to 5W rated power
- Tolerances from ±1% to ±5%
- Inherently non-inductive (≤0.02μH at 0.5MHz)
- Low temperature coefficient of resistance
- High stability over life



✓ All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)


Electrical Data

			LOB-1	LOB-3	LOB-5
	Continuous power dissipation at 25°C in free air	watts	LOB-3	3	5
Power rating	Power dissipation for 5 seconds	watts	3 5	15	5
Overload power	Overload power for 1 second	watts	15 20	25	25
Resistance range	Maximum storage temperature	ohms °C	R005 to R120	175 R005 to R100	175
Standard values	* Power Dissipation - The maximum wattage rating depends upon the amount of heat which can be transferred to the surroundings while not exceeding the maximum element temperature. Ambient air temperature, velocity of cooling air, thermal resistance of heat and the temperature of surrounding objects will affect heat transfer, this must be taken into account when selecting a resistor.				
Maximum working voltage		volts	√3xR	√5xR	√5xR
Operating temperature		°C	-55 to 175	-55 to 175	-55 to 175

Note 1: To dissipate full rated power forced air cooling must be provided to restrict the maximum body temperature to 180°C.

Physical Data

Dimensions (mm)						
Type	L max	D max	f min	d nom	C	
LOB-1	14.9±0.3	3.6±0.2	38.1±3.2	0.81±0.05	33.27	
LOB-3	14.22±0.25	5.33±0.25	34.93±3.8	0.81±0.05	33.27	
LOB-5	23.37±0.25	8.38±0.25	31.75±3.8	1.02±0.05	42.42	
LOB-3	14.22±0.25	5.33±0.25	34.93±3.8	0.77±0.05	33.27	
LOB-5	23.37±0.25	8.38±0.25	31.75±3.8	1.02±0.05	42.42	



Description
LOB Series power precision metal element resistors feature resistance values down to 0.005 Ω with virtually no inductance. Available in 1, 3 and 5 watt rated axial leaded packages, these resistors are compatible with automatic insertion equipment.


Applications

- Switchmode and linear power supplies.
- Automotive current sensing circuits.
- Instrumentation.


Construction
LOB Series resistors feature tinned copper leads welded directly to a low temperature coefficient resistance element in a highly automated proprietary process. The leaded resistor elements are then encapsulated in a moulding compound.

LOB Series

Power derating percentage vs Free air ambient temperature



Temperature coefficient of resistance vs Resistance value



Performance Data


Test	MIL-STD 202	MAX %ΔR*	Unit
Load Life (1000 hours)	Method 108	±1%	%ΔR
Thermal Shock	Method 107	±1%	%ΔR
Vibration	Method 204	± 0.5%	%ΔR
Mechanical Shock	Method 213	± 0.5%	%ΔR
Dielectric strength	Method 301	± 0.5%	%ΔR
Insulation resistance	Method 302	> 10 ¹¹	ohms

*±0.005 ohm allowance for test/contact error.

Packaging

Resistors are supplied taped and reeled (see Ordering Procedure for reel quantities.) The taping dimensions are shown below.

Taping dimensions, inches (mm)			
Type	a max	b	c
LOB-3	0.031 (0.8)	2.5±0.031 (63.5±0.8)	0.4±0.015 (10.2±0.4)
LOB-5	0.031 (0.8)	2.5±0.031 (63.5±0.8)	0.4±0.015 (10.2±0.4)



$d1-d2 \leq 0.055 \text{ (1.4)}$

LOB Series

Ordering Procedure

This product has two valid part numbers:

European (Welwyn) Part Number: LOB3-R01JI (LOB3, 10 milliohms ±5%, Pb-free)

L	O	B	3	-	R	0	1	J	I	
1			2			3	4			

1	2	3	4	
Type	Value	Tolerance	Packing & Termination Finish	
LOB3	R = ohms	F* = ±1%	I = Standard packing & Pb-free	
LOB5		H = ±3%	PB = Standard packing & SnPb	
		J* = ±5%	LOB3	Taped, 1250/reel
		* preferred	LOB5	Taped, 800/reel

USA (IRC) Part Number: LOB-3R010FLFSLT (LOB3, 10 milliohms ±5%, Pb-free)

L	O	B	-	3	R	0	1	0	F	L	F	S	L	T
1				2				3	4	5				

1	2	3	4	5	
Type	Value	Tolerance	Termination Finish	Packing	
LOB-3	R = ohms	F = ±1%	Omit for SnPb	SLT = Lead Tape	
LOB-5		H = ±3%	LF = Pb-free	LOB-3	1250/reel
		J = ±5%		LOB-5	800/reel