

## Datasheet

Item No. 73.354.6435.0

Hood BAS GOT GC 64HM32 50 A0

revos BASIC 500V size 24H hood with cable gland M32, top cable entry, high design, double locking lever



Item No.	73.354.6435.0
EAN	4015573642027
order unit	1 Piece(s)

## Approvals



## Technical data

### General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	24H
Model	Plug
Locking mechanism	Double locking levers
Cable entry	Above
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	32
Hinged lid	No
EMC-version	No



Drawings

1  
2  
3  
4  
5  
6

A  
B  
C  
D  
E  
F

**Ausführung .0**  
version .0

Verschraubung M32  
screw connection M32

1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
1  
1.1  
2.1  
1.1

<p><b>Ausführung .1</b> version .1</p> <p>Gewinde M32 thread M32</p>	<p><b>Ausführung .2</b> version .2</p> <p>Stutzen M32 intermediate support M32</p>	<p><b>Ausführung .5</b> version .5</p> <p>Kabelverschraubung M32 cable gland M32 IP 65</p>
<p><b>Ausführung .3</b> version .3</p> <p>Kabeldurchführung M 32 mit Zugentlastung und Biegeschutz cable gland M32 with strain relief and behind protection</p>	<p><b>Ausführung .4</b> version .4</p> <p>Kabelverschraubung M32 mit Zugentlastung und Knickschutz cable gland M32 with strain relief and kink protection</p>	

**Teile - Nr.**  
part - no.

73.354.6435.0	BAS GOT GC 64HM32 50 A0
73.354.6435.1	BAS GOT GC 64HM32 50 A1
73.354.6435.2	BAS GOT GC 64HM32 50 A2
73.354.6435.3	BAS GOT GC 64HM32 50 A3
73.354.6435.4	BAS GOT GC 64HM32 50 A4
73.354.6435.5	BAS GOT GC 64HM32 50 A5

**Typ**  
type

**Weitere Daten siehe Katalog**  
further data see catalog

Fertigung nach DIN 7162/Envelope system etc. to DIN 7162.  
This DIN standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances.

Fräskennzeichnung  
General tolerance

2006	12.10.	Traschen	
Veränderung	First Use		

Zeichnung Nr./Drawing No. **73.354.6435.0 01K**

Made in mm/Dimensions are in mm

**wieland**  
Elektrotechnik  
Verbindungen

**GEHAUSE\_OBERTEIL**  
HOUSING UPPER PART  
Gr.64, M32, von oben / from above

UJ-PEH-05/91