

Datasheet

Item No. R1.188.0920.1

Two-hand control relay SNZ4052K AC 115- 120V(B)

Base unit, two-channel control, 2x N.C./N.O. startup inhibit circuit, cross circuit monitoring, synchronous time monitoring, 2 enabling current paths, 1 signalling output, AC 115-120 V 50-60Hz, screw terminals fixed



Item No.	R1.188.0920.1
EAN	4015573809642
order unit	1 Piece(s)

Approvals



Technical data

**General**

Suited for safety functions	Yes
Category according to EN 954-1	4
Feedback circuit	Yes
Start contact	No
Performance level acc. to EN ISO 13849-1	e
SIL according to IEC 62061	3
Rail mounting possible	Yes
Applicable in accordance with EN 574	Type III C

**Connection Data**

Detachable clamps	No
Type of electric connection	Screw connection

**Output circuit**

Outputs, signalling function, undelayed, with contact	1
Outputs, signalling function, delayed, with contact	0
Outputs, safe, undelayed, with contact	2
Outputs, safe, delayed, with contact	0

**Control circuit**

Type of switch function of the inputs	Change-over contact
---------------------------------------	---------------------

**Supply circuit**

Min. rated control supply voltage at AC 50 Hz	97.8 V
Max. rated AC voltage for controls, 50 Hz	132 V
Rated control supply voltage at AC 60HZ	97.8 V

Rated control supply voltage at AC 50HZ	132 V
---	-------

**Dimensions**

Depth	114 mm
Width	22.5 mm
Height	96.5 mm