


DASH NO: M CODE

MADE FROM

CONNECTOR: BNC FEMALE/MALE  
DC IMPEDANCE: 600Ω NOMINAL  
POWER RATING: 2 WATTS CW AT 25° C.



MATERIAL & FINISHES:  
 ALL METAL BODY PARTS: BRASS, 00-B-626, ALLOY 360  
 KINGS TARNISH RESISTANT FINISH (TR-5)  
 OUTER CONTACT: BERYLLIUM COPPER, 00-C-530, H.T.  
 KINGS TARNISH RESISTANT FINISH (TR-5)  
 INSULATORS: TEFLON, MIL-P-19468  
 GASKET: SILICONE RUBBER, ZZ-R-765  
 MALE CENTER CONTACT: BRASS, 00-B-626, ALLOY 360  
 HARD GOLD PLATE 00005 MIN.  
 FEMALE CENTER CONTACT: BERYLLIUM COPPER, 00-C-530, H.T.  
 HARD GOLD PLATE 00005 MIN.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010
2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX.
3. PLACE DECIMALS ± .004
3. NO FILETS PERMITTED
4. ANGLES 4:0° 30'
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.
- EXCEED HALF THE SUM OF THEIR TOLERANCES.

REVISIONS

ISSUE	CHANGES
0.	ER 18548 4 AUG 78
1	CN 22754 C GL 13 NOV 81
2.	CN 26335-A GT 17 AUG 84

USED ON:

REF:

FINISH:

SPEC:

MATL:

SPEC:

BNC 600Ω 2 WATT  
TERMINATION M-A

DRAWN MJB DATE 15 JUN 78

APPR SML DATE 15 JUNE 78

KINGS ELECTRONICS  
40 MARBLEDALE ROAD  
TUCKAHOE, N. Y. 10707

1340-5-9

ESD