




- NOTES:
1. FOR USE WITH BOEING BMS13-65 DJ & ADAMS RUSSELL FC38Z CABLES.
 2. FOR CABLING INSTRUCTIONS SEE 3-546-2.
 3. FOR CRIMPING USE DIE KTH-2213.
 4. INTERFACE PER MIL-STD-348, FIG. 304-1.
 5. MARK PACKAGE: KINGS 1206-26-9 YRWK (DATE CODE)
 6. CENTER CONTACT (1-534-87MA9) SUPPLIED UNASSEMBLED.
 7. MATERIALS:
 - INSULATORS: TEFLON, ASTM-D-1710
 - GASKET: SIL. RUB. A-A-59598
 - K-GRIP SLEEVE: COM. BRONZE, ALLOY ASTM B135
 - OUTER CONTACT: C-RING: PHOS. BRONZE, ASTM-B-103
 - CRIMP CONTACT: BER. COP. ASTM-B-196
 - ALL OTHER PARTS: BRASS, ASTM-B16
 8. FINISHES:
 - CONTACTS: .00050 MIN GOLD PLATE, PER ASTM-B-488 OVER .00050 MIN NICKEL, PER AMS-QQ-N-290 (RoHS)
 - OUTER CONTACT: .000200 MIN SILVER PER ASTM-B-700 OVER .000020 MIN COPPER PER ASTM B734 (RoHS)
 - ALL OTHER METAL PARTS: .000050 MIN NICKEL PER AMS-QQ-N-290 OVER .000050 MIN COPPER PER ASTM B734 (RoHS)
 9. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: 50 OHMS
 - VOLTAGE RATING: 1000 VRMS
 - FREQUENCY RANGE: DC TO 11 GHz
 10. WEIGHT: 76.6 GRAM

REVISIONS	
ISSUE	CHANGES
0	ER 35256 JCA 12/16/93
1	CN 35739 A MJB 08/10/94
2	CN 38322 E TML 06/15/01
D	REVISED PER DMF304 & ER34270 CY 09/02/11

CUSTOMER
SALES DRAWING

THIS DRAWING, THE DESIGNS AND IDEAS EMBODIED IN THE DEVICE TO WHICH IT RELATES, AND THE METHOD OF PRODUCING THE DEVICE, ARE THE PROPERTY OF WINCHESTER ELECTRONICS CORPORATION AND SHALL NOT BE EMPLOYED, COPIED, OR DISCLOSED TO ANYONE, IN ANY MANNER WITHOUT THE CONSENT OF WINCHESTER ELECTRONICS CORPORATION.

SCALE 4:1

APPROX SURFACE AREA

WAS: E-18166

CAGE CODE: 91836

REF: BOEING

PLUG, ANGLE, N

DRAWN	JCA	DATE	04/26/93
DESIGN	JT	DATE	04/27/93
APPR.		DATE	

WINCHESTER
by WINCHESTER

Winchester Electronics
62 Borneo Industrial
Helmfield, CT 06442

B
SIZE

1206-26-9