



SECTION: A-A  
SCALE: 1:1



SECTION: B-B  
SCALE: 1:1



SECTION: C-C  
SCALE: 1:1

NOTE:

1. Stamping before plating
2. Mated with 10114826 housing
3. Product numbering:

Part No	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
10114827-001LF	AWG#28-#32	1.00mm(max)	Phosphor Bronze	Matte Tin-plated	20,000pcs
10114827-002LF	AWG#28-#32	1.00mm(max)	Phosphor Bronze	Gold-flash	20,000pcs
10114827-003LF	AWG#28-#32	1.00mm(max)	Phosphor Bronze	Gold: 15u"	20,000pcs
10114827-004LF	AWG#28-#32	1.00mm(max)	Phosphor Bronze	Gold: 30u"	20,000pcs



mat'l. code		surface		tolerance		projection		product family			
		ISO 1302 ✓		ISO 406 ISO 1101				FitMate			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title			
C	ELX-N-36746	Jason	2020/04/15	angles	.X±.25	← mm →		WTB 1.25MM TERMINAL			
D	ELX-N-43687	YS	2022/01/14	linear	.XX±.15						
E	ELX-N-47289	JH	2023/02/15	0°±x'	.XXX±.10	scale 4:1					
G	ELX-N-55541	CP	2025/04/22	dr	Jason HSU	2010/12/01			dwg no		
				eng	Jason Wang	2020/04/16			sheet 1 of 1		
				chr	-	-			10114827		
				appd	TIM YAO	2020/04/16			size		
										A3	
										type Product Customer Drawing	
sheet	revision	G									
index	sheet	1									