


SD

KH-59-84

REVISIONS

ISSUE	CHANGES
0	ER 17756 GA 11/10/77
1	CN 29865 A LI 05/23/88
2	CN 39208 E REDRAWN HVN 01/10/05
3	CN 39307 B JLA 07/27/05
4	CN 39383 E DRK 01/04/06



NOTES:

1. FOR USE WITH RG-393/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-1031.
3. INTERFACE PER MIL-STD-348, FIG. 317-1.
4. MATERIALS:
 INSULATORS: TEFLON, L-P-403
 GASKETS: SILICONE RUBBER, ZZ-R-765
 C-RING: PHOSPHOR BRONZE, QQ-B-750
 OUTER CONTACT } BER. COPPER, QQ-C-530
 CENTER CONTACT F }
 ALL OTHER METAL PARTS: BRASS, QQ-B-626
5. FINISHES:
 ALL METAL PARTS: BRIGHT SILVER PLATE, PER QQ-S-365
6. ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 1500 VRMS
 FREQUENCY RANGE: DC TO 4 GHz.

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF: MCDONNELL DOUGLAS, STSM1333-002

PLUG, ANGLE, HN

DRAWN GINO	DATE 10/25/77
DESIGN LI	DATE 10/25/77
APPR.	DATE

KINGS
 ELECTRONICS CO., INC.
 ROCK HILL, SOUTH CAROLINA 29730

KH-59-84

SD