


DASH NO. M CODE MADE FROM



NOTES:

1. FOR USE WITH RG-215/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-1608.
3. MATERIALS:
 - INSULATORS - TEFLON, L-P-403.
 - GASKETS - SILICONE RUBBER, ZZ-R-765.
 - FLAT WASHER - BRASS, QQ-B-613.
 - WASHER - COPPER, QQ-C-576.
 - C-RING } PHOSPHOR BRONZE, QQ-B-750.
 - OUTER CONTACT }
 - ALL OTHER PARTS - BRASS, QQ-B-626.
4. FINISHES:
 - CENTER CONTACT - .0001 HARD GOLD PLATE PER MIL-G-45204.
 - EXCEPT C-RING, ALL OTHER METAL PARTS - SILVER PLATE .0002 MIN. PER QQ-S-3654.

5. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: 50Ω.
 - FREQUENCY RANGE: DC TO 11 GHz.
 - WORKING VOLTAGE: 1000 V RMS.

M39012/01-0125

REVISIONS	
ISSUE	CHANGES
1	CN 23169 E JEP 13 APR 82
2	CN 26215 D EAT 28 JUN 84
3	CN 32243 A LNM 1 JUN 90

SCALE:	
KU-59-296	
USED ON:	
REF:	
N-PLUG	
DRAWN: CKC	DATE: 28 SEP 79
APPR: MJB	DATE: 28 SEP 79
 <small>KINGS ELECTRONICS CO., INC. TECHNOLOGY, NEW YORK 10107</small>	
M39012/01-0125	

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010	2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3 PLACE DECIMALS ± .004	3. NO FILLETS PERMITTED
ANGLES ± 0°30'	4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.	5. ALL DIMENSIONS PRIOR TO PLATING.
	6. ALL PLATING IN ACCORDANCE WITH KER 10004