



Switches > Push Button Switches > Emergency Stop Switch, 1 Actuator, Flush, Threaded Bushing



Configuration (Pole-Throw): **Single Pole - Single Throw**
Push Button Switch Product Type: **Emergency Stop Switch**
Number of Actuators: **Single**
Actuator Profile: **Flush**
Bushing Style: **Threaded**

[All Emergency Stop Switch, 1 Actuator, Flush, Threaded Bushing \(34\)](#)

Features

Product Type Features

Push Button Switch Product Type	Emergency Stop Switch
Illuminated	Without
Actuator Style	Round Actuator

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	With
Support Bracket	Without
Switch Feedback Type	Non-Tactile
Operating Function	Maintained

Electrical Characteristics

Contact Current Rating	8 A
Operating Voltage Range	9 – 32 VDC

Body Features

Actuator Force	2040 – 5100 g[72 – 180 oz]
Actuator Profile	Flush



Bushing Style	Threaded
Actuator Color	Red

Contact Features

Switch Contact Plating Material	Silver Alloy
---------------------------------	--------------

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 26179688775) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Pb (3.5% in Component Part) Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts


 TE Part # K1070300 Emerg. Mainswitch 1000A TYP 24-01-00-904	 TE Part # K1022851 Adapter Typ 26-57-51	 TE Part # CAT-AL8-STPBSS Push Button Switch, Socket, 1 Actuator, Flush Profile	 TE Part # K1147734 Plunger Switch 44-03-006
 TE Part # K1122917 Limit switch G13-01-1629	 TE Part # K1138349 Emergency Power Switch Type 24-05-02	 TE Part # K1165897 Foot Switch 44-03-028	 TE Part # K1123113 Limit switch G13-01-1631
 TE Part # K1133413 Limit switch G13-01-1700	 TE Part # K1158023 Actuation Protection 24-63-029 BX	 TE Part # K1125644 Limit switch G13-01-1643	 TE Part # K1153104 Safety Cap TS-2 06-63-170
 TE Part # K1050108 Limit switch G13-01-1536	 TE Part # K1166669 Foot Switch 44-03-008-1	 TE Part # CAT-AL8-STPBSC Push Button Switch, Center Thread, 1 Actuator, Flush Profile	 TE Part # CAT-AL8-KSEESS Emergency Stop Switch, 1 Actuator, Flush, Threaded Bushing



Also in the Series | **KISSLING Series ES**



Customers Also Bought



Documents

Product Drawings

Emergency Switch ES-2010-T312-018G

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ES-2010-T312-018G_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ES-2010-T312-018G_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ES-2010-T312-018G_1.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KISSLING E-STOP Series ES

English