

280-020P panel mount pin connectors with O-ring mounting flange, crimp termination



Rear panel mount HiPer-D® pin connectors feature crimp, rear-releaseable size #20 or #22 contacts and O-ring for a watertight panel seal. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D® features a rugged machined aluminum shell, environmental sealing and optional ground springs for improved resistance to electromagnetic interference. #4-40 threaded mounting holes simplify panel attachment. Threaded holes on the rear of the connector allow attachment of HiPer-D® EMI backshells. Contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone face seal and rear grommet meet IP67 immersion requirement (mated). 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

Ordering Information					
Sample Part Number		280-020P	3H44	JF	G P
Basic Part Number	280-020P				
Shell Size-Contact Arrangement	See Shell Size - Contact Arrangements Table				
Shell Finish	ME = Electroless Nickel JF = Cadmium with Yellow Chromate Z1 = Passivated Stainless Steel MT = Nickel-PTFE Z2 = Gold				
Ground Spring	G = Supplied with EMI Ground Spring N = No Ground Spring				
Mating Hardware	N = No Hardware (supplied with #8-32 tapped holes) G = Male Guide Pins P = #4-40 Female Jackposts B = Female Guide Bushings				

Shell Size - Contact Arrangements		
Shell Size-Contact Arr.	Contact Size and Qty	
	#20	#22
Standard Density		
1S9	9	
2S15	15	
3S25	25	
4S37	37	
5S50	50	
High Density		
1H15		15
2H26		26
3H44		44
4H62		62
5H78		78
6H104		104


Mating Hardware	
N No Hardware #8-32 tapped hole 	P #4-40 Female Jackposts
B Female Guide Bushings 	G Male Guide Pins

Materials and Finishes	
Shell	Aluminum alloy
Contacts	Copper alloy, 50 microin. gold plated
Insulators	Thermoset epoxy
Retention Clips	Beryllium copper alloy
O-ring, Grommet, Seal	Fluorosilicone rubber
EMI Spring	Copper alloy, nickel plated
Hardware	300 series stainless steel

Specifications	
Current Rating	#22 5 AMPS, #20 7.5 AMPS
Test Voltage	1000 VAC RMS
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +200° C.
Ingress Protection	IP 67
Shock	300 g.
Vibration, Random	43.92 g.

280-020P panel mount pin connectors with O-ring mounting flange, crimp termination

280-020P DIMENSIONS



Shell Size	A		B		C Basic		D		E		F Basic		G		H	
	in ±.015	mm ± 0.38	in ±.015	mm ± 0.38	in. ±.005	mm ± 0.13	in ±.005	mm ± 0.13	in ±.005	mm ± 0.13	in ±.015	mm ± 0.38	in ±.015	mm ± 0.38	in ±.015	mm ± 0.38
1	1.865	47.37	.725	18.42	.984	24.99	.726	18.44	.389	9.88	1.424	36.17	.469	11.91	1.609	40.87
2	2.200	55.88	.725	18.42	1.312	33.32	1.054	26.77	.389	9.88	1.752	44.50	.469	11.91	1.944	49.38
3	2.736	69.49	.725	18.42	1.852	47.04	1.594	40.49	.389	9.88	2.292	58.22	.469	11.91	2.480	62.99
4	3.385	85.98	.725	18.42	2.500	63.50	2.242	56.95	.389	9.88	2.940	74.68	.469	11.91	3.129	79.48
5	3.289	83.54	.837	21.26	2.406	61.11	2.139	54.33	.501	12.73	2.846	72.29	.581	14.76	3.033	77.04
6	3.383	85.93	.899	22.83	2.500	63.50	2.272	57.71	.563	14.30	2.940	74.68	.643	16.33	3.127	79.43

NOTES

- HiPer-D® connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D® Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
- For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
- Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Crimp Tools](#) for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
- HiPer-D® connectors meet the requirements of MIL-DTL-24308 and are interchangeable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
- Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).