


LTR	REVISION	DATE	APPD
C	021624-GZ01: REMOVED RoHS FROM DRAWING. 080924-NM01: UPDATED OPERATING TEMPERATURE	08-13-24	NM



NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. LENS MATERIAL / COLOR: UV POLYCARBONATE / CLEAR
3. SLEEVE MATERIAL: RYNITE FR530
4. ~~BASE MATERIAL: NICKEL PLATED BRASS~~
BBL508002-CUST
5. AMBIENT OPERATING TEMPERATURE RANGE: ~-22°F to ~+122°F [~-30°C to ~+50°C]
6. WEIGHT: 0.21 lbs. / 3.4 oz.

REVISION NOTIFICATION	
<input type="checkbox"/>	DLC
<input type="checkbox"/>	UL/ETL
<input type="checkbox"/>	MADE IN USA
<input type="checkbox"/>	CUSTOMER _____
<input type="checkbox"/>	OTHER _____
REDLINE CHECKLIST	
<input type="checkbox"/>	REDLINE(YES)
<input type="checkbox"/>	DATE: _____
<input type="checkbox"/>	INITIATED BY: _____
<input type="checkbox"/>	ECR REQUIRED YES <input type="checkbox"/> NO <input type="checkbox"/>
<input type="checkbox"/>	WORK ORDER# _____

ELECTRICAL-OPTICAL CHARACTERISTICS (Ta = 25°C)

BBL508-01-02	SUPER RED	120Vac	3.6 W	0.040-0.065 A	-	110 lm	633
BBL508-04-02	SUPER YELLOW	120Vac	3.6 W	0.040-0.065 A	-	78 lm	595
LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V	POWER (W)	CURRENT (A)	LIGHT OUTPUT PER LED Iv, CD	TOTAL LUMENS	λP nm

 LEDTRONICS,™ INC. 23105 KASHIWA COURT TORRANCE, CA 90505	-PROPRIETARY- This document contains Proprietary Information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.		TITLE BBL508-0X-02					
	.XXX ± .010 TOLERANCE PER ANSI-Y14.5 .XX ± .025 (UNLESS OTHERWISE STATED) ANGLES ± 0°,30' FRACT. ± 1/32		DWG NO BBL508002-CUST	SCALE 1:1	SHEET 1 OF 1	DATE 06-08-05		
	CODE IDENT NO. 8Z410	DWG BY RM 06-08-05	CHK BY	QA LUV 08-14-24	MFG PP 08-14-24	R&D UF 08-15-24		