



ISSUE DATE:



PLPVC142

NOTES:
 1.) MATERIAL WILL BE TYPE I PVC
 2.) ALL TOLERANCES TO BE ±.015 UNLESS OTHERWISE NOTED
 3.) MAXIMUM OPERATING TEMPERATURE TO BE 140° F.



PART No. 14PVC1311
 for more information visit www.hammfg.com
 Data subject to change without notice
 Drawing Not to Scale