



Quality Products. Service Excellence.

Desktop or Wall Rack 1459 Series

150 lbs|68 kg Weight Capacity



Note: This product line will soon be discontinued as a stocked series. Available while quantities last. It has been replaced with **RB-2PW Series**. For alternative solution assistance, please **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



Features

- Constructed in 16-gauge steel.
- EIA-310-D compliant front 19" mounting rails with starter pack of (50) 10-32 tapped clip nuts and screws.
- Suitable for desktop or wall mounting applications.
- Welded open frame includes:
 - Removable top & bottom panels.
 - Optional side panels sold separately.
- Rubber feet included for table mounting.
- Desktop tested to nearly double the suggested load rating of 800 lbs (363 kg).
- Wall Mount tested to nearly double the suggested load rating of 150 lbs (68 kg).
- Finished in textured black powder paint.
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.



Accessories

- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Adjustable Rack Mount DIN Rail Kit
- Outlet Strips
- Rack Panels
- Rack Unit Label
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 10-32 Mounting Screw and Clip Nut Combo-Pack
- Hinged Clear Security Cover
- Cable Management



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Optional Side Panels (Sold in Pairs)	Product Replacement
	Height	Width	Depth		Height	Width	Depth		
1459FBK1	24.70	21.12	16.14	13U	22.75	19.00	16.14	-	RB-2PW12
1459JBK1	35.20	21.12	16.14	19U	33.25	19.00	16.14	-	RB-2PW20
1459MBK1	49.20	21.12	16.14	27U	47.25	19.00	16.14	1459MQBK1	HWMR1924UBK
1459M24BK1	49.20	21.12	24.14	27U	47.25	19.00	24.14	1459M24QBK1	HWMR1924UBK

Tags: Relay Rack, H-Frame, Server Rack, Equipment Rack, SmartRack, Network Rack

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.