



LTR	REVISION	DATE	APPD
-	RELEASED	01-30-20	



ACTUAL SIZE



NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. MOUNTING DIAMETER: Ø5/32" [4.0mm]
3. SLEEVE MATERIAL / COLOR: NYLON 66 / BLACK
4. ALL PARTS WITH (*) ARE "RoHS" CERTIFIED.

REVISION NOTIFICATION	
<input type="checkbox"/>	DLC
<input type="checkbox"/>	UL/ETL
<input type="checkbox"/>	MADE IN USA
<input type="checkbox"/>	CUSTOMER _____
<input type="checkbox"/>	OTHER _____
REDLINE CHECKLIST	
<input type="checkbox"/>	REDLINE(YES)
<input type="checkbox"/>	DATE: _____
<input type="checkbox"/>	INITIATED BY: _____
<input type="checkbox"/>	ECR REQUIRED YES <input type="checkbox"/> NO <input type="checkbox"/>
<input type="checkbox"/>	WORK ORDER# _____

ELECTRICAL-OPTICAL CHARACTERISTICS (Ta = 25°C)

PP156TG4-0007	PP156TG4-2VF-T	HI-EFF GREEN	GREEN DIFFUSED	20	2.0/2.6	15 mcd	568nm	45°
PP156TR4-0006 *	PP156TR4-2VF-T	HI-EFF RED	RED DIFFUSED	20	2.0/2.6	35 mcd	642nm	45°
LEDTRONICS PART NO.	DESCRIPTION PART NO.	COLOR EMITTED	LENS COLOR	If, mA (typ)	Vf, V (typ)/(max)	LUMINOUS INTENSITY	λP nm	VIEWING ANGLE (FULL BEAM WIDTH @ 50% INTENSITY)



-PROPRIETARY-
 This document contains Proprietary information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.

.XXX ± .010 TOLERANCE PER ANSI-Y14.5
 .XX ± .025 (UNLESS OTHERWISE STATED)
 ANGLES ± 0°,30'
 FRACT. ± 1/32

TITLE							
PP156TX4-000X (PP156TX4-2VF-T)							
DWG NO		SCALE		SHEET		DATE	
PP156-2V-T		2:1		1 OF 1		01-30-20	
CODE IDENT NO.	DWG BY GP	CHK BY	QA SB	MFG LD	R&D UF		
8Z410	01-30-20		01-31-20	01-31-20	01-31-20		