



23105 Kashiwa Court, Torrance, CA 90505
Phone: (800) 579-4875 or (310) 534-1505 Fax: (310) 534-1424
E-mail: info@ledtronics.com
Website: http://www.ledtronics.com

SML080CWAG3K-031

Aqua Green

Axial Surface Mount LEDs

2.7×2.2×2.1mm, Z-bend leads

35° Viewing Angle

DWG BY:
BL / GP / HF
01-30-07

R&D:
PL
06-11-25

MFG
PP
06-11-25

QA:
LUV
06-11-25

REVISION LTR: B
ECR#: 061125-HF01
06-11-25


● **Features:**

1. Emitted Color: Aqua Green
2. Lens Appearance: Water Clear
3. This product doesn't contain restriction Substance, comply ROHS standard.

● **Applications:**

1. Backlighting: LCDs, Key pads advertising.
2. Status indicators: Consumer & industrial electronics.
3. General use.

● **Package Dimensions**



● **Absolute Maximum Ratings (Ta=25°C)**

| Parameter | Symbol | Rating | Unit |
|-------------------------|-----------------|--------------|------|
| Power Dissipation | Pd | 70 | mW |
| Forward Current | I _F | 20 | mA |
| Peak Forward Current *1 | I _{FP} | 100 | mA |
| Reverse Voltage | V _R | 5 | V |
| Operating Temperature | Topr | -40 °C~85 °C | - |
| Storage Temperature | Tstg | -40 °C~85 °C | - |
| Soldering Temperature | Tsol | See Page 6 | - |

* 1 Condition for I_{Fp} is pulse of 1/10 duty and 0.1msec width.

● **Electrical and Optical Characteristics (Ta=25°C)**

| Parameter | Symbol | Condition | Min. | Typ. | Max. | Min. |
|----------------------|-------------------|----------------------|------|-------|------|------|
| Forward Voltage | V _f | I _F =20mA | - | 3.2 | 3.6 | V |
| Luminous Intensity | I _v | I _F =20mA | - | 16000 | - | mcd |
| Reverse Current | I _R | V _R =5V | - | - | 1 | μA |
| Peak Wave Length | λ _p | I _F =20mA | - | 520 | - | nm |
| Dominant Wave Length | λ _d | I _F =20mA | 520 | - | 535 | nm |
| Viewing Angle | 2θ _{1/2} | I _F =20mA | - | 35 | - | deg |

● **Typical Electro-Optical Characteristics Curves**

Fig.1 Relative intensity vs. wavelength




Fig.2 Forward current derating curve vs. ambient temperature




Fig.3 Forward current vs. forward voltage




Fig.4 Relative luminous intensity vs. ambient temperature




Fig.5 Relative luminous intensity vs. forward current






Fig.6 Radiation diagram



● **Taping and packaging specifications (Units: mm)**
Quantity: 1,500 pcs./reel



● **Notes for designing:**

Care must be taken to provide the current limiting resistor in the circuit so as to drive the LEDs within the rated figures. Also, caution should be taken not to overload LEDs with instantaneous voltage at the turning ON and OFF of the circuit.

When using the pulse drive care must be taken to keep the average current within the rated figures. Also, the circuit should be designed so as to be subjected to reverse voltage when turning off the LEDs.

● **Storage:**

In order to avoid the absorption of moisture, it is recommended to solder LEDs as soon as possible after unpacking the sealed envelope.

If the envelope is still packed, to store it in the environment as following:

- (1) Temperature : 5°C-30°C(41°F) Humidity : RH 60% Max.
- (2) After this bag is opened, devices that will be applied to infrared reflow, vapor-phase reflow, or equivalent soldering process must be:
 - a. Completed within 168 hours.
 - b. Stored at less than 30% RH.
- (3) Devices require baking before mounting, if:
 - (2) a or (2) b is not met.
- (4) If baking is required, devices must be baked under below conditions:
 - 48 hours at 60°C ± 3°C.

● **Package and Label of Products:**

- (1) Package: Products are packed in one bag of 1500 pcs.(one taping reel) and a label is attached on each bag.

● Reliability Test

| Classification | Test Item | Reference Standard | Test Conditions | Result |
|--------------------|--|--|---|--------|
| Endurance Test | Operation Life | MIL-STD-750D:1026 MIL-STD-883D:1005 JIS-C-7021 :B-1 | Ta: Under room temperature Test time:1,000hrs IF=Product Recommended IF | 0/32 |
| | High Temperature High Humidity Storage | MIL-STD-202F:103B JIS-C-7021 :B-11 | Ta:85±5°C RH:90%-95% Test time:240hrs | 0/32 |
| | High Temperature Storage | MIL-STD-883:1008 JIS-C-7021 :B-10 | Ta:100±5°C Test time:1,000hrs | 0/32 |
| | Low Temperature Storage | JIS-C-7021 :B-11 | Ta: -45±5°C Test time=1,000hrs | 0/32 |
| Environmental Test | Temperature Cycling | MIL-STD-202F:107D MIL-STD-750D:1051 MIL-STD-883D:1010 JIS-C-7021 :A-2 | Ta:-35±5°C~25±5°C~85±5°C~25±5°C 30min 5min 30min 5min | 0/32 |
| | Thermal Shock | MIL-STD-202F:107D(1980) MIL-STD-750D:1051(1995) MIL-STD-883D:1011(1991) | Ta:-45±5°C ~+85±5°C 20min 20 min Time: 40min/cycle 10cycle | 0/32 |
| | Wetting balance | MIL-STD-883:2003 MIL-STD-202F:208D MIL-STD-883D:2003 | Ta:230±5°C Time:5±0.5s | 0/32 |
| | Solder Resistance | MIL-STD-202F:210A MIL-STD-883D:1011 JIS-C-7021 :A-1 | Ta:260±10°C Time:10±1s | 0/32 |


● Judgment criteria of failure for the reliability

| Measuring items | Symbol | Measuring conditions | Judgement criteria for failure |
|--------------------|--------------------|----------------------|--------------------------------|
| Forward voltage | V_F (V) | $I_F=20\text{mA}$ | Initial Level*1.1 |
| Reverse current | $I_R(\mu\text{A})$ | $V_R=5\text{V}$ | Over U*2 |
| Luminous intensity | I_v (mcd) | $I_F=20\text{mA}$ | Initial Level*0.7 |

Note: 1.U means the upper limit of specified characteristics.

2. Measurement shall be taken between 2 hours and after the test pieces have been returned to normal ambient conditions after completion of each test.

● **IR-Reflow Soldering**



| Profile Feature | Symbol | Pb-Free (SnAgCu) Assembly | | | Unit |
|---|--------|---------------------------|----------------|---------|------|
| | | Minimum | Recommendation | Maximum | |
| Ramp-up rate to preheat ¹⁾ 25 °C to 150 °C | | | 2 | 3 | K/s |
| Time t_s T_{Smin} to T_{Smax} | t_s | 60 | 100 | 120 | s |
| Ramp-up rate to peak ²⁾ T_{Smax} to T_p | | | 2 | 3 | K/s |
| Liquidus temperature | T_L | | 217 | | °C |
| Time above liquidus temperature | t_L | | 80 | 100 | s |
| Peak temperature | T_p | | 245 | 260 | °C |
| Time within 5 °C of the specified peak temperature $T_p - 5$ K | t_p | 10 | 20 | 30 | s |
| Ramp-down rate* T_p to 100 °C | | | 3 | 6 | K/s |
| Time 25 °C to T_p | | | | 480 | s |

All temperatures refer to the center of the package, measured on the top of the component
* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

1. Avoid any external stress applied to the resin while the LEDs are at high temperature, especially during soldering.
2. Avoid rapid cooling or any excess vibration during temperature ramp-down process.
3. Although the soldering condition is recommended above, soldering at the lowest possible temperature is feasible for the LEDs.

● **IRON Soldering**

350°C Within 3 sec., One time only.