



LTR	REVISION	DATE	APPD
B	022822-UF01: ADDED EXTERNAL SERIES RESISTOR TABLE	03-01-22	HF



ACTUAL SIZE



**NOTES:**

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. LENS MATERIAL / COLOR: POLYCARBONATE-UV STABILIZED. (UL94V-2) / CLEAR
3. SLEEVE MATERIAL: GENERAL POLYMERS RYNITE FR530 (UL 94HB)
4. BASE MATERIAL: (BODY) BRASS & NICKEL PLATED BRASS (BARREL)

\*\*FULL BEAM WIDTH @ 50% INTENSITY

REVISION NOTIFICATION	
<input type="checkbox"/>	DLC
<input type="checkbox"/>	UL/ETL
<input type="checkbox"/>	MADE IN USA
<input type="checkbox"/>	CUSTOMER _____
<input type="checkbox"/>	OTHER
REDLINE CHECKLIST	
<input type="checkbox"/>	REDLINE(YES)
<input type="checkbox"/>	DATE: _____
<input type="checkbox"/>	INITIATED BY: _____
<input type="checkbox"/>	ECR REQUIRED YES <input type="checkbox"/> NO <input type="checkbox"/>
<input type="checkbox"/>	WORK ORDER# _____

ELECTRICAL - OPTICAL CHARACTERISTICS (Ta = 25°C)

LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V	POWER (W)	CURRENT (A)	MAXIMUM CANDELA	λP nm COLOR TEMP. (K)	VIEWING ANGLE**
UTL1819-0AG	AQUA GREEN	24Vdc	0.31 W	0.013 A	7.150cd	522nm	26°
UTL1819-0CW	COOL WHITE	24Vdc	0.31 W	0.013 A	11.700cd	8000K	30°
UTL1819-0IW	WARM WHITE	24Vdc	0.31 W	0.013 A	5.200cd	3000K	37°
UTL1819-0UB	SUPER BLUE	24Vdc	0.31 W	0.013 A	1.950cd	463nm	25°
UTL1819-0UO	SUPER ORANGE	24Vdc	0.41 W	0.017 A	1.955cd	610nm	30°
UTL1819-0UR	SUPER RED	24Vdc	0.41 W	0.017 A	2.550cd	633nm	25°
UTL1819-0UY	SUPER YELLOW	24Vdc	0.41 W	0.017 A	4.420cd	593nm	20°

**(WHEN USED IN ET5, ET6 AND ET16 UTILITY LAMP HOLDERS)**

LEDTRONICS PART NO.	COLOR EMITTED	CIRCUIT RATING VOLTS	CIRCUIT VOLTAGE		EXTERNAL SERIES RESISTOR (Ω)	INCANDESCENT LAMP NUMBER	INCANDESCENT LAMP VOLTAGE RATING
			MIN.	MAX.			
UTL1819-0AG	AQUA GREEN	24VDC	22	28	10	1819	28V
UTL1819-0CW	COOL WHITE						
UTL1819-0IW	WARM WHITE						
UTL1819-0UB	SUPER BLUE						
UTL1819-0UO	SUPER ORANGE						
UTL1819-0UR	SUPER RED						
UTL1819-0UY	SUPER YELLOW						

 LEDTRONICS,™ INC. 23105 KASHIWA COURT TORRANCE, CA 90505	-PROPRIETARY- This document contains Proprietary Information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.	<b>TITLE</b> UTL1819-0XX					
	.XXX ± .010 TOLERANCE PER ANSI-Y14.5 .XX ± .025 (UNLESS OTHERWISE STATED) ANGLES ± 0°,30' FRACT. ± 1/32	<b>DWG NO</b> UTL1819-CUST	<b>SCALE</b> 2:1	<b>SHEET</b> 1 OF 1	<b>DATE</b> 01-04-10		
	<b>CODE IDENT NO.</b> 8Z410	<b>DWG BY GP</b> 01-04-10	<b>CHK BY</b>	<b>QA SB</b> 03-02-22	<b>MFG LD</b> 03-02-22	<b>R&amp;D UF</b> 03-02-22	