



UPC Code: 07847712583

Country Of Origin: Please Contact Customer Service.

## 530MI7W

30 Amp, 277/480 Volt 3PY, IEC 309-1 & 309-2, 4P, 5W, Mechanical Interlock North American Pin & Sleeve Receptacle, Hub Sold Separately (See Leviton Cat Number HUB-xxx), Industrial Grade, IP67, Watertight, Non-Fused - RED

### Technical Information

AC Horsepower Ratings

**At Rated Voltage:** 20 HP

Electrical Specifications

**Amperage:** 30 A

**Current Interrupting:** Certified for current interrupting at full rated current

**Dielectric Voltage:** 1000 V plus rated voltage for 1-minute

**Endurance:** 6,000 cycles inductive motor type load

**Phase:** 3-Phase WYE

**Pole:** 4

**Voltage:** 277/480 VAC

**Wire:** 5

Environmental Specifications

**Dust:** Type 12K per UL 50

**Flammability:** Rated V-0 per UL 94

**Gasket Aging:** 70C for 168 hours

**Hosedown:** Type 4X per UL 50

**IP Rating:** IP67/IP69K

**Operating Temperature:** -40°C to 60°C

**Rain:** Type 3R per UL 50

**UV Resistance:** Exposed plastic materials are UV stabilized

Material Specifications

**Actuator Material:** Zinc-Coated Steel

**Conduit Grounding Plate:** Zinc-Coated Steel

**Contact Carrier:** Nylon

**Cover Eyelet:** Nickel-Plated Brass

**Cover with Arm:** Valox 357

**Gasket Material:** Chloroprene

**Ground Contacts:** Brass

**Handle Material:** Valox 357

**Housing Material:** Valox 357

**Housing Screws:** Stainless Steel

**Internal Screws:** Zinc-plated steel

**Locking Mechanism:** Valox 357

**Locking Ring:** Valox 357

**Phase and Ground Sleeves:** Brass

**Switch Contacts:** Cadmium-Free Silver Alloy

**Switch Material:** Reinforced Nylon

**Switch Terminal Contacts:** Brass

Mechanical Specifications

**Cold Impact:** Same as above, after conditioning to -35C

**Crush Test:** 100 lbs

**Impact:** 1.2 lb ball dropped from 5 ft

**Mold Stress Relief:** 70°C for 7 hours

**Pullout:** 18 lb pull on internal wires

**Strength of Insulating Base and Support:** 110% of specified tightening torque on terminal screws

Product Features

**Color:** Red

**Configuration:** North American

**Device Type:** Mechanical Interlock

Standards and Certifications

**CE Marking:** Per low voltage directives 73/23/EEC, 93/68/EEC



**CSA:** C22.2

**IEC Rating:** 60309-1 and 60309-2

**UL:** 231 & 1686

**UL 508:** Non-Fused

**Warranty:** 2-Year Limited



**SPECIFICATION SUBMITTAL**

JOB NAME: <input style="width: 95%; height: 20px;" type="text"/>	CATALOG NUMBERS: <input style="width: 95%; height: 20px;" type="text"/>
JOB NUMBER: <input style="width: 95%; height: 20px;" type="text"/>	<input style="width: 95%; height: 20px;" type="text"/>

**Leviton Manufacturing Co., Inc.**  
 201 North Service Road, Melville, NY 11747  
 Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):  
 +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**  
 165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·  
 FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**  
 Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-  
 1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)  
 © 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**  
 If you would like to know where your local Leviton office is located please go to:  
[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

