

SECTION AA' (20/1)

SECTION BB' (20/1)

TABLE 1


PART NO.	PLATING	
	CONTACT AREA	OTHERWISE
LPC-F103 ()	GOLD 2 μ m OVER NICKEL 1~2 μ m	NICKEL 1~2 μ m
LPC-F104 ()	TIN 0.8~1.2 μ m OVER COPPER 1 μ m	

TABLE 2

PART NO.	COMPATIBLE WIRE	
	CORE WIRE	INSULATION DIA. RANGE
LPC-F10 () S	AWG#32	0.6
LPC-F10 () N	AWG#28~32	0.7~1.0
LPC-F10 () L	AWG#22~26	0.9~1.1

TABLE 3

PART NO.	E	F	G	H
LPC-F10 () S	1.3	1.3	1.4	1.3
LPC-F10 () N	1.3	1.3	1.4	1.7
LPC-F10 () L	1.8	1.8	1.5	2.1



NOTE1. AS FOR THE SPEC, SEE TABLE #2, #3.

2. CONTINUOUS TERMINAL FOR AUTOMATIC CRIMPING MACHINE.
(10000PCS/REEL)

△3										
△2										
△	APR.05.2005	T. O	REVISE		CONTACT	PHOSPHOR BRONZE	10000	SEE TABLE #1		
LTR.	DATE	BY	REV. DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE	
	DATE		SCALE	UNIT	3RD. A. P	HONDA TSUSHIN KOGYO CO., LTD.				
	APR.30 (1997)		10/1	mm (INCH)						
	APP. DATE&REV.									
DR.	DE.	CHK.	CHK.	APP.	NAME	FEMALE CONTACT				
T. ODA	T. ODA	—	C. NUNOKAWA	H. EBIHARA	PART NO.	LPC-F10 () ()				REV. 1A