



## Index

Product	Page
<b>HBL® Extra Heavy Duty Hospital Grade Duplex Receptacles</b>	
Features and Benefits . . . . .	L-2
Duplex and Style Line® Decorator . . . . .	L-3
SNAPConnect® Receptacles . . . . .	L-4
Hubbell-PRO Receptacles . . . . .	L-7
USB Charger Receptacle . . . . .	L-9
Single and 4-PLEX® Receptacles . . . . .	L-9
<b>Hospital Grade Plugs, Connector Bodies and Receptacles</b>	
15 and 20A, 125V . . . . .	L-10
15 and 20A, 250V . . . . .	L-11
<b>Extra Heavy Duty Industrial GFCI Receptacles</b> . . . . .	L-12
<b>Commercial GFCI Receptacles</b>	
Tamper-Resistant . . . . .	L-13
Standard . . . . .	L-14
Tamper-Resistant and Weather Resistant . . . . .	L-15
<b>Hospital Grade Surge Protection Devices</b> . . . . .	L-16
<b>Hubbellock® Plugs, Connectors and Receptacles</b> . . . . .	L-17
<b>Hubbellock® Mobile X-Ray Devices</b> . . . . .	L-18
<b>Technical Information</b> . . . . .	L-19

### HBL® Extra Heavy Duty Industrial Series



### Industrial and Commercial Series GFCIs




### Surge Protection Devices



### Hubbellock® Receptacles, Plugs and Connectors





**HBL8200GY**

## Hubbell “Hospital Grade” Devices

To qualify for the “Hospital Grade” designation and use of the associated green dot symbol, UL requires that the manufacturer design its devices to perform to specific levels. These levels form an established baseline below which no manufacturer can fall and still carry a green dot.

Hubbell sets their standards high. Each product is built to withstand the severe conditions of abuse that are unique to the hospital environment. Hubbell receptacles have exclusive design features that set them apart from the competition.

- Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature.
- Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas.
- High tech reinforced thermoplastic polyester (RTP) back is tough and heat resistant.

Because of these features and others, the benefit is performance, reliability, and value for any health care facility.



One piece, nickel plated brass mounting strap with integral ground contacts, along with secondary ground contact, provides superior grounding for low resistance flow of fault currents as well as corrosion resistance. Barbed locking arms keep the face locked in place to diminish potential for face/base separation. Back wired ground screw reduces installation time.



Exclusive bypass contacts are made of nickel-plated brass alloy. This design increases blade retention forces, insuring a reliable uninterrupted flow of power.



Reinforced thermoplastic back provides superior thermal, electrical and mechanical properties. By providing contact stability, this high performance material will reduce heat buildup giving you long lasting performance.



External wiring clamps allow for visual inspection of the terminals. A unique strand containment feature on the terminal “bundles” the wire, ensuring 100% clamping of wire strands and reducing heat from the termination.



**IP20**  
 SUITABILITY



**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP




**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP


## HBL® Extra Heavy Duty Hospital Grade Receptacles

### Duplex


Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back and side wired.	Black	<b>HBL8200BK</b>	-
	Blue	-	<b>HBL8300BL</b>
	Brown	<b>HBL8200</b>	<b>HBL8300</b>
	Gray	<b>HBL8200GY</b>	<b>HBL8300GY</b>
	Ivory	<b>HBL8200I</b>	<b>HBL8300I</b>
	Light Almond	<b>HBL8200LA</b>	<b>HBL8300LA</b>
	Red	<b>HBL8200RED</b>	<b>HBL8300RED</b>
	White	<b>HBL8200W</b>	<b>HBL8300W</b>
Flush, LED illuminated face, back and side wired.	Gray	<b>HBL8200ILGY</b>	<b>HBL8300ILGY</b>
	Ivory	<b>HBL8200ILI</b>	<b>HBL8300ILI</b>
	Red	<b>HBL8200ILR</b>	<b>HBL8300ILR</b>
	White	<b>HBL8200ILW</b>	<b>HBL8300ILW</b>
Tamper-Resistant receptacle with wire leads. Complies with requirements of NEC® article 517-18(c).	Brown	<b>HBL8200SGA</b>	<b>HBL8300SGA</b>
	Gray	<b>HBL8200SGGYA</b>	<b>HBL8300SGGYA</b>
	Ivory	<b>HBL8200SGIA</b>	<b>HBL8300SGIA</b>
	Light Almond	<b>HBL8200SGLA</b>	<b>HBL8300SGLA</b>
	Red	<b>HBL8200SGRA</b>	<b>HBL8300SGRA</b>
	White	<b>HBL8200SGWA</b>	<b>HBL8300SGWA</b>
Isolated ground <sup>A</sup> .	Orange	<b>IG8200</b>	<b>IG8300</b>
	Red	<b>IG8200R</b>	<b>IG8300R</b>




**HBL8200GY**




**HBL8300SGA**



**HBL8300RMRI**



**HBL8200ILW**



**HBL2172**

### MRI Receptacle, Duplex

Description	Color	Catalog Number	
MRI receptacle, flush, thermoplastic polyester face, back and side wired.	Ivory	<b>HBL8200IMRI</b>	<b>HBL8300IMRI</b>
	Light Almond	<b>HBL8200LAMRI</b>	<b>HBL8300LAMRI</b>
	Red	<b>HBL8200RMRI</b>	<b>HBL8300RMRI</b>
	White	<b>HBL8200WMRI</b>	<b>HBL8300WMRI</b>

### Slender/Compact, Duplex

Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back, and side wired. Fed. Spec. verified.	Brown	<b>HBL8200H</b>	<b>HBL8300H</b>
	Gray	<b>HBL8200HG</b>	<b>HBL8300HG</b>
	Green	-	<b>HBL8300HGN</b>
	Ivory	<b>HBL8200HI</b>	<b>HBL8300HI</b>
	Light Almond	<b>HBL8200HLA</b>	<b>HBL8300HLA</b>
	Red	<b>HBL8200HRED</b>	<b>HBL8300HRED</b>
	White	<b>HBL8200HW</b>	<b>HBL8300HW</b>

### Style Line® Decorator\*

Description	Color	Catalog Number	
Flush, nylon face, back and side wired.	Brown	<b>HBL2172</b>	<b>HBL2182</b>
	Gray	<b>HBL2172GY</b>	<b>HBL2182GY</b>
	Ivory	<b>HBL2172I</b>	<b>HBL2182I</b>
	Office White	-	<b>HBL2182OW</b>
	Red	<b>HBL2172R</b>	<b>HBL2182R</b>
	White	<b>HBL2172WA</b>	<b>HBL2182WA</b>
Isolated ground <sup>A</sup> .	Ivory	-	<b>IG2182I</b>
	Orange	-	<b>IG2182</b>
	White	-	<b>IG2182WA</b>

Note: <sup>A</sup>See section M for additional information on isolated ground devices.

\*Not Fed. Spec. Listed.

See pages A-48 and A-49 for accessories.

See page L-19 for technical information.

See page Tech-10 for Tamper-Resistant description.

See section N for wallplates.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).

Dimensions in Inches (mm)



**IP20**  
 SUITABILITY






**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP

## Extra Heavy Duty Hospital Grade ● SNAPConnect®

### Duplex

Description	Color	Catalog Number	
Hospital grade, finder groove, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA*.	Black	<b>SNAP8200BKA*</b>	<b>SNAP8300BKA*</b>
	Brown	<b>SNAP8200A*</b>	<b>SNAP8300A*</b>
	Gray	<b>SNAP8200GYA*</b>	<b>SNAP8300GYA*</b>
	Ivory	<b>SNAP8200IA*</b>	<b>SNAP8300IA*</b>
	Light Almond	<b>SNAP8200LAA*</b>	<b>SNAP8300LAA*</b>
	Red	<b>SNAP8200RA*</b>	<b>SNAP8300RA*</b>
	White	<b>SNAP8200WA*</b>	<b>SNAP8300WA*</b>
 Hospital grade, Tamper-Resistant, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP8200BKTR</b>	<b>SNAP8300BKTR</b>
	Brown	<b>SNAP8200TR</b>	<b>SNAP8300TR</b>
	Gray	<b>SNAP8200GYTR</b>	<b>SNAP8300GYTR</b>
	Ivory	<b>SNAP8200ITR</b>	<b>SNAP8300ITR</b>
	Light Almond	<b>SNAP8200LATR</b>	<b>SNAP8300LATR</b>
	Red	<b>SNAP8200RTR</b>	<b>SNAP8300RTR</b>
	White	<b>SNAP8200WTR</b>	<b>SNAP8300WTR</b>
Isolated ground <sup>A</sup> , Hospital grade, Tamper-Resistant.	Orange	<b>SNAP8200IGTR</b>	<b>SNAP8300IGTR</b>
	Red	<b>SNAP8200RIGTR</b>	<b>SNAP8300RIGTR</b>
 Hospital grade, with Power Indicating LED, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP8200BKL</b>	<b>SNAP8300BKL</b>
	Brown	<b>SNAP8200L</b>	<b>SNAP8300L</b>
	Gray	<b>SNAP8200GYL</b>	<b>SNAP8300GYL</b>
	Ivory	<b>SNAP8200IL</b>	<b>SNAP8300IL</b>
	Light Almond	<b>SNAP8200LAL</b>	<b>SNAP8300LAL</b>
	Red	<b>SNAP8200RL</b>	<b>SNAP8300RL</b>
	White	<b>SNAP8200WL</b>	<b>SNAP8300WL</b>
Isolated ground <sup>A</sup> , Hospital grade, with Power Indicating LED.	Orange	<b>SNAP8200IGL</b>	<b>SNAP8300IGL</b>
	Red	<b>SNAP8200RIGL</b>	<b>SNAP8300RIGL</b>
  Hospital grade, Tamper-Resistant, with Power Indicating LED, smooth nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP8200BKLTR</b>	<b>SNAP8300BKLTR</b>
	Brown	<b>SNAP8200LTR</b>	<b>SNAP8300LTR</b>
	Gray	<b>SNAP8200GYLTR</b>	<b>SNAP8300GYLTR</b>
	Ivory	<b>SNAP8200ILTR</b>	<b>SNAP8300ILTR</b>
	Light Almond	<b>SNAP8200LALTR</b>	<b>SNAP8300LALTR</b>
	Red	<b>SNAP8200RLTR</b>	<b>SNAP8300RLTR</b>
	White	<b>SNAP8200WLTR</b>	<b>SNAP8300WLTR</b>
Isolated ground <sup>A</sup> , Hospital grade, TR with Power Indicating LED.	Orange	<b>SNAP8200IGLTR</b>	<b>SNAP8300IGLTR</b>
	Red	<b>SNAP8200RIGLTR</b>	<b>SNAP8300RIGLTR</b>


Note: <sup>A</sup>See section M additional information on isolated ground devices.  
 See page A-15 for additional information on SNAPConnect® features.  
 See pages A-48 and A-49 for accessories.  
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.  
 See page L-20 for technical information.  
 See section N for wallplates.  
 Consult factory for available Split-Circuit capable SNAPConnect® devices.

### SNAPConnect® Right Angle Pigtailed Connector


Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material	Solid	<b>SNAP1RA</b>	<b>SNAP1RNA</b>
	Stranded	<b>SNAP2RA</b>	<b>SNAP2RNA</b>

Note: For Assembled in USA products, must order connector with NA suffix.  
 See page L-20 for technical information.


**Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**




SNAP8300WA




SNAP8300LATR



SNAP8300L



SNAP8300RLTR



SNAP1RA

Dimensions in Inches (mm)

Straight Blade Devices  
**15 and 20 Ampere, 125 Volts**  
 2 Pole, 3 Wire Grounding



**IP20**  
SUITABILITY



**15A 125V**  
NEMA 5-15R  
UL CSA  
0.5 HP



**20A 125V**  
NEMA 5-20R  
UL CSA  
1 HP

**Extra Heavy Duty  
 Hospital Grade ● SNAPConnect®**

**Style Line® Decorator**


Description	Color	Catalog Number	
Hospital grade, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA*.	Black	<b>SNAP2172BKA*</b>	<b>SNAP2182BKA*</b>
	Brown	<b>SNAP2172A*</b>	<b>SNAP2182A*</b>
	Gray	<b>SNAP2172GYA*</b>	<b>SNAP2182GYA*</b>
	Ivory	<b>SNAP2172IA*</b>	<b>SNAP2182IA*</b>
	Light Almond	<b>SNAP2172LAA*</b>	<b>SNAP2182LAA*</b>
	Red	<b>SNAP2172RA*</b>	<b>SNAP2182RA*</b>
	White	<b>SNAP2172WA*</b>	<b>SNAP2182WA*</b>
Hospital grade, Tamper-Resistant, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP2172BKTR</b>	<b>SNAP2182BKTR</b>
	Brown	<b>SNAP2172TR</b>	<b>SNAP2182TR</b>
	Gray	<b>SNAP2172GYTR</b>	<b>SNAP2182GYTR</b>
	Ivory	<b>SNAP2172ITR</b>	<b>SNAP2182ITR</b>
	Light Almond	<b>SNAP2172LATR</b>	<b>SNAP2182LATR</b>
	Red	<b>SNAP2172RTR</b>	<b>SNAP2182RTR</b>
	White	<b>SNAP2172WTR</b>	<b>SNAP2182WTR</b>
Isolated ground <sup>A</sup> , Hospital grade, Tamper-Resistant.	Orange	<b>SNAP2172IGTR</b>	<b>SNAP2182IGTR</b>
	Red	<b>SNAP2172RIGTR</b>	<b>SNAP2182RIGTR</b>
Hospital grade, with Power Indicating LED, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP2172BKL</b>	<b>SNAP2182BKL</b>
	Brown	<b>SNAP2172L</b>	<b>SNAP2182L</b>
	Gray	<b>SNAP2172GYL</b>	<b>SNAP2182GYL</b>
	Ivory	<b>SNAP2172IL</b>	<b>SNAP2182IL</b>
	Light Almond	<b>SNAP2172LAL</b>	<b>SNAP2182LAL</b>
	Red	<b>SNAP2172RL</b>	<b>SNAP2182RL</b>
	White	<b>SNAP2172WL</b>	<b>SNAP2182WL</b>
Isolated ground <sup>A</sup> , Hospital grade, with Power Indicating LED.	Orange	<b>SNAP2172IGL</b>	<b>SNAP2182IGL</b>
	Red	<b>SNAP2172RIGL</b>	<b>SNAP2182RIGL</b>
Hospital grade, Tamper-Resistant, with Power Indicating LED, Style Line® decorator, flush, nylon face, modular receptacle which requires pigtailed connector below. Assembled in USA.	Black	<b>SNAP2172BKLTR</b>	<b>SNAP2182BKLTR</b>
	Brown	<b>SNAP2172LTR</b>	<b>SNAP2182LTR</b>
	Gray	<b>SNAP2172GYLTR</b>	<b>SNAP2182GYLTR</b>
	Ivory	<b>SNAP2172ILTR</b>	<b>SNAP2182ILTR</b>
	Light Almond	<b>SNAP2172LALTR</b>	<b>SNAP2182LALTR</b>
	Red	<b>SNAP2172RLTR</b>	<b>SNAP2182RLTR</b>
	White	<b>SNAP2172WLTR</b>	<b>SNAP2182WLTR</b>
Isolated ground <sup>A</sup> , Hospital grade, TR with Power Indicating LED.	Orange	<b>SNAP2172IGLTR</b>	<b>SNAP2182IGLTR</b>
	Red	<b>SNAP2172RIGLTR</b>	<b>SNAP2182RIGLTR</b>

Note: <sup>A</sup>See section M additional information on isolated ground devices.  
 See page A-15 for additional information on SNAPConnect® features.  
 See pages A-48 and A-49 for accessories.  
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.  
 See page L-20 for technical information.  
 See section N for wallplates.  
 Consult factory for available Split-Circuit capable SNAPConnect® devices.


**SNAPConnect® Right Angle Pigtailed Connector**

Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material	Solid	<b>SNAP1RA</b>	<b>SNAP1RNA</b>
	Stranded	<b>SNAP2RA</b>	<b>SNAP2RNA</b>


Note: For Assembled in USA products, must order connector with NA suffix.  
 See page L-20 for technical information.




**SNAP2182A**



**SNAP2182ITR**



**SNAP2182RL**



**SNAP2182GYLTR**



**SNAP1RA**

Dimensions in Inches (mm)

**Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**



Fed.Spec.


Meets UL  
 Standard 943  
 Class A GFCI



**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP




**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP



**GFRST83SNAPR**

**SNAPConnect® GFCI LED Hospital Grade ●, Assembled in USA**

Description	Rating	Color	Catalog Number	
Hospital Grade SNAPConnect GFCI LED, self-grounding staple, requires connector below, sold separately.	15 and 20A 125V AC	Almond	<b>GFRST82SNAPAL</b>	<b>GFRST83SNAPAL</b>
		Black	<b>GFRST82SNAPBK</b>	<b>GFRST83SNAPBK</b>
		Brown	<b>GFRST82SNAP</b>	<b>GFRST83SNAP</b>
		Gray	<b>GFRST82SNAPGY</b>	<b>GFRST83SNAPGY</b>
		Ivory	<b>GFRST82SNAPI</b>	<b>GFRST83SNAPI</b>
		Light Almond	<b>GFRST82SNAPLA</b>	<b>GFRST83SNAPLA</b>
		Red	<b>GFRST82SNAPR</b>	<b>GFRST83SNAPR</b>
		White	<b>GFRST82SNAPW</b>	<b>GFRST83SNAPW</b>




**GFTWRST83SNAPI**

**SNAPConnect® GFCI LED Hospital Grade ●, Tamper and Weather Resistant, Assembled in USA**



Description	Rating	Color	Catalog Number	
Hospital Grade SNAPConnect GFCI TR/WR, self-grounding staple, requires connector below, sold separately.	15 and 20A 125V AC	Almond	<b>GFTWRST82SNAPAL</b>	<b>GFTWRST83SNAPAL</b>
		Black	<b>GFTWRST82SNAPBK</b>	<b>GFTWRST83SNAPBK</b>
		Brown	<b>GFTWRST82SNAP</b>	<b>GFTWRST83SNAP</b>
		Gray	<b>GFTWRST82SNAPGY</b>	<b>GFTWRST83SNAPGY</b>
		Ivory	<b>GFTWRST82SNAPI</b>	<b>GFTWRST83SNAPI</b>
		Light Almond	<b>GFTWRST82SNAPLA</b>	<b>GFTWRST83SNAPLA</b>
		Red	<b>GFTWRST82SNAPR</b>	<b>GFTWRST83SNAPR</b>
		White	<b>GFTWRST82SNAPW</b>	<b>GFTWRST83SNAPW</b>



**SNAP8300USBW**

**SNAPConnect® USB Charger Hospital Grade ●, Duplex Receptacles**




**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP



Description	Color	Catalog Number	
Hospital Grade SNAPConnect USB Charger, Tamper-Resistant Style Line® decorator duplex receptacle, two USB type 2.0 ports 3 Amp, 5 Volt DC, 15 or 20 Amp, 125 Volt AC.	Black	<b>SNAP8200USBBK</b>	<b>SNAP8300USBBK</b>
	Brown	<b>SNAP8200USB</b>	<b>SNAP8300USB</b>
	Gray	<b>SNAP8200USBGY</b>	<b>SNAP8300USBGY</b>
	Ivory	<b>SNAP8200USBI</b>	<b>SNAP8300USBI</b>
	Light Almond	<b>SNAP8200USBLA</b>	<b>SNAP8300USBLA</b>
	Red	<b>SNAP8200USBR</b>	<b>SNAP8300USBR</b>
	White	<b>SNAP8200USBW</b>	<b>SNAP8300USBW</b>



**SNAP8262S**

**SNAPConnect® Surge Protection Hospital Grade ●, Tamper-Resistant Receptacle with Power Indicating LED**




**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP



Description	Color	Catalog Number	
Hospital Grade SNAPConnect Surge suppression, Tamper-Resistant, smooth face, duplex receptacle.	Blue	<b>SNAP8262S</b>	<b>SNAP8362S</b>
	Gray	<b>SNAP8262GYS</b>	<b>SNAP8362GYS</b>
	Ivory	<b>SNAP8262IS</b>	<b>SNAP8362IS</b>
	Light Almond	<b>SNAP8262LAS</b>	<b>SNAP8362LAS</b>
	Red	<b>SNAP8262RS</b>	<b>SNAP8362RS</b>
	White	<b>SNAP8262WS</b>	<b>SNAP8362WS</b>



**SNAP1RA**

**SNAPConnect® Right Angle Pigtailed Terminal**

Description	Wire Type	General Use Catalog Number	Assembled in USA Catalog Number
Clear right angle terminal with 6 inch leads, 600V, #12 AWG THHN/THWN-2, Polycarbonate housing material.	Solid	<b>SNAP1RA</b>	<b>SNAP1RNA</b>
	Stranded	<b>SNAP2RA</b>	<b>SNAP2RNA</b>


Note: See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.  
 See page M-19 for SNAPConnect® technical information.

Dimensions in Inches (mm)

Hospital Products  
**15 and 20 Ampere, 125 Volts**  
 2 Pole, 3 Wire Grounding



**Hubbell-PRO Features**




**8200REDLTRA**

**Hubbell-PRO Heavy Duty Hospital Grade ● Receptacles**




**Duplex**


Description	Color	Catalog Number	
Hospital grade, smooth nylon face, back and side wired. Assembled in USA.	Black	<b>8200BK</b>	<b>8300BK</b>
	Brown	<b>8200</b>	<b>8300</b>
	Gray	<b>8200GY</b>	<b>8300GY</b>
	Ivory	<b>8200IV</b>	<b>8300IV</b>
	Light Almond	<b>8200LA</b>	<b>8300LA</b>
	Red	<b>8200RED</b>	<b>8300RED</b>
	White	<b>8200WHI</b>	<b>8300WHI</b>
Hospital grade, Tamper-Resistant, smooth nylon face, back and side wired. Assembled in USA.	Black	<b>8200BKTR</b>	<b>8300BKTRA</b>
	Brown	<b>8200TR</b>	<b>8300TRA</b>
	Gray	<b>8200GYTR</b>	<b>8300GYTRA</b>
	Ivory	<b>8200IVTR</b>	<b>8300IVTRA</b>
	Light Almond	<b>8200LATR</b>	<b>8300LATRA</b>
	Red	<b>8200REDTR</b>	<b>8300REDTRA</b>
	White	<b>8200WTR</b>	<b>8300WTRA</b>
Hospital grade, with Power Indicating LED, smooth nylon face, back and side wired. Assembled in USA.	Black	<b>8200BKL</b>	<b>8300BKL</b>
	Brown	<b>8200L</b>	<b>8300L</b>
	Gray	<b>8200GYL</b>	<b>8300GYL</b>
	Ivory	<b>8200IVL</b>	<b>8300IVL</b>
	Light Almond	<b>8200LAL</b>	<b>8300LALM</b>
	Red	<b>8200REDL</b>	<b>8300REDL</b>
	White	<b>8200WL</b>	<b>8300WL</b>
Hospital grade, Tamper-Resistant, with Power Indicating LED, smooth nylon face, back and side wired. Assembled in USA.	Black	<b>8200BKLTR</b>	<b>8300BKLTRA</b>
	Brown	<b>8200LTR</b>	<b>8300LTRA</b>
	Gray	<b>8200GYLTR</b>	<b>8300GYLTRA</b>
	Ivory	<b>8200IVLTR</b>	<b>8300IVLTRA</b>
	Light Almond	<b>8200LALTR</b>	<b>8300LALTRA</b>
	Red	<b>8200REDLTR</b>	<b>8300REDLTRA</b>
	White	<b>8200WLTR</b>	<b>8300WLTRA</b>



**8200LA**



**8200TRA**




**8200REDLTRA**

Dimensions in Inches (mm)


Note: See pages A-48 and A-49 for accessories.  
 See page L-21 for technical information.  
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.  
 See section N for wallplates.

**The products listed on this page are Assembled in USA, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**




**Hubbell-PRO Features**


**2182IVLTRA**



**2172LATRA**




**2172L**



**2182IVLTRA**

Dimensions in Inches (mm)

**Hubbell-PRO Heavy Duty  
 Hospital Grade ● Receptacles**



**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



**20A 125V**  
 NEMA 5-20R  
 UL CSA  
 1 HP

**Style Line® Decorator**

Description	Color	Catalog Number	
Hospital grade, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	<b>2172BK</b>	<b>2182BK</b>
	Brown	<b>2172</b>	<b>2182</b>
	Gray	<b>2172GY</b>	<b>2182GY</b>
	Ivory	<b>2172IV</b>	<b>2182IV</b>
	Light Almond	<b>2172LA</b>	<b>2182LA</b>
	Red	<b>2172RED</b>	<b>2182RED</b>
Hospital grade, Tamper-Resistant, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	<b>2172BKTR</b>	<b>2182BKTRA</b>
	Brown	<b>2172TR</b>	<b>2182TRA</b>
	Gray	<b>2172GYTR</b>	<b>2182GYTRA</b>
	Ivory	<b>2172IVTR</b>	<b>2182IVTRA</b>
	Light Almond	<b>2172LATR</b>	<b>2182LATRA</b>
	Red	<b>2172REDTR</b>	<b>2182REDTRA</b>
Hospital grade, with Power Indicating LED, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	<b>2172BKL</b>	<b>2182BKL</b>
	Brown	<b>2172L</b>	<b>2182L</b>
	Gray	<b>2172GYL</b>	<b>2182GYL</b>
	Ivory	<b>2172IVL</b>	<b>2182IVL</b>
	Light Almond	<b>2172LAL</b>	<b>2182LAL</b>
	Red	<b>2172REDL</b>	<b>2182REDL</b>
Hospital grade, Tamper-Resistant, with Power Indicating LED, Style Line® decorator, flush, nylon face, back and side wired. Assembled in USA.	Black	<b>2172BKLTR</b>	<b>2182BKLTRA</b>
	Brown	<b>2172LTR</b>	<b>2182LTRA</b>
	Gray	<b>2172GYLTR</b>	<b>2182GYLTRA</b>
	Ivory	<b>2172IVLTR</b>	<b>2182IVLTRA</b>
	Light Almond	<b>2172LALTR</b>	<b>2182LALTRA</b>
	Red	<b>2172REDLTR</b>	<b>2182REDLTRA</b>
White	<b>2172WLTR</b>	<b>2182WLTRA</b>	

Note: See pages A-48 and A-49 for accessories.  
 See page L-21 for technical information.  
 See page Tech-10 for Tamper-Resistant and LED Power Indicators description.  
 See section N for wallplates.

**The products listed on this page are Assembled in USA, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**



## USB Charger Tamper-Resistant Hospital Grade Receptacles




15A 125V  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



20A 125V  
 NEMA 5-20R  
 UL CSA  
 1 HP

Description	Color	Catalog Number	
USB Charger Tamper-Resistant receptacle, Two USB Type 2.0 ports 3.8 Amp, 5 Volt DC, 15 or 20 Amp, 125 Volt AC decorator duplex.	Black	<b>USB8200BK</b>	<b>USB8300BK</b>
	Brown	<b>USB8200</b>	<b>USB8300</b>
	Gray	<b>USB8200GY</b>	<b>USB8300GY</b>
	Ivory	<b>USB8200I</b>	<b>USB8300I</b>
	Light Almond	<b>USB8200LA</b>	<b>USB8300LA</b>
	Red	<b>USB8200R</b>	<b>USB8300R</b>
	White	<b>USB8200W</b>	<b>USB8300W</b>



USB8300W

Note: See page A-20 for standard USB charger.  
 See page Tech-10 for Tamper-Resistant description.

## HBL® Extra Heavy Duty Hospital Grade Single Receptacles

**IP20**  
 SUITABILITY




15A 125V  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



20A 125V  
 NEMA 5-20R  
 UL CSA  
 1 HP

Description	Color	Catalog Number	
Flush, nylon face, back and side wired, Fed. Spec. verified.	Almond	-	<b>HBL8310AL</b>
	Brown	<b>HBL8210</b>	<b>HBL8310</b>
	Gray	<b>HBL8210GY</b>	<b>HBL8310GY</b>
	Ivory	<b>HBL8210I</b>	<b>HBL8310I</b>
	Red	<b>HBL8210R</b>	<b>HBL8310R</b>
	White	<b>HBL8210W</b>	<b>HBL8310W</b>
Panel mount on 1.94 in. (49.2) centers.	Brown	<b>HBL8284</b>	-
	Ivory	<b>HBL8284I</b>	<b>HBL8384I</b>
Isolated ground <sup>A</sup> .	Orange	<b>IG8210</b>	<b>IG8310</b>



HBL8210GY

Note: <sup>A</sup>See section M for additional information on isolated ground devices.

## 4-PLEX® Hospital Grade Receptacles




15A 125V  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



20A 125V  
 NEMA 5-20R  
 UL CSA  
 1 HP


Description	Color	Catalog Number	
4 outlet high impact resistant Polycarbonate construction. Mount to 4 in. square box.	Brown	<b>HBL415H</b>	<b>HBL420H</b>
	Gray	-	<b>HBL420HG</b>
	Ivory	<b>HBL415HI</b>	<b>HBL420HI</b>
	Red	<b>HBL415HR</b>	<b>HBL420HR</b>
	White	<b>HBL415HW</b>	<b>HBL420HW</b>



HBL415HI

## 4-PLEX® Accessories

Description	Color	Catalog Number	
4-PLEX adapter plates for 1- and 2-gang, device boxes.	Brown	<b>HBL4AP</b>	<b>HBL4AP</b>
	Gray	<b>HBL4APGY</b>	<b>HBL4APGY</b>
	Ivory	<b>HBL4API</b>	<b>HBL4API</b>
	Red	<b>HBL4APR</b>	<b>HBL4APR</b>
	White	<b>HBL4APW</b>	<b>HBL4APW</b>



HBL4API

Note: See page A-25 for additional information on 4-PLEX devices.  
 See page A-62 for technical information.  
 4-PLEX devices are not Fed. Spec. Listed.

Dimensions in Inches (mm)

**IP20**  
SUITABILITY



**15A 125V**  
NEMA 5-15P  
UL CSA



**20A 125V**  
NEMA 5-20P  
UL CSA




**HBL8215C**

## Hospital Grade ● Plugs

### Insulgrip®

Description	Cord Diameter	Catalog Number	
Black and white nylon.	.230"-.720" (5.8-18.3)	<b>HBL8215C</b>	<b>HBL8315C</b>
Transparent housing.	.230"-.720" (5.8-18.3)	<b>HBL8215CT</b>	<b>HBL8315CT</b>
8 position angle plug, transparent housing.	.250"-.655" (6.4-16.6)	<b>HBL8215CAT*</b>	<b>HBL8315CAT*</b>




**HBL8215CAT**

### Valise®

Description	Cord Diameter	Catalog Number	
White nylon.	.300"-.660" (7.6-16.8)	<b>HBL8115V</b>	<b>HBL8364V</b>
Insulation displacement, white nylon.	.300"-.360" (7.6-9.1)	<b>HBL8013V*</b>	-

Note: \*Not Fed. Spec. Listed.  
 See page A-49 for accessories.  
 See pages L-23 and L-24 for technical information.



**HBL8115V**

**IP20**  
SUITABILITY



**15A 125V**  
NEMA 5-15R  
UL CSA  
0.5 HP



**20A 125V**  
NEMA 5-20R  
UL CSA  
1 HP

## Hospital Grade ● Connector Bodies

### Insulgrip®

Description	Cord Diameter	Catalog Number	
Black and white nylon.	.230"-.720" (5.8-18.3)	<b>HBL8219C</b>	<b>HBL8319C</b>
Transparent housing.	.230"-.720" (5.8-18.3)	<b>HBL8219CT</b>	<b>HBL8319CT</b>


### Valise®

Description	Cord Diameter	Catalog Number	
White nylon.	.300"-.660" (7.6-16.8)	<b>HBL8119V</b>	-


Note: See page A-49 for accessories.  
 See pages L-23 and L-24 for technical information.



**HBL8219C**



**HBL8219CT**



**HBL8119V**

Dimensions in Inches (mm)

**IP20**  
SUITABILITY



**15A 250V**  
NEMA 6-15P  
UL CSA  
1.5 HP




**20A 250V**  
NEMA 6-20P  
UL CSA  
2 HP

## Hospital Grade ● Plugs

**Valise®**

Description	Cord Diameter	Catalog Number	
Valise plug, white nylon.	.300"-.660" (7.6-16.8)	<b>HBL8666V</b>	<b>HBL8464V</b>

Note: HP ratings listed above are based on 208 to 240V AC only.



## Hospital Grade ● Receptacles

**HBL® Extra Heavy Duty, Duplex**

Description	Color	Catalog Number	
Flush, thermoplastic polyester face, back and side wired, multiple drive screws.	Brown Ivory	<b>HBL8600</b> <b>HBL8600I</b>	<b>HBL8400</b> <b>HBL8400I</b>


Note: See page A-48 for accessories.  
 See section N for wallplates.



**15A 250V**  
NEMA 6-15R  
UL CSA  
1.5 HP



**20A 250V**  
NEMA 6-20R  
UL CSA  
2 HP



## Hospital Grade ● Connector Bodies

**Valise®**

Description	Cord Diameter	Catalog Number
White nylon.	.300"-.660" (7.6-16.8)	<b>HBL8469V</b>



**15A 250V**  
NEMA 6-15R  
UL CSA  
1.5 HP



**20A 250V**  
NEMA 6-20R  
UL CSA  
2 HP



Dimensions in Inches (mm)

# Hospital Products Extra Heavy Duty Industrial GFCI Receptacles Tamper-Resistant and Weather Resistant



GFR5362SGI

## Features

### 10kA Short Circuit Current Rating

Limits improper access to energized contacts

- Exclusive patented tamper-resistant protection through switching technology
- Continually tests and monitors for people protection automatically
- Patented self test diagnostics

Power indication

- Steady "ON" GREEN LED provides indication of power

Ground fault indicator

- Steady "ON" RED LED provides visual indication of a ground fault condition; flashing red indicates device has lost capability to provide protection

No power at face if reverse wired

- Open circuit condition eliminates false assumption of protection at face

Durable face with V-0 flammability rating

- Polyester face cover



## AUTOGUARD® Self Test GFCI Receptacles Tamper-Resistant and Weather Resistant



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP



GFR8300SGW

Description	Rating	Color	Catalog Number	
Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	<b>GFR8200SGBK</b>	<b>GFR8300SGBK</b>
		Brown	<b>GFR8200SG</b>	<b>GFR8300SG</b>
	Gray	<b>GFR8200SGGY</b>	<b>GFR8300SGGY</b>	
	Ivory	<b>GFR8200SGI</b>	<b>GFR8300SGI</b>	
	Red	<b>GFR8200SGR</b>	<b>GFR8300SGR</b>	
	White	<b>GFR8200SGW</b>	<b>GFR8300SGW</b>	

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with both a matching color nylon wallplate, and a SS26 302/304 super stainless steel wallplate. 20 amp feed-through capability. See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.

## GFCI Receptacle Specifications per GFCI Products Listed (Pages L-12 to L-15)

Trip Level	4 to 6 mA.
Trip Time	.025 second nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15% (102V to 132V).
Amperage	15A/20A, 20A Feed Thru.
Maximum Interrupting Capacity	10,000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978. CSA Certified.
Codes	Meets all NEC® and CEC requirements. NEMA WD-6 ANSI 73.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).



GFTRST20

**Features**

- Patented shutter design for tamper-resistant protection
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost
- Alarm version provides audible notification of a trip condition



**Hospital Grade • Tamper-Resistant**



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP

Description	Rating	Color	Catalog Number	
Night Light Two LED Night Lights, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFTRST82ALNL</b>	<b>GFTRST83ALNL</b>
		Black	<b>GFTRST82BKNL</b>	<b>GFTRST83BKNL</b>
		Brown	<b>GFTRST82BNL</b>	<b>GFTRST83BNL</b>
		Gray	<b>GFTRST82GYNL</b>	<b>GFTRST83GYNL</b>
		Ivory	<b>GFTRST82INL</b>	<b>GFTRST83INL</b>
		Light Almond	<b>GFTRST82LANL</b>	<b>GFTRST83LANL</b>
		Red	<b>GFTRST82RNL</b>	<b>GFTRST83RNL</b>
		White	<b>GFTRST82WNL</b>	<b>GFTRST83WNL</b>
		Alarm, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond
Black	<b>GFTRST82BKB</b>			<b>GFTRST83BKB</b>
Brown	<b>GFTRST82B</b>			<b>GFTRST83B</b>
Gray	<b>GFTRST82GYB</b>			<b>GFTRST83GYB</b>
Ivory	<b>GFTRST82IB</b>			<b>GFTRST83IB</b>
Light Almond	<b>GFTRST82LAB</b>			<b>GFTRST83LAB</b>
Red	<b>GFTRST82RB</b>			<b>GFTRST83RB</b>
White	<b>GFTRST82WB</b>			<b>GFTRST83WB</b>




GFTRST83WNL



GFTRST83GYB

**Product Dimensions** Inches (mm)

GFCI Receptacle	
A	3.27 (83.1)
B	2.75 (69.8)
C	1.75 (44.5)
D	1.47 (37.4)
E	1.10 (27.9)





**GFRST82WNL**

**Features**

- Fed. Spec UL Listed, Hospital Grade
- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.



**Hospital Grade**

Rating	Rating	Color	Catalog Number			
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFRST82AL</b>	<b>GFRST83AL</b>		
		Black	<b>GFRST82BK</b>	<b>GFRST83BK</b>		
		Brown	<b>GFRST82</b>	<b>GFRST83</b>		
		Gray	<b>GFRST82GY</b>	<b>GFRST83GY</b>		
		Ivory	<b>GFRST82I</b>	<b>GFRST83I</b>		
		Light Almond	<b>GFRST82LA</b>	<b>GFRST83LA</b>		
		Red	<b>GFRST82R</b>	<b>GFRST83R</b>		
		White	<b>GFRST82W</b>	<b>GFRST83W</b>		
		Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFRST82ALU</b>	<b>GFRST83ALU</b>
				Black	<b>GFRST82BKU</b>	<b>GFRST83BKU</b>
Brown	<b>GFRST82U</b>			<b>GFRST83U</b>		
Gray	<b>GFRST82GYU</b>			<b>GFRST83GYU</b>		
Ivory	<b>GFRST82IU</b>			<b>GFRST83IU</b>		
Light Almond	<b>GFRST82LAU</b>			<b>GFRST83LAU</b>		
Red	<b>GFRST82RU</b>			<b>GFRST83RU</b>		
White	<b>GFRST82WU</b>			<b>GFRST83WU</b>		
Night Light Two LED Night Lights, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC			Almond	<b>GFRST82ALNL</b>	<b>GFRST83ALNL</b>
				Black	<b>GFRST82BKNL</b>	<b>GFRST83BKNL</b>
		Brown	<b>GFRST82NL</b>	<b>GFRST83NL</b>		
		Gray	<b>GFRST82GYNL</b>	<b>GFRST83GYNL</b>		
		Ivory	<b>GFRST82INL</b>	<b>GFRST83INL</b>		
		Light Almond	<b>GFRST82LANL</b>	<b>GFRST83LANL</b>		
		Red	<b>GFRST82RNL</b>	<b>GFRST83RNL</b>		
		White	<b>GFRST82WNL</b>	<b>GFRST83WNL</b>		
		Alarm, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFRST82ALB</b>	<b>GFRST83ALB</b>
				Black	<b>GFRST82BKB</b>	<b>GFRST83BKB</b>
Brown	<b>GFRST82B</b>			<b>GFRST83B</b>		
Gray	<b>GFRST82GYB</b>			<b>GFRST83GYB</b>		
Ivory	<b>GFRST82IB</b>			<b>GFRST83IB</b>		
Light Almond	<b>GFRST82LAB</b>			<b>GFRST83LAB</b>		
Red	<b>GFRST82RB</b>			<b>GFRST83RB</b>		
White	<b>GFRST82WB</b>			<b>GFRST83WB</b>		
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC			Almond	<b>GFRST82SNAPAL</b>	<b>GFRST83SNAPAL</b>
				Black	<b>GFRST82SNAPBK</b>	<b>GFRST83SNAPBK</b>
		Brown	<b>GFRST82SNAP</b>	<b>GFRST83SNAP</b>		
		Gray	<b>GFRST82SNAPGY</b>	<b>GFRST83SNAPGY</b>		
		Ivory	<b>GFRST82SNAPI</b>	<b>GFRST83SNAPI</b>		
		Light Almond	<b>GFRST82SNAPLA</b>	<b>GFRST83SNAPLA</b>		
		Red	<b>GFRST82SNAPR</b>	<b>GFRST83SNAPR</b>		
		White	<b>GFRST82SNAPW</b>	<b>GFRST83SNAPW</b>		



**GFRST82R**



**GFRST83INL**



**GFRST83BKB**



**GFRST83SNAPGY**

**Right Angle Pigtailed Terminal**

Clear right angle terminal with 6 inch leads,  
 600V, #12 AWG THHN/THWN-2,  
 Polycarbonate housing material.

Type	Catalog Number
Solid	<b>SNAP1RA</b>
Stranded	<b>SNAP2RA</b>

# Hospital Products Commercial Tamper-Resistant and Weather Resistant GFCI Receptacles




**GFTWRST20WIG**

## Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired



## Hospital Grade • Tamper-Resistant Weather Resistant



Description	Rating	Color	Catalog Number	
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFTWRST82AL</b>	<b>GFTWRST83AL</b>
		Black	<b>GFTWRST82BK</b>	<b>GFTWRST83BK</b>
		Brown	<b>GFTWRST82</b>	<b>GFTWRST83</b>
		Gray	<b>GFTWRST82GY</b>	<b>GFTWRST83GY</b>
		Ivory	<b>GFTWRST82I</b>	<b>GFTWRST83I</b>
		Light Almond	<b>GFTWRST82LA</b>	<b>GFTWRST83LA</b>
		Red	<b>GFTWRST82R</b>	<b>GFTWRST83R</b>
		White	<b>GFTWRST82W</b>	<b>GFTWRST83W</b>
Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFTWRST82ALU</b>	<b>GFTWRST83ALU</b>
		Black	<b>GFTWRST82BKU</b>	<b>GFTWRST83BKU</b>
		Brown	<b>GFTWRST82U</b>	<b>GFTWRST83U</b>
		Gray	<b>GFTWRST82GYU</b>	<b>GFTWRST83GYU</b>
		Ivory	<b>GFTWRST82IU</b>	<b>GFTWRST83IU</b>
		Light Almond	<b>GFTWRST82LAU</b>	<b>GFTWRST83LAU</b>
		Red	<b>GFTWRST82RU</b>	<b>GFTWRST83RU</b>
		White	<b>GFTWRST82WU</b>	<b>GFTWRST83WU</b>
Isolated Ground, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFTWRST82ALIG</b>	<b>GFTWRST83ALIG</b>
		Black	<b>GFTWRST82BKIG</b>	<b>GFTWRST83BKIG</b>
		Brown	<b>GFTWRST82IG</b>	<b>GFTWRST83IG</b>
		Gray	<b>GFTWRST82GYIG</b>	<b>GFTWRST83GYIG</b>
		Ivory	<b>GFTWRST82IIG</b>	<b>GFTWRST83IIG</b>
		Light Almond	<b>GFTWRST82LAIG</b>	<b>GFTWRST83LAIG</b>
		Red	<b>GFTWRST82RIG</b>	<b>GFTWRST83RIG</b>
		White	<b>GFTWRST82WIG</b>	<b>GFTWRST83WIG</b>
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple	15 and 20A 125V AC	Almond	<b>GFTWRST82SNAPAL</b>	<b>GFTWRST83SNAPAL</b>
		Black	<b>GFTWRST82SNAPBK</b>	<b>GFTWRST83SNAPBK</b>
		Brown	<b>GFTWRST82SNAP</b>	<b>GFTWRST83SNAP</b>
		Gray	<b>GFTWRST82SNAPGY</b>	<b>GFTWRST83SNAPGY</b>
		Ivory	<b>GFTWRST82SNAPI</b>	<b>GFTWRST83SNAPI</b>
		Light Almond	<b>GFTWRST82SNAPLA</b>	<b>GFTWRST83SNAPLA</b>
		Red	<b>GFTWRST82SNAPR</b>	<b>GFTWRST83SNAPR</b>
		White	<b>GFTWRST82SNAPW</b>	<b>GFTWRST83SNAPW</b>




## Right Angle Pigtailed Terminal

Clear right angle terminal with 6 inch leads,  
600V, #12 AWG THHN/THWN-2,  
Polycarbonate housing material.


Type	Catalog Number
Solid	<b>SNAP1RA</b>
Stranded	<b>SNAP2RA</b>

# Hospital Products Surge Protection Devices


15 and 20 Ampere, 125 Volts AC 60 Hz




**SNAP8362GYS**



**HBL8362ISA**



**HBL420HS**



**HBL4API**



**HBL6PSHG**

Dimensions in Inches (mm)

## Hospital Grade ● Circuit Guard® Receptacles



SNAPConnect® Tamper-Resistant, surge suppression receptacle, smooth face, duplex. Requires connector on page L-15, sold separately.

Surge suppression receptacles with light and alarm, 240 joules/15000A per mode.

Isolated ground, surge suppression receptacles with light and alarm, 240 joules/15000A per mode.

4-PLEX® surge suppression receptacles with lights, 80 joules/6500A per mode.



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP

Description	Color	Catalog Number	
SNAPConnect® Tamper-Resistant, surge suppression receptacle, smooth face, duplex. Requires connector on page L-15, sold separately.	Blue	<b>SNAP8262S</b>	<b>SNAP8362S</b>
	Gray	<b>SNAP8262GYS</b>	<b>SNAP8362GYS</b>
	Ivory	<b>SNAP8262IS</b>	<b>SNAP8362IS</b>
	Light Almond	<b>SNAP8262LAS</b>	<b>SNAP8362LAS</b>
	Red	<b>SNAP8262RS</b>	<b>SNAP8362RS</b>
	White	<b>SNAP8262WS</b>	<b>SNAP8362WS</b>
Surge suppression receptacles with light and alarm, 240 joules/15000A per mode.	Almond	<b>HBL8262ALSA</b>	<b>HBL8362ALSA</b>
	Blue	<b>HBL8262SA</b>	<b>HBL8362SA</b>
	Gray	<b>HBL8262GYSA</b>	<b>HBL8362GYSA</b>
	Ivory	<b>HBL8262ISA</b>	<b>HBL8362ISA</b>
	Red	<b>HBL8262RSA</b>	<b>HBL8362RSA</b>
	White	<b>HBL8262WSA</b>	<b>HBL8362WSA</b>
Isolated ground, surge suppression receptacles with light and alarm, 240 joules/15000A per mode.	Blue	<b>IG8262SA</b>	<b>IG8362SA</b>
	Gray	<b>IG8262GYSA</b>	<b>IG8362GYSA</b>
	Ivory	<b>IG8262ISA</b>	<b>IG8362ISA</b>
	Orange	<b>IG8262OSA</b>	<b>IG8362OSA</b>
	Red	<b>IG8262RSA</b>	<b>IG8362RSA</b>
	White	<b>IG8262WSA</b>	<b>IG8362WSA</b>
4-PLEX® surge suppression receptacles with lights, 80 joules/6500A per mode.	Blue	-	<b>HBL420HS</b>
	Ivory	-	<b>HBL420HIS</b>
	Red	-	<b>HBL420HRS</b>

Note: See page Tech-10 for Tamper-Resistant description.

## 4-PLEX® Accessories

Description	Color	Catalog Number
4-PLEX Adapter Plates for 1- and 2-gang, and 4 in. (101.6) square device boxes.	Blue	<b>HBL4APBL</b>
	Ivory	<b>HBL4API</b>
	Red	<b>HBL4APR</b>
4-PLEX Portable Box. Portable 4 in. (101.6) square box with cord grip. Accepts up to .66 in. (16.8) diameter cord.	Ivory	<b>HBL4PBI</b>

Note: 4-PLEX Box is not UL Listed.

## Metallic Power Strip Surge Protected



Description	Catalog Number
15A 125V power strip with filtering, surge protection, 3 hospital grade duplex receptacles, 6 foot power supply cord and hospital grade plug.	<b>HBL6PSHG</b>

Note: See section M for additional information on surge protection products.

## Wallplates (Sold Separately)

Configuration	High-Impact Nylon			Plated Steel		Stainless Steel (S/S) Brass	
	Color	Standard	Mid-Size				
1-Gang	Almond	<b>NP26AL</b>	<b>NPJ26AL</b>	Chrome	<b>SCH26</b>	Smooth S/S	<b>SS26</b>
	Blue	-	<b>NPJ26CBL*</b>				
	Blue	-	<b>NPJ26BL</b>	Plated		Smooth Brass	<b>SB26</b>
	Gray	<b>NP26GY</b>	<b>NPJ26GY</b>				
	Ivory	-	<b>NPJ26C*</b>				
	Ivory	<b>NP26I</b>	<b>NPJ26I</b>				
	Off. White	<b>NP26OW</b>	<b>NPJ26OW</b>				
	Orange	<b>NP26OIG**</b>	-				
	Red	<b>NP26R</b>	<b>NPJ26R</b>				
	White	<b>NP26W</b>	<b>NPJ26W</b>				

Note: \*Premarked "COMPUTER ONLY." Lettering is block 1/4" high.  
 \*\*Premarked "ISOLATED GROUND." Lettering is block 1/4" high.  
 ^ Jumbo size plate.  
 See page A-62 for technical information on 4-PLEX devices.

# Hospital Products Hubbell<sup>®</sup> Plugs, Connector Bodies and Receptacles

20 Ampere, 125 Volts AC only, 2 Pole, 3 Wire Grounding



## For Hospital Use Only



### Hubbell<sup>®</sup> Plugs and Connector Bodies

Description	Plugs	Connector Bodies
Nylon cover, thermoset interior.	<b>HBL23014HGB</b>	<b>HBL23001HGB</b>
Armored, epoxy filled, rubber cord grip.	<b>HBL23004HG</b>	-


Note: Cord clamp range for plug and connector .300" to .660" (7.6 to 16.8).



20A 125V AC



20A 125V AC



**HBL23014HGB**

### Receptacles

Description	Catalog Number
Black, back wired.	- <b>HBL23000HG</b>




**HBL23001HGB**

### Wallplates

Description	Catalog Number
Stainless steel 302/304, single-gang.	<b>HBL23901HG</b>
Stainless steel 302/304, three-gang for two receptacles.	<b>HBL23909HG</b>


Note: Suffix HG or HGB type for hospital use only.



**HBL23000HG**



**IP30**  
SUITABILITY



20A 125V AC


### Explosion Proof Plug

Description	Catalog Number
Plug, with, epoxy kit, accepts #12 or #14 type SO cable.	<b>HBL24312</b>

### Hazardous to Non-hazardous Location Receptacle Conversion Kits

Conversion kits for replacement of explosion proof receptacles listed above, with non-explosion proof receptacles, in the hospital areas formerly classified as hazardous locations and now classified non-hazardous locations due to the change from flammable anesthetizing gases to nonflammable anesthetizing gases.

For Conversion To:	Catalog Number
20A, 125V, duplex receptacle (Hubbell HBL830 Series). Includes adapter ring and stainless steel wall plate for duplex receptacle (receptacle not included).	<b>HBL24300RKD</b>
20A, 125V, Hospital Hubbell receptacle (Hubbell HBL23000HG) or 20A, 125V, straight blade single receptacle (Hubbell HBL8310 series). Includes adapter ring and stainless wall plate for single receptacle (receptacle not included).	<b>HBL24300RKS</b>




**HBL24312**



**24352** Low-profile style explosion-proof receptacle (now discontinued).



**HBL24300RKD** Retrofit kit for duplex receptacles.



**HBL24300RKD** Duplex retrofit kit accepts 20A duplex straight blade hospital grade receptacles (HBL8300, HBL8300I, IG8300, etc.). Order receptacles separately.



**HBL24300RKS** Retrofit kit for single receptacles.



**HBL24300RKS** Single retrofit accepts hospital only Hubbell single receptacles (Hubbell HBL23000HG) or 20A single straight blade hospital grade receptacles (Hubbell HBL8310, HBL8310I, IG8310, etc.). Order receptacles separately.


Dimensions in Inches (mm)




**HBL25515**




**HBL25615**



**HBL25605**




**HBL25603**




**HBL25509**

**IP30**  
 SUITABILITY



**50A 250V AC**




**60A 250V AC**


**Mobile X-Ray Plugs**

Description	Catalog Number	
Plug, with epoxy kit, less cord clamp.	<b>HBL25515</b>	<b>HBL25615</b>
Plug, with cord clamp, less epoxy kit.	<b>HBL25525</b>	<b>HBL25625</b>

*Note: Cord clamp range of plugs with cord clamps .830" to 1.3" (21.1 to 33.0).  
 50A plugs fit 50A or 60A receptacles.*



**50A 250V AC**



**60A 250V AC**

**Mobile X-Ray Receptacles**

Description	Catalog Number	
Receptacle with stainless steel plate assembly.	<b>HBL25505</b>	<b>HBL25605</b>
Receptacle with cast aluminum plate assembly.	<b>HBL25503</b>	<b>HBL25603</b>
Replacement receptacle interior.	-	<b>IN16494</b>

**Accessory**

Description	Catalog Number
Box stamped steel 8" x 8" x 4" (203.2 x 203.2 x 101.6), accommodates 50A and 60A mobile X-ray receptacles. Knockout sizes 1¼", 1½" and 2".	<b>HBL25509</b>

Dimensions in Inches (mm)



**HBL8200GY**

**HBL® Extra Heavy Duty, Straight Blade  
Hospital Grade Duplex Receptacles**

**Specifications**

Receptacles	Part	Description
Typical Specification – Catalog No. HBL8200	Receptacle	15A
Manufacturer’s Identification – Hubbell HBL8200	Top	PBT*
Description – Hospital Grade, Straight Blade Duplex Receptacle	Base	RTP**
Type – 2 Pole, 3 Wire, Grounding	By-Pass Power Contacts	.037 in. (.9) Brass – Nickel Finish
Rating – 15A, 125V	Clamping Plate	.031 in. (.8) Brass – Nickel Finish
Certification: UL Listed to UL 498 File E2186, Fed. Spec. WC596,	Mounting Strap	.050 in. (1.3) Brass – Nickel Finish
Hospital Grade, NEMA® WD-6 Compliant	Line Terminal Screws	#10-32 Silicone Bronze, Multiple Drive
Certified to CSA, C22.2, No. 42 File 285	Hex Head Grounding Screw	#10-32 (Green) Silicon Bronze, Multiple Drive
	Center Assembly Rivet	Silicon Bronze
	Automatic Self-Grounding Clip	Stainless Steel
	Flat Head Mounting Screws	Stainless Steel

**Performance**

**Electrical**

Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.

**Mechanical**

Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green).
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.

**Environmental – Material**

Flammability	UL 94V-0 and UL 94-5 VA.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

Note: \*Polybutylene Terephthalate.

\*\*Reinforced Thermoplastic Polyester.



**SNAPConnect® Straight Blade  
Hospital Grade Duplex Receptacles**



**Specifications**

Receptacle	Part	Description
Typical Specification – Catalog No. SNAP8200	Receptacle	15A
Manufacturer's Identification – Hubbell SNAP8200	Top	Nylon
Description – Straight Blade Duplex Receptacle	Base	Nylon
Type – 2 Pole, 3 Wire, Grounding	Triple Wipe Power Contacts	Brass
Rating – 15A, 125V	Mounting Strap	Galvanized Steel; Brass (HG)
Certification – UL Listed to UL 498	Automatic Self-Grounding Clip	Stainless Steel
Fed. Spec. WC596, Certified to CSA 22.2, No. 42	Flat Head Mounting Screws	Steel-Zinc Plated/Self Tapping


  

Connector	Contact	Connector Body	Wire
SNAP1RA	Brass	Clear Polycarbonate	6" Solid copper #12 AWG THHN/THWN-2 600V, T90 Nylon FT-1, PVC 90°C (min).
SNAP2RA	Brass	Clear Polycarbonate	6" Stranded copper #12 AWG THHN/THWN-2 600V, T90 Nylon FT-1, PVC 90°C (min).

**Performance**

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V as rated.
Current Interrupting	Receptacle certified for current interrupting at full rated current with equivalently rated NEMA® plug.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated DC current.
Mechanical	
Terminal Wire Leads Identification	Terminal wire leads identified in accordance with UL 498 (Black, White, Green).
Product Identification	Ratings are a permanent part of the device.
Environmental – Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact).

**Dimensions**



NEMA® is a registered trademark of the National Electrical Manufacturers Association.



**8200REDLTRA**



**2182IVLTRA**

**Hubbell-PRO Heavy Duty, Straight Blade  
Hospital Grade Duplex Receptacles**

**Specifications**

Receptacle	Part	Description
Typical Specification - Catalog No. 8200	Receptacle	15A
Manufacturer's Identification - Hubbell-PRO 8200	Top	Nylon
Description - Straight Blade Hospital Grade Duplex Receptacle	Base	Nylon
Type - 2 Pole, 3 Wire, Grounding	Triple Wipe Power Contacts	.0295 in. Brass
Rating - 15A, 125V (also 20A, 125V)	Clamping Plate	Plated Steel
Certification - UL Listed to UL 498, Fed. Spec. WC596	Mounting Strap	.040 in. Galvanized Steel
Hospital Grade, NEMA® WD-6 Compliant	Terminal Screws	Plated Steel
Certified to CSA	Hex Head Grounding Screw	Plated Steel
	Automatic Self-Grounding Staple	Stainless Steel
	Mounting Screws	Zinc Plated Steel

**Performance**

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.
Environmental – Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

*NEMA® is a registered trademark of the National Electrical Manufacturers Association.*



**USB8300R**

**USB Charger Tamper-Resistant, Straight Blade  
Hospital Grade Duplex Receptacles**

**Specifications**

USB Charger Receptacle	Part	Description
Typical Specification - Catalog No. USB8300 Manufacturer's Identification - Hubbell USB8300 USB Charger	Charger Receptacle	USB 3.8 Amp 5V DC, Electrical 15 or 20 Amp 125V AC
Receptacle	Ports	Type A, 2.0
Description - Hospital Grade, Straight Blade Duplex Receptacle	LED	Green Indicator
Type - 2 Pole, 3 Wire, Grounding	Top	Nylon
Rating - 15 or 20 Amp, 125V AC, USB 3.8 Amp, 5V DC	Base	Nylon
Certification - cULus Listed to UL498 and UL1310	Triple Wipe Power Contacts	.030 in. Cooper Alloy
Hospital Grade, NEMA® WD-6 Compliant (USB8200 and 8300 series only)	Clamping Plate	Plated Steel
Complies with battery charging specification USB BC1.2	Mounting Strap	.040 in. Galvanized Steel
Complies with Part 15 of the FCC rules	Terminal Screws	Plated Steel
Compatible with USB 1.1/2.0/3.0 devices, including Apple products	Hex Head Grounding Screw	Plated Steel
	Automatic Self-Grounding Staple	Stainless Steel
	Mounting Screws	Zinc Plated Steel

**Performance**

Electrical	
Dielectric Voltage	Withstands 2,000V minimum.
Max. Working Voltage	125V.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.
Mechanical	
USB Port	Stainless Steel Rated for 10,000 plug insertions and removal
Terminal Identification	Terminals identified in accordance with UL 498 and CSA (Brass, White, Green)
Terminal Accommodation	#14-10 AWG stranded or solid copper conductor only.
Product Identification	Ratings are a permanent part of the device.
Circuit Feed-Through	20 Amp 125 Volt
Environmental - Material	
Flammability	UL 94V-2.
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact).

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



**HBL8215C**



**HBL8219C**

**Insulgrip® Plugs and Connectors  
Hospital Grade**

**Specifications**

Plug	Part	Description
Typical Specification—Catalog No. HBL8215C	Plug	15A
Manufacturer's Identification—Hubbell HBL8215C Plug	Housing	Nylon— Black
Description—Hospital Grade Straight Blade Plug	Blade Holder	Nylon— Natural
Type—2 Pole, 3 Wire, Grounding	Retainer	Polycarbonate—Clear
Rating— 15A, 125V	Cord Clamp	Nylon—Natural
Certification—UL Listed, CSA Certified	Contact Blades	.060 in. (1.5) Brass
UL Verified to Fed. Spec. WC596	Ground Contact Blade	.040 in. (1.0) Brass
IP Suitability—IP20	Line Terminal Screws	#8-32 Brass, Multiple Drive
	Ground Screw	#8-32 Brass, Multiple Drive (Green)
	Wire Clamps	.080 in. (2.0) Steel—Nickel Finish
Connector	Part	Description
Typical Specification—Catalog No. HBL8219	Connector	15A
Manufacturer's Identification—Hubbell HBL8219C Connector	Housing	Nylon—Black
Description—Hospital Grade Straight Blade Connector Body	Contact Holder	Nylon— Natural
Type—2 Pole, 3 Wire, Grounding	Retainer	Polycarbonate—Clear
Rating—15A, 125V	Cord Clamp	Nylon—Natural
Certification—UL Listed, CSA Certified	Contacts	.040 in. (1.0) Copper Alloy
UL Verified to Fed. Spec. WC596	Line Terminal Screws	#8-32 Brass, Multiple Drive
IP Suitability—IP20	Ground Screw	#8-32 Brass, Multiple Drive (Green)
	Wire Clamps	.080 in. (2.0) Steel—Nickel Finish

**Performance**

Electrical	
Dielectric Voltage	Withstands 2000V AC minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 100 cycles of overload at 150% of rated voltage DC.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL and CSA (Brass, White, and Green).
Terminal Accommodation	#18-10 AWG.
Product Identification	Ratings are a permanent part of the device.
Torque Range	Cord clamp/terminal screws 9 to 12 in-lbs.
Cord Diameter Range	.230"-.720" (5.8-18.3) Integral cord grip.
Environmental-Material	
Flammability	UL 94HB or better.
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)

*Note: Please consult the factory for product dimensions and specifications for other products listed in this catalog.*



**HBL8115V**



**HBL8119V**

**Valise® Plugs and Connectors  
Hospital Grade**

**Specifications**

Plug	Part	Description
Typical Specification—Catalog No. HBL8115V	Plug	15A
Manufacturer's Identification—Hubbell HBL8115V Plug	Housing	Nylon
Description—Hospital Grade Straight Body Plug	Contact Blades	Brass
Type— 2 Pole, 3 Wire, Grounding	Ground Blade	Brass
Rating—15A, 125V	Terminal Screws	Multiple Drive
Certifications—UL Listed to UL498	Cable Inserts	Polyphenylene Oxide
File E1706, CSA Certified to C22.2	Terminal Clamps	Plated CR Steel
No. 42 File LR280. Fed. Spec. WC596	Body Holding Screws	Multiple Drive
IP Suitability—IP20		
Connector	Part	Description
Typical Specification—Catalog No. HBL8119V	Connector	15A
Manufacturer's Identifications—Hubbell HBL8119V Connector Body	Housing	Nylon
Description—Hospital Grade Straight Connector Body	Contact and Ground Spring	Brass
Type—2 Pole, 3 Wire, Grounding	Terminal Screws	Multiple Drive
Rating—15A, 125V	Cable Inserts	Polyphenylene Oxide
Certifications—UL Listed to UL498	Terminal Clamps	Plated CR Steel
File E1706, CSA Certified to C22.2	Body Holding Screws	Multiple Drive
No. 42 File LR280. Fed. Spec. WC596		
IP Suitability—IP20		

**Performance**

Electrical	
Dielectric Voltage	Withstands 2000V AC minimum.
Max. Working Voltage	125V or 250V as rated.
Current Interrupting	Certified for current Interrupting at full rated current.
Temperature Rise	Max. 30°C temperature rise at full rated current.
Mechanical	
Terminal Identification	Terminals identified in accordance with UL and CSA (Brass, White, and Green)
Terminal Accommodation	#16 to #12 AWG.
Product Identification	Ratings are a permanent part of the device.
Torque	Terminal screws 12 in.-lbs. Cord clamp screws 7 to 10 in.-lbs.
Cord Diameter Range	.300" to .660" (7.6 to 16.8)
Environmental-Material	
Flammability	UL 94HB
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact).
Standards	
NEMA® Configurations WD6.	
Listed to UL Standard UL498 and UL Verified to Ped. Spec. WC596.	
Certified to CSA Standard C22.2 No. 42.	

NEMA® is a registered trademark of the National Electrical Manufacturers Association.