

GigaMax™ Cat 5e UTP Patch Cords

APPLICATION

GigaMax Cat 5e UTP Patch Cords are designed to be used in Cat 5e UTP structured cabling systems. Uses include high-bandwidth applications such as Gigabit Ethernet and 622 Mbps ATM.



SPECIFICATION

The patch cords shall provide Cat 5e performance for cross connecting Cat 5e equipment and/or backbone cables to high-performance Cat 5e horizontal cable systems. The patch cords shall be 24-gauge stranded UTP with a standard 8-position modular plug and colored strain-relief boot on each end. The cords shall be available in lengths of 3, 5, 7, and 10 feet. The cords must meet performance and assembly requirements per ANSI/TIA-568.2-D. Patch cord plug shall have industry-standard, ANSI/TIA-1096-A compliant 50 micro inches of gold plating.

FEATURES

- Available in five colors for color coding and organization
- Available in four standard lengths (custom lengths available)

DESIGN CONSIDERATIONS

- ANSI/TIA channel performance limits the total length of patching and equipment cords to 32 feet (10 meters) per ANSI/TIA-568.2-D
- Color-matched cable and boots
- Color-matched rubber boot provides protection for plug

STANDARDS COMPLIANCE

- ANSI/TIA-568.2-D Cat 5e
- ISO/IEC 11801-1 Class D
- ANSI/TIA-1096-A (formerly FCC Part 68)
- cULus Listed
- RoHS 2 Compliant
- UL 444 CM Rated
- IEEE 802.3bt PoE Type 1 (15.4 Watts) formerly 802.3af, Type 2 (30 Watts) formerly 802.3at, Type 3 (60 Watts)
- Cisco UPoE (60 Watts)

PHYSICAL SPECIFICATIONS

Dimensions:	See page two
Outer Diameter:	0.22"
Materials:	24-gauge, Cat 5e stranded UTP, standard modular non-keyed, 8-position 8-conductor plug, 94V-0 rated
Color:	White, yellow, blue, green, gray with color-matched boots
Environmental Conditions:	Operating Temperature: -20 °C to +60 °C Installation Temperature: 0 °C to +50 °C

COUNTRY OF ORIGIN


China

WARRANTY INFORMATION

Limited Product and Limited Extended Warranties are rendered VOID if the installed structured cabling system is used for PoE applications that exceed the product's specified power rating. For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



5G460-XXX

GIGAMAX™ CAT 5E UTP PATCH CORDS – STOCKED ITEMS

Description	White	Yellow	Blue	Green	Gray
Cat 5e UTP Patch Cord, 3 feet (0.9 m)	5G460-03W	5G460-03Y	5G460-03L	5G460-03G	5G460-03S
Cat 5e UTP Patch Cord, 5 feet (1.5 m)	5G460-05W	5G460-05Y	5G460-05L	5G460-05G	5G460-05S
Cat 5e UTP Patch Cord, 7 feet (2.1 m)	5G460-07W	5G460-07Y	5G460-07L	5G460-07G	5G460-07S
Cat 5e UTP Patch Cord, 10 feet (3.0 m)	5G460-10W	5G460-10Y	5G460-10L	5G460-10G	5G460-10S

NOTE: Other lengths are available by special order. Please contact customer service for more information.



For assistance customizing your patch cords, please visit www.leviton.com/configurator or call Tech Support at 800.824.3005.



Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
T +44.0.1592.772124
E customerserviceeu@leviton.com

Mexico
T +52.55.5082.1040
E lsmarketing@leviton.com

Middle East & Africa
T +971.4.247.9800
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com