



HBL3524C -- Twist-Lock Flanged Receptacle



4P5W, 20A 250V/10A 600V AC, Non-NEMA, White Nylon

Product Specifications

Product Type	 <p>Twist-Lock Devices</p>
Product Item	Flanged Receptacle
Wiring Scheme	4-Pole, 5-Wire Grounding
Amperage	20A
Voltage	Multi Rated
NEMA Configuration	Non-NEMA
Item Style	Standard
Device Color	White
Terminal Retainer Material	Clear polycarbonate
Blade Material	Brass
Terminal Clamp Material	.08" (2) steel-nickel plated
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive
Ground Screw Material	#10-32 Brass (green finish) Multi-drive
Body Holding Screw Material	Steel, zinc plated Multi-drive
Body Contact Carrier Material	Natural White Nylon
Flanged Casing Material	Natural White Nylon
Mounting Screw Material	Nickel-plated Brass Round head screws
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	30A #10 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Listings	UL/CSA
UPC Number	783585039930
Weight in LBS	0.3
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



NEMA Configuration

