


ANT-433-CW-HD-SMA

✓ ACTIVE

TE Internal #: ANT-433-CW-HD-SMA
Terminal/Duck Antenna, Single Band, LPWAN / LoRaWAN,
External Mount, Stud/Screw/Lug Mount, SMA, Omnidirectional,
Single Port, 0 < 3 dBi Peak Gain
[View on TE.com >](#)



Antennas



Communication Protocol: **LoRaWAN, LPWAN**
Mounting Location: **External**
Mounting Type: **Stud/Screw/Lug Mount**
Frequency Category: **410 – 470**
Antenna Type: **Terminal/Duck**

Features

Product Type Features

Antenna Termination	SMA
Antenna Product Type	Antenna

Configuration Features

Antenna Style	Whip
Mounting Location	External
Antenna Type	Terminal/Duck
Band Type	Single Band
Port Configuration	Single Port

Electrical Characteristics

Impedance	50 Ω
VSWR (Max)	<2.1:1

Signal Characteristics

Frequency Band	433 MHz
Gain (Max)	.7 dB



Frequency Category	410 – 470
--------------------	-----------

Peak Gain	0 < 3 dBi
-----------	-----------

Body Features

Antenna Weight	19.43 g[.685 oz]
----------------	------------------

Mechanical Attachment

Polarization	Linear
--------------	--------

Mounting Type	Stud/Screw/Lug Mount
---------------	----------------------

Dimensions

Product Width	13.5 mm[.53 in]
---------------	-----------------

Product Length	88 mm[3.46 in]
----------------	----------------

Product Height	0 mm[0 in]
----------------	------------

Operation/Application

Antenna Environment	Outdoor
---------------------	---------

Directionality	Omnidirectional
----------------	-----------------

Industry Standards

Communication Protocol	LoRaWAN, LPWAN
------------------------	----------------

Primary Application	LoRaWAN, LPWAN
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Candidate List Declared Against: Not Yet Reviewed SVHC > Threshold: Pb (4% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
--	---

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	--

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # CONSMA008-G
SMA Jack 50 Ohm Through Hole PCB

TE Part # CONSMA001
SMA Jack 50 Ohm PCB Through Hole

TE Part # CONSMA002-SMD-G
SMA Jack 50 Ohm PCB Surface Mount

TE Part # CONSMA002-L-G
SMA Jack 50 Ohm PCB Through Hole

Customers Also Bought

TE Part #ANT-418-CW-HD
Antenna 1/4 Wave HD Whip 418MHz RPS

TE Part #796096-2
SLD CPC RCPT ASY,11-4,STD SEX

TE Part #1622347-1
LR1 1% 18R

TE Part #1658612-3
15 POS HDF RCPT, MS, LEAD FREE

TE Part #1658613-3
15 POS HDF PLUG, MS, LEAD FREE

TE Part #1658614-2
25 POS HDF RCPT, AP, LEAD FREE

TE Part #1-1734248-7
1.0 FPC, ZIF V/T, SMT, 17P

TE Part #2176344-1
CRGCO 1206 1R0 5%

ANT-433-CW-HD-SMA

Terminal/Duck Antenna, Single Band, LPWAN / LoRaWAN, External Mount, Stud /Screw/Lug Mount, SMA, Omnidirectional, Single Port, 0 < 3 dBi Peak Gain



TE Part #5103309-3
A/L LOW PRO HDR 16P VERT BLACK



TE Part #2267473-1
SIZE 11 PERIPHERAL SEAL, CPC

Documents

Product Drawings

Antenna 1/4 Wave HD Whip 433MHz SMA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ANT-433-CW-HD-SMA_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ANT-433-CW-HD-SMA_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ANT-433-CW-HD-SMA_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ANT-433-CW-HD

English