

HBL8815C -- Twist-Lock Flanged Inlet



2P2W, 20A 250V, L2-20P, White Nylon

Product Specifications

Product Type



Product Item	Flanged Inlet
Wiring Scheme	2-Pole, 2-Wire Non-Grounding
Amperage	20A
Voltage	250V AC
NEMA Configuration	L2-20P
Item Style	Standard
Device Color	White
Terminal Retainer Material	Clear polycarbonate
Blade Material	Brass
Terminal Clamp Material	.062" cold rolled steel-nickel-plated
Terminal Screw Material	#8-32 Brass
Flanged Casing Material	Natural White Nylon
Mounting Screw Material	Brass, zinc plated
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	20A #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
UPC Number	783585180755
Weight in LBS	0.05
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

