

Product designation				Auxiliary contactor
Product type designation				BG00
Contact characteristics				
Number of poles		Nr.	4	
Rated insulation voltage U_i IEC/EN		V	690	
Rated impulse withstand voltage U_{imp}		kV	6	
Operational frequency	min	Hz	25	
	max	Hz	400	
IEC Conventional free air thermal current I_{th}		A	10	
Protection fuse		gG (IEC)	A	16
	Tightening torque for terminals			
	min	Nm	0.8	
	max	Nm	1	
	min	I _{bin}	0.59	
	max	I _{bin}	0.74	
Tightening torque for coil terminal	min	Nm	0.8	
	max	Nm	1	
	min	I _{bin}	Prodotti finiti	
	max	I _{bin}	Prodotti finiti	
Max number of wires simultaneously connectable		Nr.	2	
Conductor section	Flexible w/o lug conductor section			
		min	mm ²	0.75
		max	mm ²	2.5
	Flexible c/w lug conductor section			
		min	mm ²	1.5
		max	mm ²	2.5
Flexible with insulated spade lug conductor section	min	mm ²	1.5	
	max	mm ²	2.5	
Power terminal protection according to IEC/EN 60529				IP20 when wired
Mechanical features				
Operating position	normal allowable		Vertical plan ±30°	
			Screw / DIN rail 35mm	
Fixing				Screw / DIN rail 35mm
Weight				g 203
Auxiliary contact characteristics				
Type of contact				3 NO + 1 NC
Thermal current I_{th}		A	10	
IEC/EN 60947-5-1 designation				A600 - Q600
Operating current AC15	230V	A	3	
	400V	A	1.9	
	500V	A	1.4	
Operating current DC12			110V A 2.9	
Operating current DC13				

24V	A	2.9
48V	A	1.4
60V	A	1.2
110V	A	0.6
125V	A	0.55
220V	A	0.3
600V	A	0.1

Operations

Mechanical life cycles 20000000

Safety related data

Performance level B10d according to EN/ISO 13489-1

mechanical load cycles 20000000

Mirror contacts according to IEC/EN 60947-4-1 YES

EMC compatibility Yes

DC coil operating

DC rated control voltage V 24

DC operating voltage

pick-up	min	%Us	75
	max	%Us	115
drop-out	min	%Us	10
	max	%Us	20

Average coil consumption $\leq 20^{\circ}\text{C}$

in-rush	W	2.3
holding	W	2.3

Max cycles frequency

Mechanical operation cycles/h 3600

Operating times

Average time for Us control

in AC

Closing NO	min	ms	12
	max	ms	21
Opening NO	min	ms	9
	max	ms	18
Closing NC	min	ms	17
	max	ms	26
Opening NC	min	ms	7
	max	ms	17

in DC

Closing NO	min	ms	18
	max	ms	25
Opening NO	min	ms	2
	max	ms	3
Closing NC	min	ms	3
	max	ms	5
Opening NC	min	ms	3
	max	ms	5

min	ms	11
max	ms	17

UL technical data

General USE

Contactor

AC current A 160

Contact rating of auxiliary contacts according to UL

A600 - Q600

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	+70

Storage temperature

min	°C	-60
max	°C	+80

Max altitude

m 3000

Resistance & Protection

Pollution degree

3

Dimensions

Wiring diagrams

Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-5-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL 60947-1

UL 60947-5-1

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000196 -
Contactor relay