



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cable Seal**

Operating Temperature Range: -55 – 125 °C [-67 – 257 °F]

Primary Product Color: **Red**

Primary Product Material: **VMQ**

Shore A Hardness: **40**

## Features

### Product Type Features

Connector Seal & Plug Type	Cable Seal
----------------------------	------------

### Configuration Features

Number of Positions	1
---------------------	---

### Body Features

Primary Product Color	Red
Primary Product Material	VMQ

### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
Operating Temperature (Max)	125 °C[257 °F]

### Packaging Features

Packaging Method	Box
Packaging Quantity	2500

### Other

Shore A Hardness	40
------------------	----



Contains Lubricant

Yes

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JAN 2025 (247)</p> <p>SVHC &gt; Threshold:</p> <p>Dodecamethylcyclohexasiloxane (D6) (.5% in 27519579030)</p> <p>Decamethylcyclopentasiloxane (D5) (.5% in 27519579030)</p> <p>Octamethylcyclotetrasiloxane (D4) (.5% in 27519579030)</p> <p><b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




### Compatible Parts



Also in the Series | **DEUTSCH DTSK**




Also in the Series | **DEUTSCH DT**





Infotainment & Multimedia Cable Assemblies(1)




Other Automotive Connector Accessories(27)



Rectangular Backshells & Clamps(3)

## Customers Also Bought



TE Part #YHVA630-2PHM-6MM-A  
HVA630-2phm,6sqmm,Key A



TE Part #DTSK04-1-08PA  
RECEPTACLE, INLINE, KEY A



TE Part #YHVA630-2PHM-4MM-A  
HVA630-2phm,4sqmm,Key A



TE Part #776437-2  
AS16,PLUG ASSY,ST,12P,N SEAL,  
CODE B



TE Part #2399666-2  
H&S 95mm, Inner spacer



TE Part #1587977-2  
INNER HOUSING, PLUG, HVA280-  
2PHM, PASS T




TE Part #4-2103015-4  
PLUG SUBASSY, D, HVA280-2PHM F



TE Part #2103170-1  
INNER HOUSING, CAP, HVA280-2PHM



TE Part #2141262-3  
SHIELDING,EMC



TE Part #2141264-3  
SINGLE WIRE SEAL,AMP MCP6.3/4.8K

## Documents

### Product Drawings

[WS-32-001, SEAL, RED, 9.49-10.52, DTSK](#)

English

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2289242-1\\_A.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2289242-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2289242-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[DEUTSCH DTSK Connectors Series Brief](#)

English

[DEUTSCH DTSK Components Infographic](#)

English

[ICT Terminals and Connectors Catalogue](#)

English

---

### Product Specifications

[Application Specification](#)

English