


TaNFilm® Precision SIP Network Commercial and MIL Qualified

4700 Series

- Inherent reliability
- MIL-PRF-83401 qualified
- Custom configuration available
- Bonded leads not susceptible to solder reflow problems
- Absolute tolerance to $\pm 0.1\%$ - ratio accuracy to $\pm 0.01\%$
- Absolute TCR to $\pm 15\text{ppm}/^\circ\text{C}$ - TC tracking to $\pm 5\text{ppm}/^\circ\text{C}$



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

The IRC 4700 Series is the ultimate combination of precision performance, reliability, and long term stability in a low profile, TaNFilm® SIP package. Rugged welded lead construction combined with the inherent passivation characteristics of tantalum nitride ensure superior ongoing performance over the installed life of the part.

Visit our website to view a graphical demonstration of IRC's TaNFilm reliability and performance features.

Commercial Product Capability Data

Schematic	Resistance Range (Ω)	Absolute Tolerance	Ratio Tolerance	Absolute TCR ($\text{ppm}/^\circ\text{C}$)	Tracking TCR ($\text{ppm}/^\circ\text{C}$)	Element Power (mW)
C	49.9 - 99.9	F, G, J	F, G	$\pm 50; \pm 100; \pm 300$	± 20	120
	100 - 200	B, D, F, G, J	D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 15	
	201 - 1.9K	B, D, F, G, J	B, D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 10	
	2.0K - 200K	B, D, F, G, J	A, B, D, F, G	$\pm 15; \pm 25; \pm 50; \pm 100; \pm 300$	± 5	
G	20 - 49.9	F, G, J	F, G	$\pm 50; \pm 100; \pm 300$	± 20	200
	50.0 - 199	D, F, G, J	B, D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 5	
	200 - 999	B, D, F, G, J	A, B, D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 5	
	1.0K - 100K	B, D, F, G, J	T, Q, A, B, D, F, G	$\pm 15; \pm 25; \pm 50; \pm 100; \pm 300$	± 5	
	101K - 400K	B, D, F, G, J	A, B, D, F, G	$\pm 15; \pm 25; \pm 50; \pm 100; \pm 300$	± 5	
F	49.9 - 99.9	F, G, J	F, G	$\pm 50; \pm 100; \pm 300$	± 20	120
	100 - 199	F, G, J	D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 10	
	200 - 999	B, D, F, G, J	B, D, F, G	$\pm 25; \pm 50; \pm 100; \pm 300$	± 5	
	1.0K - 200K	B, D, F, G, J	A, B, D, F, G	$\pm 15; \pm 25; \pm 50; \pm 100; \pm 300$	± 5	

Consult factory for tighter tolerances and TCR. Custom circuits and special testing available.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

4700 Series

MIL-PRF-83401 QPL Capability Data

Schematic	Resistance Range	Absolute Tolerance	Element Power (mW)	Size	Characteristic
C,G	100 - 100K	B, F, G, J	120	6, 8, 10	M, H, K

Package Specification Data

Schematic	Package Power (mW)			Voltage Rating	Temperature Range	Substrate	Lead Finish	Noise
	6-pin	8-pin	10-pin					
C, F (MIL and Commercial)	600	840	1080	$\sqrt{P \times R}$ not to exceed 100V	-65°C to +125°C	99.6% Alumina	Gold Plate (60/40 Sn/Pb available)	<-30dB
G (MIL)	360	480	600					
G (Commercial)	600	800	1000					

Environmental Data


Test Per MIL-PRF-83401	MIL-PRF-83401 ΔR Limits			TaNFilm® Test Data ΔR	
	M	K	H	Max	Typical
Thermal Shock And Power Conditioning	±0.7%	±0.7%	±0.5%	±0.10%	±0.02%
Low Temperature Operation	±0.5%	±0.25%	±0.1%	±0.05%	±0.02%
Short-term Overload	±0.5%	±0.25%	±0.1%	±0.1%	±0.02%
Terminal Strength	±0.25%	±0.25%	±0.1%	±0.1%	±0.02%
Resistance To Solder Heat	±0.25%	±0.25%	±0.1%	±0.1%	±0.02%
Moisture Resistance	±0.5%	±0.5%	±0.4%	±0.1%	±0.02%
Shock	±0.25%	±0.25%	±0.25%	±0.1%	±0.02%
Vibration	±0.25%	±0.25%	±0.25%	±0.1%	±0.02%
Life	±2.0%	±0.5%	±0.5%	±0.1%	±0.02%
High Temperature Exposure	±1.0%	±0.5%	±0.2%	±0.1%	±0.02%
Low Temperature Storage	±0.5%	±0.25%	±0.1%	±0.1%	±0.02%
25°C Double Load	±2.0%	±0.5%	±0.5%	±0.05%	±0.02%

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

4700 Series

Schematic Data



Physical Data



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

4700 Series

Commercial and MIL-Screened (Non-QPL) Ordering Data

Sample Part No. SIP - 4781 - 03 - 1001 - F - B

Model

- 4761 = 6-pin SIP, schematic C, gold terminations
- 4761SD = 6-pin SIP, schematic C, 60/40 Sn/Pb terminations
- 4768 = 6-pin SIP, schematic F, gold terminations
- 4768SD = 6-pin SIP, schematic F, 60/40 Sn/Pb terminations
- 4769 = 6-pin SIP, schematic G, gold terminations
- 4769SD = 6-pin SIP, schematic G, 60/40 Sn/Pb terminations

- 4781 = 8-pin SIP, schematic C, gold terminations
- 4781SD = 8-pin SIP, schematic C, 60/40 Sn/Pb terminations
- 4788 = 8-pin SIP, schematic F, gold terminations
- 4788SD = 8-pin SIP, schematic F, 60/40 Sn/Pb terminations
- 4789 = 8-pin SIP, schematic G, gold terminations
- 4789SD = 8-pin SIP, schematic G, 60/40 Sn/Pb terminations

- 4701 = 10-pin SIP, schematic C, gold terminations
- 4701SD = 10-pin SIP, schematic C, 60/40 Sn/Pb terminations
- 4708 = 10-pin SIP, schematic F, gold terminations
- 4708SD = 10-pin SIP, schematic F, 60/40 Sn/Pb terminations
- 4709 = 10-pin SIP, schematic G, gold terminations
- 4709SD = 10-pin SIP, schematic G, 60/40 Sn/Pb terminations

Absolute TCR

01 = ±100ppm/°C; 02 = ±50ppm/°C; 03 = ±25ppm/°C; 11 = ±15ppm/°C

MIL-PRF-83401 Group A Screening

04 = ±300ppm/°C Characteristic M; 05 = ±100ppm/°C Characteristic K
06 = ±50ppm/°C Characteristic H; 07 = ±25ppm/°C Characteristic H

Resistance

Standard 4-digit MIL resistance code
Example: 1001 = 1000Ω; 50R0=50Ω

Absolute Tolerance

J = ±5%; G = ±2%; F = ±1.0%; D = ±0.5%; B = ±0.1%

Optional Ratio Tolerance to R₁

F = ±1.0%; D = ±0.5%; C = ±0.25%; B = ±0.1%; A = ±0.05%; Q = ±0.02%, T = ±0.01%

Custom schematics and screening available.

Ordering Data - Military (MIL-PRF-83401)

Sample Part No. M83401 - 08 - H - 1002 - F - G

Model

M83401 = Military qualified resistor network

Size

- 07 = RZ070 6-pin SIP
- 08 = RZ080 8-pin SIP
- 09 = RZ090 10-pin SIP
- 21 = RZ210 Hi-Rel 6-pin SIP
- 22 = RZ220 Hi-Rel 8-pin SIP
- 23 = RZ230 Hi-Rel 10-pin SIP

Characteristic per MIL-PRF-83401

M; K; H

Resistance

Standard 4-digit MIL resistance code
Example: 1000 = 100Ω; 1001=1000Ω

Absolute Tolerance Code

J = ±5%; G = ±2%; F = ±1%; B = ±0.1%

Schematic

C; G

Standard termination is gold plate. Contact factory for optional 60/40 Sn/Pb hot solder dip finish.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.