

KEMET Part Number: PHE840MP6100MA05R06
(F840AL104M275C)

PHE840M/F840, Film, Metallized Polypropylene, Safety, 0.1 uF, 20%, 275 VAC (X2), 760 VDC, 105C, Lead Spacing = 10mm



General Information	
Supplier:	KEMET
Series:	PHE840M/F840
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
Notes:	Not For New Design, Please Check Possible Alternative Parts (AltPart)

Dimensions	
L	13mm MAX
H	7.5mm MAX
T	9.5mm MAX
S	10mm +/-0.4mm
LL	6mm NOM
F	0.6mm NOM

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	600

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage AC:	275 VAC (X2)
Voltage DC:	760 VDC
Temperature Range:	-55/+105C
Rated Temperature:	105C
Insulation Resistance:	30 GOhms
Max dV/dt:	100 V/us
Safety Class:	X2