



NOTES:

1. FOR USE WITH BOEING BMS13-65 OH & ADAMS RUSSELL FC28Z CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-546-2.
3. FOR CRIMPING USE DIE KTH-2212.
4. INTERFACE PER MIL-STD-348, FIG. 302-1.
5. CENTER CONTACT (1-856-24MA9) SUPPLIED UNASSEMBLED.
6. MARK PACKAGE: KINGS 795-16-9 (DATE CODE)
7. MATERIALS:
 INSULATOR: TEFLON, ASTM D1710
 GASKET: SIL. RUB., A-A-59588
 K-GRIP SLEEVE: COM. BRONZE TUBE PER ASTM B135
 OUTER CONTACT }
 SPRING WASHERS } BER. COP., ASTM B196
 ALL OTHER PARTS: BRASS, ASTM B16

8. FINISHES:

- CENTER CONTACT: .000050 MIN GOLD PLATE, PER ASTM B488
 OVER .000050 MIN NICKEL PER AMS-QQ-N-290 (RoHS)
 OUTER CONTACT & SPRING WASHER: .000200 MIN SILVER PER ASTM B700
 OVER .000020 MIN COPPER PER ASTM B734 (RoHS)
 ALL OTHER METAL PARTS: .000050 MIN NICKEL PER AMS-QQ-N-290
 OVER .000050 MIN COPPER PER ASTM B734 (RoHS)

9. ELECTRICAL CHARACTERISTICS:

- NOMINAL IMPEDANCE: 50 OHMS
 VOLTAGE RATING: 1000 VRMS
 FREQUENCY RANGE: DC TO 11 GHz
 VSWR: 1.35 MAX. .5 - 11 GHz
 INSERTION LOSS: DC TO 3.5 GHz, .03 dB MAX.
 3.5 TO 5.0 GHz, .105 dB MAX.

10. WEIGHT: 27.2 GRAMS

REVISIONS

ISSUE	CHANGES
F	REVISED AND REDRAWN PER ER8354 RMS 06/05/08
G	REVISED PER DMF304 AND ER3534 CY 10/24/11

795-16-9

CUSTOMER SALES DRAWING

THIS DRAWING, THE DESIGNS AND IDEAS EMBODIED IN THE DEVICE TO WHICH IT RELATES, AND THE METHOD OF PRODUCING THE DEVICE, ARE THE PROPERTY OF WINCHESTER ELECTRONICS CORPORATION AND SHALL NOT BE EMPLOYED, COPIED, OR DISCLOSED TO ANYONE, IN ANY MANNER WITHOUT THE CONSENT OF WINCHESTER ELECTRONICS CORPORATION.

SCALE 4:1

APPROX SURFACE AREA

WAS: E-17399

CAGE CODE:91836

REF:

PLUG, C

DRAWN	JCA	DATE	04/15/92
DESIGN	JT	DATE	04/16/92
APPR.		DATE	

KINGS
 by WINCHESTER
 ELECTRONICS
 Winchester Electronics
 62 Barnes Industrial
 Road North
 Wallingford, CT 06492

795-16-9