


SD



STAMP: KINGS KC-59-152

NOTES:

1. FOR USE WITH RG-174, 179, 187 & 188/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-406.
3. FOR CRIMPING USE DIE KTH-2032.
4. INTERFACE PER MIL-STD-348, FIG. 301-1.
5. MATERIALS:
 - INSULATORS: TEFLON, ASTM-D-4894
 - K-GRIP SLEEVE: COM. BRONZEASTM-B-145
 - GASKET: SILICONE RUBBER, ZZ-R-765
 - CENTER CONTACT } BER. COPPER, ASTM-B-196
 - OUTER CONTACT }
 - SPRING WASHER }
 - ALL OTHER METAL PARTS: BRASS, ASTM-B16
6. FINISHES:
 - SPRING WASHER: SILVER PLATE, PER QQ-S-365
 - CRIMP & CENTER CONTACT: HARD GOLD PLATE, PER MIL-G-45204
 - ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
7. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: 50 OHMS
 - WORKING VOLTAGE: 500 VRMS
 - FREQUENCY RANGE: DC TO 4 GHz.

SD

KC-59-152

REVISIONS

ISSUE	CHANGES	
	DATE	BY
6	CN 37051 D REDRAWN JJS 07/09/96	
7	CN 37267 E KH 02/21/97	
8	CN 37366 C MRM 07/22/97	

C59152C

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

PLUG, BNC

DRAWN	JJS	DATE	07/09/96
DESIGN	MJB	DATE	07/09/96
APPR.		DATE	

KINGS
ELECTRONICS CO., INC.
TUCKAHOE, NEW YORK 10707

KC-59-152