



- NOTES:
1. FOR USE WITH RG-8 AND 213/U CABLE.
  2. FOR CABLING INSTRUCTION SEE CP-480.
  3. FOR CABLE TRIMMING USE KTI-137 & KTD-138.
  4. FOR CRIMPING USE DIE SIZE 04.
  5. ITEM ④ TO BE SUPPLIED UNASSEMBLED.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010	2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. PLACE DECIMALS ± .004	3. NO FILLETS PERMITTED.
4. ANGLES ± 0°30'	4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.	5. ALL DIMENSIONS PRIOR TO PLATING.
	6. ALL PLATING IN ACCORDANCE WITH KER 10004.

(SHEET 1 OF 2)  
 KN-59-201

REVISIONS	
ISSUE	CHANGES
4	CN 22707 E REDRAWN M.D. 30 OCT 81
5	CN 26916 D EAJ 15 FEB 85
6	CN 31129 C JCA 11 SEP 89

**MASTER**  
**S-D**

SCALE	3:1
APPROX SURFACE AREA	
USED ON	
REF.	
N PLUG	
DRAWN M.D.	DATE 30 OCT 81
APPR. MJB	DATE 3 NOV 81

KN-59-201  
(SHEET 1 OF 2)