


DASH NO. M CODE MADE FROM

REVISIONS	
ISSUE	CHANGES
3	CH 11274 A WJA 25 JUN 72
4	CN 23812 C MD. 10 SEP 82

SD-65-N



NOTES:

- FOR USE WITH RG-9, 9A, 9B & 214/U CABLE.
- FOR CABLE TRIMMING USE KTY-7A & KTD-2B.
- FOR CRIMPING USE DIE SIZE 04.
- FOR CABLING INSTRUCTIONS SEE CP-402.
- MATERIALS:
 - K-GRIP BODY } BRASS,
 - COUPLING NUT } QQ-B-613
 - CENTER CONTACT } PHOSPHOR BRONZE,
 - OUTER CONTACT } QQ-B-750
 - SPRING } ALLOY 220.
 - K-GRIP SLEEVE - COMM. BRONZE,
 - INSULATOR - TEFLON, MIL-P-1946B.
 - GASKET - SILICONE RUBBER
 - ZZ-R-765a
- FINISHES:
 - CENTER CONTACT - SILVER PLATE
 - QQ-S-365, .0004 MIN.
 - ALL OTHER } SILVER PLATE
 - METAL PARTS } .0002 MIN. QQ-S-365.
- ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE - 50 Ω.
 - WORKING VOLTAGE - 1000 VOLTS RMS.
 - FREQUENCY RANGE - DC TO 11 GHz.

SCALE:

USED ON:

REF:

FINISH SPEC.

MATL SPEC.

N PLUG

DRAWN NPM	DATE 27 JULY 75
APPR. [Signature]	DATE 27 JUL 75

KINGS ELECTRONICS
40 MARBLEDALE ROAD
TUCKAHOE, N. Y. 10707

KN-59-65

UNLESS OTHERWISE SPECIFIED:

- TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010
3 PLACE DECIMALS ± .004 ANGLES ± 0° 30'
- REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX.
- NO FILLETS PERMITTED.
- SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
- ALL DIMENSIONS PRIOR TO PLATING.