



DASH NO.	DESCRIPTION	MADE FROM
----------	-------------	-----------



S-D

M39012/28-0502

REVISIONS	
ISSUE	CHANGES
0	ER 14639 MJB 25 JUL 75
1	CN 21633 C PAS 23 FEB 81
2	CN 22767 E JEP 17 NOV. 81
5	CN 32302 A LNM 20 JUN 90

- NOTES:
- FOR USE WITH RG-180, 180A, 180B, 195, 195A/U CABLE.
 - FOR CABLE TRIMMING USE KTJ-116 & KTD-161.
 - FOR FORMING USE CRIMP DIE SIZE 07.
 - FOR CABLING INSTRUCTIONS SEE CP-465.
 - ITEM 5 TO BE SUPPLIED UNASSEMBLED.

KA-19-151

USED ON:

REP:

FINISH

SPEC. KER 10009

ITEM	REQ'D	DESCRIPTION	PART NO.
9	1	CABLING INSTRUCTIONS	3-103-2780
8	1	RETAINING RING	E-2252-MC7
7	1	HEX. NUT	492A-9-MC7
6	1	LOCKWASHER	492A-12-MC7
5	1	ENCRIMP CAPTIVE CONTACT	1-507-35M9D
4	1	INSULATOR	A-19-106-2-M39
3	1	GASKET	492A-10-M39
2	1	K-GRIP BODY	E-59-1191-MC7
1	1	K-GRIP SLEEVE	E-59-1191-MC7

MATL	
SPEC.	
TNC BULKHEAD JACK	
DRAWN	MJB
DATE	25 JUL 75
APPR.	L1
DATE	25 JUL 75

KINGS ELECTRONICS
 40 MARBLEDALE ROAD
 TUCKAHOE, N. Y. 10707

M39012/28-0502

UNLESS OTHERWISE SPECIFIED:

- | | |
|--|--|
| 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010 | 2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX. |
| 3 PLACE DECIMALS ± .004 | 3. NO FILLETS PERMITTED. |
| T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES. | 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX. |
| | 5. ALL DIMENSIONS PRIOR TO PLATING. |

C-N