

Single Row Terminal Blocks

Kulka® 411 Series

300 Volts*



Specifications:

- Base, Phenolic, 150° C
- Open Back Design (Insulator Strip Required for Voltage Rating)
- JJ (GDI-30F) Material Available
- Screws, #2-56 Binder Head, Phil-Slot
- Terminals, Plated Brass
- 1-23 Poles
- 1/4" Centers
- Wire Range With Wire Binding Screw #18-#20 AWG – 5 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. E47811
- CSA Certified File No. LR19766
- C€

Hardware Options: (Hardware options may affect ratings - consult factory)

KT10	= Full Quick Connect (0° Flat)	See Page 92
KT11	= Full Quick Connect (45° Bend)	See Page 92
KT12	= Full Quick Connect (90° Bend)	See Page 92
ST	= Full Solder	See Page 94
J 410	= Line to Line Jumper	See Page 96
3/4 ST	= Half Solder	See Page 94
KT 16	= Half Quick Connect (0° Flat)	See Page 92
KT 17	= Half Quick Connect (45° Bend)	See Page 92
KT 18	= Half Quick Connect (90° Bend)	See Page 92
Z	= Lug Over the Side (.312)	
1921	= Printed Circuit Pin (.125) (Over the Side)	
1904	= Feed Thru Solder	See Page 98

Catalog Description	Number of Poles	Dimensions	
		A	B
411 GP 01	1	0.75	0.50
411 GP 02	2	1.00	0.75
411 GP 03	3	1.25	1.00
411 GP 04	4	1.50	1.25
411 GP 05	5	1.75	1.50
411 GP 06	6	2.00	1.75
411 GP 07	7	2.25	2.00
411 GP 08	8	2.50	2.25
411 GP 09	9	2.75	2.50
411 GP 10	10	3.00	2.75
411 GP 11	11	3.25	3.00
411 GP 12	12	3.50	3.25
411 GP 13	13	3.75	3.50
411 GP 14	14	4.00	3.75
411 GP 15	15	4.25	4.00
411 GP 16	16	4.50	4.25
411 GP 17	17	4.75	4.50
411 GP 18	18	5.00	4.75
411 GP 19	19	5.25	5.00
411 GP 20	20	5.50	5.25
411 GP 21	21	5.75	5.50
411 GP 22	22	6.00	5.75
411 GP 23	23	6.25	6.00

MM=Dim X 25.4

*Based on Class B Requirements

